

REV. 2

DCO 142340


COIL: @ 25°C
 RESISTANCE 210 OHMS ± 10%
 NOMINAL VOLTAGE 12.0 VDC
 MUST OPERATE 5.4 VDC
 MUST RELEASE 3.2 VDC MAX. 0.6 VDC MIN.

ENVIRONMENT:

VIBRATION 10 CPS TO 3000 CPS @ 30 g's
 SHOCK 75 g's 6 MS. DURATION
 TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE & RELEASE 4 MS MAX.
CONTACT STABILIZATION 2.5 MS MAX.

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO
2 AMPS 28 VDC RESISTIVE
50,000 OPERATIONS

DR. R.B. 3/21/97

CK. *[Signature]*



COMMUNICATIONS
 INSTRUMENTS, INC.

CUST. QPL
 CUST. NO. M39016/13-056M REV.

"3SBC" RELAY

3SBC1517A2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[3SBC1517A2](#)