

REV. 0

DCO 143070


TOL $\pm .010$ UNLESS OTHERWISE SPECIFIED

COIL: @ 25°C
 RESISTANCE 210 OHMS $\pm 10\%$
 NOMINAL VOLTAGE 12.0 VDC
 MUST OPERATE 5.4 VDC
 MUST RELEASE 3.2 VDC MAX., 0.6 VDC MIN.

ENVIRONMENT:
 VIBRATION 10 CPS TO 3000 CPS @ 30 g's
 SHOCK 75 g's 6 MS. DURATION
 TEMPERATURE -65°C TO +125°C

NOTES: OPERATE 4 MS MAX.
 RELEASE 6 MS MAX.
 CONTACT STABILIZATION 2.0 MS MAX.

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL TO
 2 AMPS 28 VDC RESISTIVE
 50,000 OPERATIONS

DR. B.D. 6/28/01 CK 6/28/01

CII Technologies
 advanced control electronic solutions

CUST. QPL
 CUST. NO. M39016/37-017P REV.

"3SBC" RELAY

3SBC2087A2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[3SBC2087A2](#)