




D




C




B



A



SECTION X-X



RECOMMENDED HOLE LAYOUT

- 1 THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING
- 2 POINT OF MEASUREMENT FOR PLATING THICKNESS
- 3 .000030 GOLD IN CONTACT AREA, .000100-.000200 MATTE TIN-LEAD ON THE SOLDER TAIL, ALL OVER .000050 NICKEL
- 4 .000030 GOLD IN CONTACT AREA, .000100-.000200 MATTE TIN ON THE SOLDER TAIL, ALL OVER .000050 NICKEL
- 5 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

OBSOLETE	4	4	2.890	.190	3.200	2.900	29	60	-7-103337-8
	4	4	1.890	.190	2.200	1.900	19	40	-6-103337-8
	4	4	1.590	.190	1.900	1.600	16	34	6-103337-5
	4	4	1.190	.190	1.500	1.200	12	26	6-103337-1
OBSOLETE	3	3	—	.390	1.000	.700	7	16	5-103337-6
	3	3	2.890	.190	3.200	2.900	29	60	-2-103337-8
	3	3	2.790	.190	3.100	2.800	28	58	2-103337-7
	3	3	2.690	.190	3.000	2.700	27	56	2-103337-6
	3	3	2.590	.190	2.900	2.600	26	54	2-103337-5
	3	3	2.490	.190	2.800	2.500	25	52	2-103337-4
	3	3	2.390	.190	2.700	2.400	24	50	2-103337-3
	3	3	2.290	.190	2.600	2.300	23	48	2-103337-2
	3	3	2.190	.190	2.500	2.200	22	46	2-103337-1
	3	3	2.090	.190	2.400	2.100	21	44	2-103337-0
	3	3	1.990	.190	2.300	2.000	20	42	1-103337-9
	3	3	1.890	.190	2.200	1.900	19	40	1-103337-8
	3	3	1.790	.190	2.100	1.800	18	38	1-103337-7
	3	3	1.690	.190	2.000	1.700	17	36	1-103337-6
	3	3	1.590	.190	1.900	1.600	16	34	1-103337-5
OBSOLETE	3	3	1.490	.190	1.800	1.500	15	32	1-103337-4
	3	3	1.390	.190	1.700	1.400	14	30	1-103337-3
	3	3	1.290	.190	1.600	1.300	13	28	1-103337-2
	3	3	1.190	.190	1.500	1.200	12	26	1-103337-1
	3	3	1.090	.190	1.400	1.100	11	24	1-103337-0
	3	3	.990	.190	1.300	1.000	10	22	103337-9
	3	3	.890	.190	1.200	.900	9	20	103337-8
	3	3	—	.490	1.100	.800	8	18	103337-7
	3	3	—	.390	1.000	.700	7	16	103337-6
	3	3	—	.390	.900	.600	6	14	103337-5
OBSOLETE	3	3	—	.290	.800	.500	5	12	103337-4
	3	3	—	.290	.700	.400	4	10	103337-3
	3	3	—	.190	.600	.300	3	8	103337-2
	3	3	—	.190	.500	.200	2	6	103337-1
	3	3	—	.190	.500	.200	2	6	103337-1
	3	3	—	.190	.500	.200	2	6	103337-1

PLATING	E	D	C	B	A	NO OF POSN	ASSEMBLY PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.							
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DWN H MOLL 01SEP87		Tyco Electronics Corporation	
0 PLC ± -		1 PLC ± -		CHK T. CLARK 03SEP87		Tyco Electronics Corporation	
2 PLC ± -		3 PLC ± -		APVD T. CLARK 03SEP87		Harrisburg, Pa 17105-3608	
4 PLC ± -		ANGLES ± -		NAME		HDR ASSY, MOD II, COMPLIANT	
MATERIAL: HOUSING: FLAME RETARDANT THERMOPLASTIC, COLOR-BLACK		FINISH: SEE TABLE		PRODUCT SPEC		PIN, DBL ROW, .100X.100 C/L, 4 SIDED SHROUD	
POSTS: Cu-Ni-Sn		WEIGHT		APPLICATION SPEC		SIZE CAGE CODE DRAWING NO	
		CUSTOMER DRAWING		A1 00779		RESTRICTED TO	
				SCALE 4:1		SHEET 1 OF 1	
						REV K2	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[6-103337-1](#)