





LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			L	REVISED PER ECO-15-014472	09OCT2015	NK	MM




RECOMMENDED PCB LAYOUT
FOR USE WITH .008 THICK STENCIL



1	THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND THE HOUSING.
2	0.000762[.000030] GOLD ON CONTACT AREA, 0.00254[.000100]–0.00508[.000200] MATTE TIN–LEAD ON SOLDER TAIL, ALL OVER 0.00127[.000050] NICKEL.
3	HOUSING: LCP, COLOR–BLACK. POSTS: COPPER ALLOY.
4	0.000762[.000030] GOLD ON CONTACT AREA, 0.00254[.000100]–0.00508[.000200] MATTE TIN ON SOLDER TAIL, ALL OVER 0.00127[.000050] NICKEL.
5	OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

	35.56 [1.400]	14	35.69 [1.484]	15	6-146128-3
	33.02 [1.300]	13	33.15 [1.384]	14	6-146128-2
	30.48 [1.200]	12	30.61 [1.284]	13	6-146128-1
	27.94 [1.100]	11	28.07 [1.184]	12	6-146128-0
	25.40 [1.000]	10	27.53 [1.084]	11	5-146128-9
	22.86 [.900]	9	24.99 [.984]	10	5-146128-8
	20.32 [.800]	8	22.45 [.884]	9	5-146128-7
	17.78 [.700]	7	19.91 [.784]	8	5-146128-6
	15.24 [.600]	6	17.37 [.684]	7	5-146128-5
	12.70 [.500]	5	14.83 [.584]	6	5-146128-4
	10.16 [.400]	4	12.29 [.484]	5	5-146128-3
	7.62 [.300]	3	9.75 [.384]	4	5-146128-2
	5.08 [.200]	2	7.21 [.284]	3	5-146128-1
	35.56 [1.400]	14	35.69 [1.484]	15	1-146128-3
	33.02 [1.300]	13	33.15 [1.384]	14	1-146128-2
	30.48 [1.200]	12	30.61 [1.284]	13	1-146128-1
	27.94 [1.100]	11	28.07 [1.184]	12	1-146128-0
	25.40 [1.000]	10	27.53 [1.084]	11	146128-9
	22.86 [.900]	9	24.99 [.984]	10	146128-8
	20.32 [.800]	8	22.45 [.884]	9	146128-7
	17.78 [.700]	7	19.91 [.784]	8	146128-6
	15.24 [.600]	6	17.37 [.684]	7	146128-5
	12.70 [.500]	5	14.83 [.584]	6	146128-4
	10.16 [.400]	4	12.29 [.484]	5	146128-3
	7.62 [.300]	3	9.75 [.384]	4	146128-2
	5.08 [.200]	2	7.21 [.284]	3	146128-1
PLATING	C	B	A	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J KNAUB 50-09-94 QLK G DUBNICZKI 30-09-94 APVD G DUBNICZKI 30-09-94		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES, UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 3 PLC ± .127[.005] 4 PLC ± — ANGLES ± —		NAME SURFACE MOUNT HEADER ASSEMBLY, MOD II, BREAKAWAY, VERTICAL, SINGLE ROW, .100 X.100 C/L .025 SQ.POST	
		PRODUCT SPEC APPLICATION SPEC		SIZE GAGE CODE DRAWING NO A1 00779 C=146128	
MATERIAL FINISH SEE TABLE		WEIGHT —		RESTRICTED TO —	
		CUSTOMER DRAWING		SCALE 10:1 SHEET 1 OF 1 REV —	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[146128-3](#)