








SECTION X-X



RECOMMENDED HOLE LAYOUT

- | | |
|---|--|
| 1 | THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING |
| 2 | POINT OF MEASUREMENT FOR PLATING THICKNESS |
| 3 | .000030 GOLD IN CONTACT AREA, .000100-.000200 MATTE TIN-LEAD ON THE SOLDER TAIL, ALL OVER .000050 NICKEL |
| 4 | .000030 GOLD IN CONTACT AREA, .000100-.000200 MATTE TIN ON THE SOLDER TAIL, ALL OVER .000050 NICKEL |
| 5 | OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI |

5	OBSOLETE	4	2.890	.190	3.200	2.900	29	60	7-103337-8
		4	1.890	.190	2.200	1.900	19	40	6-103337-8
		4	1.590	.190	1.900	1.600	16	34	6-103337-5
		4	1.190	.190	1.500	1.200	12	26	6-103337-1
6	OBSOLETE	4	—	.390	1.000	.700	7	16	5-103337-6
		3	2.890	.190	3.200	2.900	29	60	2-103337-8
		3	2.790	.190	3.100	2.800	28	58	2-103337-7
		3	2.690	.190	3.000	2.700	27	56	2-103337-6
		3	2.590	.190	2.900	2.600	26	54	2-103337-5
		3	2.490	.190	2.800	2.500	25	52	2-103337-4
		3	2.390	.190	2.700	2.400	24	50	2-103337-3
		3	2.290	.190	2.600	2.300	23	48	2-103337-2
		3	2.190	.190	2.500	2.200	22	46	2-103337-1
		3	2.090	.190	2.400	2.100	21	44	2-103337-0
		3	1.990	.190	2.300	2.000	20	42	1-103337-9
		3	1.890	.190	2.200	1.900	19	40	1-103337-8
		3	1.790	.190	2.100	1.800	18	38	1-103337-7
		3	1.690	.190	2.000	1.700	17	36	1-103337-6
		3	1.590	.190	1.900	1.600	16	34	1-103337-5
		OBSOLETE	3	1.490	.190	1.800	1.500	15	32
3	1.390		.190	1.700	1.400	14	30	1-103337-3	
3	1.290		.190	1.600	1.300	13	28	1-103337-2	
3	1.190		.190	1.500	1.200	12	26	1-103337-1	
OBSOLETE	3	1.090	.190	1.400	1.100	11	24	1-103337-0	
	3	.990	.190	1.300	1.000	10	22	103337-9	
	3	.890	.190	1.200	.900	9	20	103337-8	
	3	—	.490	1.100	.800	8	18	103337-7	
OBSOLETE	3	—	.390	1.000	.700	7	16	103337-6	
	3	—	.390	.900	.600	6	14	103337-5	
	3	—	.290	.800	.500	5	12	103337-4	
	3	—	.290	.700	.400	4	10	103337-3	
	3	—	.190	.600	.300	3	8	103337-2	
	3	—	.190	.500	.200	2	6	103337-1	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG H. MOLL	01SEP87	 Tyco Electronics Corporation Harrisburg, Pa 17105-3608
		CHK T. CLARK	03SEP87	
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		
INCHES		APVD T. CLARK	03SEP87	
	0. PLC ± .	PRODUCT SPEC	—	
	1. PLC ± .	APPLICATION SPEC	—	
MATERIAL HOUSING: — NAME — FLAME RETARDANT THERMOPLASTIC, COLOR—BLACK POSTS: Cu-Ni-Sn		FINISH SEE TABLE	WEIGHT	SIZE CAD CODE DRAWING NO RESTRICTED TO
		CUSTOMER DRAWING	A1 00779 C-103337	—
			SCALE 4:1 SHEET 1 OF 1 REV K3	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-103337-1](#)