





- | | | | | | | | | |
|---------------|----------|--------------|--------------|------------------|------------------|----|----|------------|
| <div>11</div> | | <div>9</div> | <div>6</div> | 23.37
[.920] | 25.27
[.995] | 8 | 9 | 3–103669–0 |
| | | <div>9</div> | <div>6</div> | 8.13
[.320] | 10.03
[.395] | 2 | 3 | 2–103669–9 |
| | | <div>9</div> | <div>6</div> | 15.75
[.620] | 17.65
[.695] | 5 | 6 | 2–103669–8 |
| | | <div>9</div> | <div>6</div> | 13.21
[.520] | 15.11
[.595] | 4 | 5 | 2–103669–7 |
| | | <div>9</div> | <div>6</div> | 10.67
[.420] | 12.57
[.495] | 3 | 4 | 2–103669–6 |
| | | <div>9</div> | <div>6</div> | 5.59
[.220] | 7.49
[.295] | 1 | 2 | 2–103669–5 |
| <div>11</div> | OBSOLETE | <div>9</div> | <div>1</div> | 64.01
[2.520] | 65.91
[2.595] | 24 | 25 | 2–103669–4 |
| <div>11</div> | OBSOLETE | <div>9</div> | <div>1</div> | 61.47
[2.420] | 63.37
[2.495] | 23 | 24 | 2–103669–3 |
| <div>11</div> | OBSOLETE | <div>9</div> | <div>1</div> | 58.93
[2.320] | 60.83
[2.395] | 22 | 23 | 2–103669–2 |
| <div>11</div> | OBSOLETE | <div>9</div> | <div>1</div> | 56.39
[2.220] | 58.29
[2.295] | 21 | 22 | 2–103669–1 |
| <div>11</div> | OBSOLETE | <div>9</div> | <div>1</div> | 53.85
[2.120] | 55.75
[2.195] | 20 | 21 | 2–103669–0 |
| <div>11</div> | | <div>9</div> | <div>1</div> | 51.31
[2.020] | 53.21
[2.095] | 19 | 20 | 1–103669–9 |
| | OBSOLETE | <div>9</div> | <div>1</div> | 48.77
[1.920] | 50.67
[1.995] | 18 | 19 | 1–103669–8 |
| | OBSOLETE | <div>9</div> | <div>1</div> | 46.23
[1.820] | 48.13
[1.895] | 17 | 18 | 1–103669–7 |
| <div>11</div> | | <div>9</div> | <div>1</div> | 43.69
[1.720] | 45.59
[1.795] | 16 | 17 | 1–103669–6 |
| | | <div>9</div> | <div>1</div> | 41.15
[1.620] | 43.05
[1.695] | 15 | 16 | 1–103669–5 |
| <div>11</div> | OBSOLETE | <div>9</div> | <div>1</div> | 38.61
[1.520] | 40.51
[1.595] | 14 | 15 | 1–103669–4 |
| <div>11</div> | | <div>9</div> | <div>1</div> | 36.07
[1.420] | 37.97
[1.495] | 13 | 14 | 1–103669–3 |
| | | <div>9</div> | <div>1</div> | 33.53
[1.320] | 35.43
[1.395] | 12 | 13 | 1–103669–2 |
| | | <div>9</div> | <div>1</div> | 30.99
[1.220] | 32.89
[1.295] | 11 | 12 | 1–103669–1 |
| | | <div>9</div> | <div>1</div> | 28.45
[1.120] | 30.35
[1.195] | 10 | 11 | 1–103669–0 |
| | | <div>9</div> | <div>1</div> | 25.91
[1.020] | 27.81
[1.095] | 9 | 10 | 103669–9 |
| | | <div>9</div> | <div>1</div> | 23.37
[.920] | 25.27
[.995] | 8 | 9 | 103669–8 |
| | | <div>9</div> | <div>1</div> | 20.83
[.820] | 22.73
[.895] | 7 | 8 | 103669–7 |
| | | <div>9</div> | <div>1</div> | 18.29
[.720] | 20.19
[.795] | 6 | 7 | 103669–6 |
| | | <div>9</div> | <div>1</div> | 15.75
[.620] | 17.65
[.695] | 5 | 6 | 103669–5 |
| | | <div>9</div> | <div>1</div> | 13.21
[.520] | 15.11
[.595] | 4 | 5 | 103669–4 |
| | | <div>9</div> | <div>1</div> | 10.67
[.420] | 12.57
[.495] | 3 | 4 | 103669–3 |
| | | <div>9</div> | <div>1</div> | 8.13
[.320] | 10.03
[.395] | 2 | 3 | 103669–2 |
| | | <div>9</div> | <div>1</div> | 5.59
[.220] | 7.49
[.295] | 1 | 2 | 103669–1 |

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 3-5-91 SHUEY CHK 2-14-92 M. RIDER APD: M. RIDER 2-14-92		 TE Connectivity	
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 P/LC ± .01 1 P/LC ± .01 2 P/LC ± .015(.005) 3 P/LC ± .01 4 P/LC ± .01 ANGLES ± ±		NAME HDR ASSY, VERT, SINGLE ROW 2.54 [100] C/L 0.64 [025] SQ POST WITH PLZLN, AMPMODU MTE	
		PRODUCT SPEC 108-25034 APPLICATION SPEC 114-25026		SIZE CAGE CODE DRAWING NO A1 00779 C 10366	
MATERIAL: HOUSING: LCP, CONTACTS: BRASS		WEIGHT —		RESTRICTED TO —	
SEE TABLE		CUSTOMER DRAWING		SCALE 4:1 SHEET 1 OF 2 REV A0	

8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT

By

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

OBSOLETE

11

<div><div>9</div><div>10</div></div>	<div><div>8</div></div>	64.01 [2.520]	65.91 [2.595]	24	25	7-103669-4
<div><div>9</div><div>10</div></div>	<div><div>8</div></div>	61.47 [2.420]	63.37 [2.495]	23	24	7-103669-3
<div><div>9</div><div>10</div></div>	<div><div>8</div></div>	58.93 [2.320]	60.83 [2.395]	22	23	7-103669-2
<div><div>9</div><div>10</div></div>	<div><div>8</div></div>	56.39 [2.220]	58.29 [2.295]	21	22	7-103669-1
<div><div>9</div><div>10</div></div>	<div><div>8</div></div>	53.85 [2.120]	55.75 [2.195]	20	21	7-103669-0
<div><div>9</div><div>10</div></div>	<div><div>8</div></div>	51.31 [2.020]	53.21 [2.095]	19	20	6-103669-9
<div><div>9</div><div>10</div></div>	<div><div>8</div></div>	48.77 [1.920]	50.67 [1.995]	18	19	6-103669-8
<div><div>9</div><div>10</div></div>	<div><div>8</div></div>	46.23 [1.820]	48.13 [1.895]	17	18	6-103669-7
<div><div>9</div><div>10</div></div>	<div><div>8</div></div>	43.69 [1.720]	45.59 [1.795]	16	17	6-103669-6
<div><div>9</div><div>10</div></div>	<div><div>8</div></div>	41.15 [1.620]	43.05 [1.695]	15	16	6-103669-5
<div><div>9</div><div>10</div></div>	<div><div>8</div></div>	38.61 [1.520]	40.51 [1.595]	14	15	6-103669-4
<div><div>9</div><div>10</div></div>	<div><div>8</div></div>	36.07 [1.420]	37.97 [1.495]	13	14	6-103669-3
<div><div>9</div><div>10</div></div>	<div><div>8</div></div>	33.53 [1.320]	35.43 [1.395]	12	13	6-103669-2
<div><div>9</div><div>10</div></div>	<div><div>8</div></div>	30.99 [1.220]	32.89 [1.295]	11	12	6-103669-1
<div><div>9</div><div>10</div></div>	<div><div>8</div></div>	28.45 [1.120]	30.35 [1.195]	10	11	6-103669-0
<div><div>9</div><div>10</div></div>	<div><div>8</div></div>	25.91 [1.020]	27.81 [1.095]	9	10	5-103669-9
<div><div>9</div><div>10</div></div>	<div><div>8</div></div>	23.37 [.920]	25.27 [.995]	8	9	5-103669-8
<div><div>9</div><div>10</div></div>	<div><div>8</div></div>	20.83 [.820]	22.73 [.895]	7	8	5-103669-7
<div><div>9</div><div>10</div></div>	<div><div>8</div></div>	18.29 [.720]	20.19 [.795]	6	7	5-103669-6
<div><div>9</div><div>10</div></div>	<div><div>8</div></div>	15.75 [.620]	17.65 [.695]	5	6	5-103669-5
<div><div>9</div><div>10</div></div>	<div><div>8</div></div>	13.21 [.520]	15.11 [.595]	4	5	5-103669-4
<div><div>9</div><div>10</div></div>	<div><div>8</div></div>	10.67 [.420]	12.57 [.495]	3	4	5-103669-3
<div><div>9</div><div>10</div></div>	<div><div>8</div></div>	8.13 [.320]	10.03 [.395]	2	3	5-103669-2
<div><div>9</div><div>10</div></div>	<div><div>8</div></div>	5.59 [.220]	7.49 [.295]	1	2	5-103669-1
REMARKS	PLATING	C	B	A	NO. OF POSN	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
S. SHUEY

3-5-91

CHK
M. RIDER

2-14-92

APVD
M. RIDER

2-14-92

NAME

DIMENSIONS:
INCHES

0 PLC ± —

1 PLC ± —

2 PLC ± 0.13[.005]

3 PLC ± —

4 PLC ± —

ANGLES ± —

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

FINISH

MATERIAL
HOUSING: LCP,
CONTACTS: BRASS

SEE TABLE

PRODUCT SPEC
108-25034

APPLICATION SPEC
114-25026

WEIGHT
—

SIZE
A1

CAGE CODE
00779

DRAWING NO
C=103669

RESTRICTED TO
—

CUSTOMER DRAWING

SCALE
4:1

SHEET
2

OF
2

REV
AC

STE

TE Connectivity

HDR ASSY, VERT, SINGLE ROW
2.54 [.100] C/L 0.64 [.025] SQ POST
WITH PLZN, AMPMODU MTE

4805 (1/15)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[6-103669-5](#)