


<div>9</div>	<div>6</div>	23.37 [.920]	25.27 [.995]	8	9	3-103669-0
<div>9</div>	<div>6</div>	8.13 [.320]	10.03 [.395]	2	3	2-103669-9
<div>9</div>	<div>6</div>	15.75 [.620]	17.65 [.695]	5	6	2-103669-8
<div>9</div>	<div>6</div>	13.21 [.520]	15.11 [.595]	4	5	2-103669-7
<div>9</div>	<div>6</div>	10.67 [.420]	12.57 [.495]	3	4	2-103669-6
<div>9</div>	<div>6</div>	5.59 [.220]	7.49 [.295]	1	2	2-103669-5
<div>9</div>	<div>1</div>	64.01 [2.520]	65.91 [2.595]	24	25	2-103669-4
<div>9</div>	<div>1</div>	61.47 [2.420]	63.37 [2.495]	23	24	2-103669-3
<div>9</div>	<div>1</div>	58.93 [2.320]	60.83 [2.395]	22	23	2-103669-2
<div>9</div>	<div>1</div>	56.39 [2.220]	58.29 [2.295]	21	22	2-103669-1
<div>9</div>	<div>1</div>	53.85 [2.120]	55.75 [2.195]	20	21	2-103669-0
<div>9</div>	<div>1</div>	51.31 [2.020]	53.21 [2.095]	19	20	1-103669-9
<div>9</div>	<div>1</div>	48.77 [1.920]	50.67 [1.995]	18	19	1-103669-8
<div>9</div>	<div>1</div>	46.23 [1.820]	48.13 [1.895]	17	18	1-103669-7
<div>9</div>	<div>1</div>	43.69 [1.720]	45.59 [1.795]	16	17	1-103669-6
<div>9</div>	<div>1</div>	41.15 [1.620]	43.05 [1.695]	15	16	1-103669-5
<div>9</div>	<div>1</div>	38.61 [1.520]	40.51 [1.595]	14	15	1-103669-4
<div>9</div>	<div>1</div>	36.07 [1.420]	37.97 [1.495]	13	14	1-103669-3
<div>9</div>	<div>1</div>	33.53 [1.320]	35.43 [1.395]	12	13	1-103669-2
<div>9</div>	<div>1</div>	30.99 [1.220]	32.89 [1.295]	11	12	1-103669-1
<div>9</div>	<div>1</div>	28.45 [1.120]	30.35 [1.195]	10	11	1-103669-0
<div>9</div>	<div>1</div>	25.91 [1.020]	27.81 [1.095]	9	10	103669-9
<div>9</div>	<div>1</div>	23.37 [.920]	25.27 [.995]	8	9	103669-8
<div>9</div>	<div>1</div>	20.83 [.820]	22.73 [.895]	7	8	103669-7
<div>9</div>	<div>1</div>	18.29 [.720]	20.19 [.795]	6	7	103669-6
<div>9</div>	<div>1</div>	15.75 [.620]	17.65 [.695]	5	6	103669-5
<div>9</div>	<div>1</div>	13.21 [.520]	15.11 [.595]	4	5	103669-4
<div>9</div>	<div>1</div>	10.67 [.420]	12.57 [.495]	3	4	103669-3
<div>9</div>	<div>1</div>	8.13 [.320]	10.03 [.395]	2	3	103669-2
<div>9</div>	<div>1</div>	5.59 [.220]	7.49 [.295]	1	2	103669-1

REMARKS	PLATING	C	B	A	NO. OF POSN	PART NO.
---------	---------	---	---	---	-------------------	----------

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 3--9-91 S. SHUEY CHK 2-14-92 M. RIDER		 TE Connectivity	
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED: APPLIC. SPEC. 2-14-92 M. RIDER		NAME	
		PRODUCT SPEC 108-25034 APPLICATION SPEC 114-25026		HDR ASSY, VERT, SINGLE ROW 2.54 [100] C/L 0.64 [025] SQ POST WITH PLZLN, AMPMOD MTE	
MATERIAL		WEIGHT		SIZE	CAGE CODE
HOUSING: LCP, CONTACTS: BRASS		SEE TABLE		A1	00779
		CUSTOMER DRAWING		DRAWING NO	
				103660	
				SCALE	4:1
				SHEET	1 OF 2
				REV	A

8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT

By

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

OBSOLETE

11

<div>9</div> <div>10</div>	<div>8</div>	64.01 [2.520]	65.91 [2.595]	24	25	7-103669-4
<div>9</div> <div>10</div>	<div>8</div>	61.47 [2.420]	63.37 [2.495]	23	24	7-103669-3
<div>9</div> <div>10</div>	<div>8</div>	58.93 [2.320]	60.83 [2.395]	22	23	7-103669-2
<div>9</div> <div>10</div>	<div>8</div>	56.39 [2.220]	58.29 [2.295]	21	22	7-103669-1
<div>9</div> <div>10</div>	<div>8</div>	53.85 [2.120]	55.75 [2.195]	20	21	7-103669-0
<div>9</div> <div>10</div>	<div>8</div>	51.31 [2.020]	53.21 [2.095]	19	20	6-103669-9
<div>9</div> <div>10</div>	<div>8</div>	48.77 [1.920]	50.67 [1.995]	18	19	6-103669-8
<div>9</div> <div>10</div>	<div>8</div>	46.23 [1.820]	48.13 [1.895]	17	18	6-103669-7
<div>9</div> <div>10</div>	<div>8</div>	43.69 [1.720]	45.59 [1.795]	16	17	6-103669-6
<div>9</div> <div>10</div>	<div>8</div>	41.15 [1.620]	43.05 [1.695]	15	16	6-103669-5
<div>9</div> <div>10</div>	<div>8</div>	38.61 [1.520]	40.51 [1.595]	14	15	6-103669-4
<div>9</div> <div>10</div>	<div>8</div>	36.07 [1.420]	37.97 [1.495]	13	14	6-103669-3
<div>9</div> <div>10</div>	<div>8</div>	33.53 [1.320]	35.43 [1.395]	12	13	6-103669-2
<div>9</div> <div>10</div>	<div>8</div>	30.99 [1.220]	32.89 [1.295]	11	12	6-103669-1
<div>9</div> <div>10</div>	<div>8</div>	28.45 [1.120]	30.35 [1.195]	10	11	6-103669-0
<div>9</div> <div>10</div>	<div>8</div>	25.91 [1.020]	27.81 [1.095]	9	10	5-103669-9
<div>9</div> <div>10</div>	<div>8</div>	23.37 [.920]	25.27 [.995]	8	9	5-103669-8
<div>9</div> <div>10</div>	<div>8</div>	20.83 [.820]	22.73 [.895]	7	8	5-103669-7
<div>9</div> <div>10</div>	<div>8</div>	18.29 [.720]	20.19 [.795]	6	7	5-103669-6
<div>9</div> <div>10</div>	<div>8</div>	15.75 [.620]	17.65 [.695]	5	6	5-103669-5
<div>9</div> <div>10</div>	<div>8</div>	13.21 [.520]	15.11 [.595]	4	5	5-103669-4
<div>9</div> <div>10</div>	<div>8</div>	10.67 [.420]	12.57 [.495]	3	4	5-103669-3
<div>9</div> <div>10</div>	<div>8</div>	8.13 [.320]	10.03 [.395]	2	3	5-103669-2
<div>9</div> <div>10</div>	<div>8</div>	5.59 [.220]	7.49 [.295]	1	2	5-103669-1
REMARKS	PLATING	C	B	A	NO. OF POSN	PART NO.

11

OBSOLETE

<div>9</div> <div>10</div>	<div>8</div>	38.61 [1.520]	40.51 [1.595]	14	15	6-103669-4
<div>9</div> <div>10</div>	<div>8</div>	36.07 [1.420]	37.97 [1.495]	13	14	6-103669-3
<div>9</div> <div>10</div>	<div>8</div>	33.53 [1.320]	35.43 [1.395]	12	13	6-103669-2
<div>9</div> <div>10</div>	<div>8</div>	30.99 [1.220]	32.89 [1.295]	11	12	6-103669-1
<div>9</div> <div>10</div>	<div>8</div>	28.45 [1.120]	30.35 [1.195]	10	11	6-103669-0
<div>9</div> <div>10</div>	<div>8</div>	25.91 [1.020]	27.81 [1.095]	9	10	5-103669-9
<div>9</div> <div>10</div>	<div>8</div>	23.37 [.920]	25.27 [.995]	8	9	5-103669-8
<div>9</div> <div>10</div>	<div>8</div>	20.83 [.820]	22.73 [.895]	7	8	5-103669-7
<div>9</div> <div>10</div>	<div>8</div>	18.29 [.720]	20.19 [.795]	6	7	5-103669-6
<div>9</div> <div>10</div>	<div>8</div>	15.75 [.620]	17.65 [.695]	5	6	5-103669-5
<div>9</div> <div>10</div>	<div>8</div>	13.21 [.520]	15.11 [.595]	4	5	5-103669-4
<div>9</div> <div>10</div>	<div>8</div>	10.67 [.420]	12.57 [.495]	3	4	5-103669-3
<div>9</div> <div>10</div>	<div>8</div>	8.13 [.320]	10.03 [.395]	2	3	5-103669-2
<div>9</div> <div>10</div>	<div>8</div>	5.59 [.220]	7.49 [.295]	1	2	5-103669-1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
S. SHUEY

3-5-91

CHK
M. RIDER

2-14-92

APVD
M. RIDER

2-14-92

NAME

DIMENSIONS:

INCHES

0 PLC

±

—

1 PLC

±

—

2 PLC

±

0.13[.005]

3 PLC

±

—

4 PLC

±

—

ANGLES

±

—

TOLERANCES UNLESS OTHERWISE SPECIFIED:

FINISH

SEE TABLE

MATERIAL

HOUSING: LCP,
CONTACTS: BRASS

PRODUCT SPEC

108-25034

APPLICATION SPEC

114-25026

WEIGHT

—

CUSTOMER DRAWING

SCALE

4:1

SHEET

2

OF

2

REV

AC

STE

TE Connectivity

HDR ASSY, VERT, SINGLE ROW

2.54 [.100] C/L 0.64 [.025] SQ POST

WITH PLZN, AMPMODU MTE

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A1

00779

C=103669

—

4805 (1/15)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[103669-5](#)