



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	R	REVISED PER ECO-17-002209	11APR2017	RS	MM
	S	REVISED PER ECO-20-001323	17JUN2020	SM	JO


D




C



B



SECTION X-X



DETAIL Z
POST DETAIL TYP
2 POST MINIMUM

RECOMMENDED HOLE LAYOUT

A

9	7	8	6	2.595	2.520	2.400	24	25	7-103908-4
9	7	8	6	2.495	2.420	2.300	23	24	7-103908-3
9	7	8	6	2.395	2.320	2.200	22	23	7-103908-2
9	7	8	6	2.295	2.220	2.100	21	22	7-103908-1
9	7	8	6	2.195	2.120	2.000	20	21	7-103908-0
9	7	8	6	2.095	2.020	1.900	19	20	6-103908-9
9	7	8	6	1.995	1.920	1.800	18	19	6-103908-8
9	7	8	6	1.895	1.820	1.700	17	18	6-103908-7
9	7	8	6	1.795	1.720	1.600	16	17	6-103908-6
9	7	8	6	1.695	1.620	1.500	15	16	6-103908-5
9	7	8	6	1.595	1.520	1.400	14	15	6-103908-4
9	7	8	6	1.495	1.420	1.300	13	14	6-103908-3
9	7	8	6	1.395	1.320	1.200	12	13	6-103908-2
9	7	8	6	1.295	1.220	1.100	11	12	6-103908-1
9	7	8	6	1.195	1.120	1.000	10	11	6-103908-0
9	7	8	6	1.095	1.020	.900	9	10	5-103908-9
9	7	8	6	.995	.920	.800	8	9	5-103908-8
9	7	8	6	.895	.820	.700	7	8	5-103908-7
9	7	8	6	.795	.720	.600	6	7	5-103908-6
9	7	8	6	.695	.620	.500	5	6	5-103908-5
9	7	8	6	.595	.520	.400	4	5	5-103908-4
9	7	8	6	.495	.420	.300	3	4	5-103908-3
9	7	8	6	.395	.320	.200	2	3	5-103908-2
9	7	8	6	.295	.220	.100	1	2	5-103908-1
9	8	1	1	2.595	2.520	2.400	24	25	2-103908-4
9	8	1	1	2.495	2.420	2.300	23	24	2-103908-3
9	8	1	1	2.395	2.320	2.200	22	23	2-103908-2
9	8	1	1	2.295	2.220	2.100	21	22	2-103908-1
9	8	1	1	2.195	2.120	2.000	20	21	2-103908-0
9	8	1	1	2.095	2.020	1.900	19	20	1-103908-9
9	8	1	1	1.995	1.920	1.800	18	19	1-103908-8
9	8	1	1	1.895	1.820	1.700	17	18	1-103908-7
9	8	1	1	1.795	1.720	1.600	16	17	1-103908-6
9	8	1	1	1.695	1.620	1.500	15	16	1-103908-5
9	8	1	1	1.595	1.520	1.400	14	15	1-103908-4
9	8	1	1	1.495	1.420	1.300	13	14	1-103908-3
9	8	1	1	1.395	1.320	1.200	12	13	1-103908-2
9	8	1	1	1.295	1.220	1.100	11	12	1-103908-1
9	8	1	1	1.195	1.120	1.000	10	11	1-103908-0
9	8	1	1	1.095	1.020	.900	9	10	103908-9
9	8	1	1	.995	.920	.800	8	9	103908-8
9	8	1	1	.895	.820	.700	7	8	103908-7
9	8	1	1	.795	.720	.600	6	7	103908-6
9	8	1	1	.695	.620	.500	5	6	103908-5
9	8	1	1	.595	.520	.400	4	5	103908-4
9	8	1	1	.495	.420	.300	3	4	103908-3
9	8	1	1	.395	.320	.200	2	3	103908-2
9	8	1	1	.295	.220	.100	1	2	103908-1
	REMARKS	PLATING	D	C	B	A	NO. OF POSN	ASSEMBLY PART NUMBER	


D

C

103908

B

A

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H. MOLL 7-28-86		 TE Connectivity							
DIMENSIONS: INCHES		CHK PC deJONG 7-28-86									
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± -	APVD PC deJONG 7-28-86		NAME HEADER ASSY, AMPMODU MTE, VERTICAL, SINGLE ROW, .100 CL, .025 SQ POSTS WITH LATCH & RETENTIVE POSTS							
		PRODUCT SPEC —									
		APPLICATION SPEC —									
		MATERIAL HOUSING: FLAME RETARDENT LCP COLOR-BLACK CONTACTS-BRASS		FINISH		SIZE A2		CAGE CODE 00779		DRAWING NO C-103908	
SEE TABLE		CUSTOMER DRAWING				SCALE 4:1		SHEET 1 of 1		REV S	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-103908-5](#)