




RECOMMENDED HOLE LAYOUT

		1,2,39,40	1,2,39,40	3.984	3.900	39	80	2-104353-0
5	OBSOLETE	1,2,29,30	1,2,29,30	2.984	2.900	29	60	1-104353-9
		1,2,24,25	1,2,24,25	2.484	2.400	24	50	1-104353-8
		1,2,19,20	1,2,19,20	1.984	1.900	19	40	1-104353-7
		1,2,16,17	1,2,16,17	1.684	1.600	16	34	1-104353-6
		1,2,14,15	1,2,14,15	1.484	1.400	14	30	1-104353-5
		1,2,13,14	1,2,13,14	1.384	1.300	13	28	1-104353-4
5	OBSOLETE	1,2,12,13	1,2,12,13	1.284	1.200	12	26	1-104353-3
		1,2,11,12	1,2,11,12	1.184	1.100	11	24	1-104353-2
		1,2,10,11	1,2,10,11	1.084	1.000	10	22	1-104353-1
		1,2,9,10	1,2,9,10	.984	.900	9	20	1-104353-0
		1,2,8,9	1,2,8,9	.884	.800	8	18	104353-9
		1,2,7,8	1,2,7,8	.784	.700	7	16	104353-8
5	OBSOLETE	1,2,6,7	1,2,6,7	.684	.600	6	14	104353-7
		1,2,5,6	1,2,5,6	.584	.500	5	12	104353-6
		1,2,4,5	1,2,4,5	.484	.400	4	10	104353-5
		1,2,3,4	1,2,3,4	.384	.300	3	8	104353-4
		1,2,3	1,2,3	.284	.200	2	6	104353-3
		1,2	1,2	.184	.100	1	4	104353-2
5	OBSOLETE	1	1	.084	-	-	2	104353-1
		ROW N	ROW M	C	B	A	NO OF POSN	ASSEMBLY PART NUMBER
		HOLD-DOWN POST CONFIG LOCATION						

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN M. PASTAL 04FEB88		 TE Connectivity		
			CHK R. FEIDT 09FEB88				
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD R. FEIDT 09FEB88		NAME HEADER ASSEMBLY, MOD II, BREAKAWAY, RIGHT ANGLE, DOUBLE ROW, .100X.100CL .025 SQ POSTS WITH HOLD-DOWN CONFIGURATIONS	
		0 PLC ± —		PRODUCT SPEC			
		1 PLC ± —		—			
		2 PLC ± —		APPLICATION SPEC			
3 PLC ± .005		4 PLC ± —		—		SIZE A2	
ANGLES ± —		WEIGHT —		CAGE CODE 00779			
MATERIAL HOUSING: FLAME RETARDANT THERMOPLASTIC, COLOR:BLACK POSTS: COPPER ALLOY		FINISH POSTS: .000030 GOLD ON THE CONTACT AREA, .000100-.000200 MATTE TIN-LEAD ON THE SOLDER TAIL. OVER .000050 NICKEL		DRAWING NO C-104353		RESTRICTED TO —	
CUSTOMER DRAWING				SCALE 4:1		SHEET 1 of 1	REV G

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-104353-3](#)