







	35.56 [1.400]	14	37.69 [1.484]	30	6-146135-4
	33.02 [1.300]	13	35.15 [1.384]	28	6-146135-3
	30.48 [1.200]	12	32.61 [1.284]	26	6-146135-2
	27.94 [1.100]	11	30.07 [1.184]	24	6-146135-1
	25.40 [1.000]	10	27.53 [1.084]	22	6-146135-0
	22.86 [.900]	9	24.99 [.984]	20	5-146135-9
	20.32 [.800]	8	22.45 [.884]	18	5-146135-8
	17.78 [.700]	7	19.91 [.784]	16	5-146135-7
	15.24 [.600]	6	17.37 [.684]	14	5-146135-6
	12.70 [.500]	5	14.83 [.584]	12	5-146135-5
	10.16 [.400]	4	12.29 [.484]	10	5-146135-4
	7.62 [.300]	3	9.75 [.384]	8	5-146135-3
	2.54 [.100]	1	4.67 [.184]	4	5-146135-1
	15.24 [.600]	6	17.37 [.684]	14	1-146135-7
	5.08 [.200]	2	7.21 [.284]	6	1-146135-6
	35.56 [1.400]	14	37.69 [1.484]	30	1-146135-4
	33.02 [1.300]	13	35.15 [1.384]	28	1-146135-3
	30.48 [1.200]	12	32.61 [1.284]	26	1-146135-2
	27.94 [1.100]	11	30.07 [1.184]	24	1-146135-1
	25.40 [1.000]	10	27.53 [1.084]	22	1-146135-0
	22.86 [.900]	9	24.99 [.984]	20	146135-9
	20.32 [.800]	8	22.45 [.884]	18	146135-8
	17.78 [.700]	7	19.91 [.784]	16	146135-7
	15.24 [.600]	6	17.37 [.684]	14	146135-6
	12.70 [.500]	5	14.83 [.584]	12	146135-5
	10.16 [.400]	4	12.29 [.484]	10	146135-4
	7.62 [.300]	3	9.75 [.384]	8	146135-3
	5.08 [.200]	2	7.21 [.284]	6	146135-2
	2.54 [.100]	1	4.67 [.184]	4	146135-1
PLATING	C	B	A	NO. OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN. J. KNAUB JOSEP#84 CHK. G. DUBNICZKI JOSEP#94 APVD. G. DUBNICZKI JOSEP#94		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		0 PLC ± . — 1 PLC ± . — 2 PLC ± .015 [.005] 3 PLC ± . — 4 PLC ± . — ANGLES ± . — FINISH		SURFACE MOUNT HEADER ASSEMBLY, MOD II, BREAKAWAY, VERTICAL, DOUBLE ROW, .100 X.100 CL, .025 SQ. POST	
MATERIAL 		WEIGHT — SEE TABLE		SIZE CAGE CODE DRAWING NO A1 00779 C-146135	
CUSTOMER DRAWING		SCALE 8:1		SHEET 1 of 1 REV. P	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[146135-7](#)