



LOC		DIST		REVISIONS					
AD		00		P	LTR	DESCRIPTION	DATE	DWN	APVD
					H	REVISED PER ECO-14-000066	27JUN2014	NK	MM



RECOMMENDED HOLE LAYOUT

OBSOLETE	7	6	1,2,39,40	1,2,39,40	3.984	3.900	39	80	7-104354-0
	7	6	1,2,29,30	1,2,29,30	2.984	2.900	29	60	6-104354-9
	7	6	1,2,24,25	1,2,24,25	2.484	2.400	24	50	6-104354-8
	7	6	1,2,19,20	1,2,19,20	1.984	1.900	19	40	6-104354-7
	7	6	1,2,16,17	1,2,16,17	1.684	1.600	16	34	6-104354-6
	7	6	1,2,14,15	1,2,14,15	1.484	1.400	14	30	6-104354-5
	7	6	1,2,13,14	1,2,13,14	1.384	1.300	13	28	6-104354-4
	7	6	1,2,12,13	1,2,12,13	1.284	1.200	12	26	6-104354-3
	7	6	1,2,11,12	1,2,11,12	1.184	1.100	11	24	6-104354-2
	7	6	1,2,10,11	1,2,10,11	1.084	1.000	10	22	6-104354-1
	7	6	1,2,9,10	1,2,9,10	.984	.900	9	20	6-104354-0
	7	6	1,2,8,9	1,2,8,9	.884	.800	8	18	5-104354-9
	7	6	1,2,7,8	1,2,7,8	.784	.700	7	16	5-104354-8
	7	6	1,2,6,7	1,2,6,7	.684	.600	6	14	5-104354-7
7	6	1,2,5,6	1,2,5,6	.584	.500	5	12	5-104354-6	
7	6	1,2,4,5	1,2,4,5	.484	.400	4	10	5-104354-5	
7	6	1,2,3,4	1,2,3,4	.384	.300	3	8	5-104354-4	
7	6	1,2,3	1,2,3	.284	.200	2	6	5-104354-3	
7	6	1,2	1,2	.184	.100	1	4	5-104354-2	
5	5	1,2,39,40	1,2,39,40	3.984	3.900	39	80	2-104354-0	
5	5	1,2,29,30	1,2,29,30	2.984	2.900	29	60	1-104354-9	
5	5	1,2,24,25	1,2,24,25	2.484	2.400	24	50	1-104354-8	
5	5	1,2,19,20	1,2,19,20	1.984	1.900	19	40	1-104354-7	
5	5	1,2,16,17	1,2,16,17	1.684	1.600	16	34	1-104354-6	
5	5	1,2,14,15	1,2,14,15	1.484	1.400	14	30	1-104354-5	
5	5	1,2,13,14	1,2,13,14	1.384	1.300	13	28	1-104354-4	
5	5	1,2,12,13	1,2,12,13	1.284	1.200	12	26	1-104354-3	
5	5	1,2,11,12	1,2,11,12	1.184	1.100	11	24	1-104354-2	
5	5	1,2,10,11	1,2,10,11	1.084	1.000	10	22	1-104354-1	
5	5	1,2,9,10	1,2,9,10	.984	.900	9	20	1-104354-0	
5	5	1,2,8,9	1,2,8,9	.884	.800	8	18	104354-9	
5	5	1,2,7,8	1,2,7,8	.784	.700	7	16	104354-8	
5	5	1,2,6,7	1,2,6,7	.684	.600	6	14	104354-7	
5	5	1,2,5,6	1,2,5,6	.584	.500	5	12	104354-6	
5	5	1,2,4,5	1,2,4,5	.484	.400	4	10	104354-5	
5	5	1,2,3,4	1,2,3,4	.384	.300	3	8	104354-4	
5	5	1,2,3	1,2,3	.284	.200	2	6	104354-3	
5	5	1,2	1,2	.184	.100	1	4	104354-2	
5	5	1	1	.084	-	-	2	104354-1	
REMARKS	PLATING	ROW N	ROW M	C	B	A	NO OF POSN	ASSEMBLY PART NUMBER	
		HOLD-DOWN POST CONFIG LOCATION							

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG MKT	PASTAL	2-4-88			TE Connectivity	
		CHEK R.FEIDT		2-9-88				
DIMENSIONS: INCHES		TO FRANCES UNLESS OTHERWISE SPECIFIED:		APOD R FEIDT	2-9-88	NAME		
	0 P/LC ± — .1 P/LC ± — .2 P/LC ± .005 .3 P/LC ± — ANGLES ± —			PRODUCT SPEC		HEADER ASSEMBLY, MOD II, BREAKAWAY, RIGHT ANGLE, DOUBLE, ROW., 100X.100 CL,		
MATERIAL HOUSING RETARDANT THEOPHORIC COLOR BLACK	TENSILE	SEE TABLE		APPLICATION SPEC		.025 SQ POSTS WITH HOLD-DOWN CONFIGURATIONS		
POSTS COPPER ALLOY	WEIGHT	—		SIZE GAGE CODE DRAWING NO		RESTRICTED TO		—
	CUSTOMER DRAWING	A1		100779 C-104354				—
	SCALE	4:1		SHEET	1 OF 1		REV	H

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-104354-0](#)