




1. ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS
2. TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADER IS HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD
3. THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING
4. POST PLATING: 0.00254-0.00508[.000100-.000200] MATTE TIN-LEAD OVER 0.00127[.000050] NICKEL ENTIRE POST.
5. HOUSING: LCP, COLOR-BLACK.
6. POST: COPPER ALLOY.
7. POST PLATING: 0.00254-0.00508[.000100-.000200] MATTE TIN OVER 0.00127[.000050] NICKEL ENTIRE POST.
8. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

	7	101.19 [3.984]	99.06 [3.900]	39	80	9-146258-0
8	7	98.65 [3.884]	96.52 [3.800]	38	78	8-146258-9
8	7	96.11 [3.784]	93.98 [3.700]	37	76	8-146258-8
8	7	93.57 [3.684]	91.44 [3.600]	36	74	8-146258-7
8	7	91.03 [3.584]	88.90 [3.500]	35	72	8-146258-6
8	7	88.49 [3.484]	86.36 [3.400]	34	70	8-146258-5
8	7	85.95 [3.384]	83.82 [3.300]	33	68	8-146258-4
8	7	83.41 [3.284]	81.28 [3.200]	32	66	8-146258-3
8	7	80.87 [3.184]	78.74 [3.100]	31	64	8-146258-2
8	7	78.33 [3.084]	76.20 [3.000]	30	62	8-146258-1
8	7	75.79 [2.984]	73.66 [2.900]	29	60	8-146258-0
8	7	73.25 [2.884]	71.12 [2.800]	28	58	7-146258-9
8	7	70.71 [2.784]	68.58 [2.700]	27	56	7-146258-8
8	7	68.17 [2.684]	66.04 [2.600]	26	54	7-146258-7
8	7	65.63 [2.584]	63.5 [2.500]	25	52	7-146258-6
8	7	63.09 [2.484]	60.96 [2.400]	24	50	7-146258-5
8	7	60.55 [2.384]	58.42 [2.300]	23	48	7-146258-4
8	7	58.01 [2.284]	55.88 [2.200]	22	46	7-146258-3
8	7	55.47 [2.184]	53.34 [2.100]	21	44	7-146258-2
8	7	52.93 [2.084]	50.80 [2.000]	20	42	7-146258-1
8	7	50.39 [1.984]	48.26 [1.900]	19	40	7-146258-0
8	7	47.85 [1.884]	45.72 [1.800]	18	38	6-146258-9
8	7	45.31 [1.784]	43.18 [1.700]	17	36	6-146258-8
8	7	42.77 [1.684]	40.64 [1.600]	16	34	6-146258-7
8	7	40.23 [1.584]	38.10 [1.500]	15	32	6-146258-6
8	7	37.69 [1.484]	35.56 [1.400]	14	30	6-146258-5
8	7	35.15 [1.384]	33.02 [1.300]	13	28	6-146258-4
8	7	32.61 [1.284]	30.48 [1.200]	12	26	6-146258-3
8	7	30.07 [1.184]	27.94 [1.100]	11	24	6-146258-2
8	7	27.53 [1.084]	25.40 [1.000]	10	22	6-146258-1
8	7	24.99 [.984]	22.86 [.900]	9	20	6-146258-0
	7	22.45 [.884]	20.32 [.800]	8	18	5-146258-9
	7	19.91 [.784]	17.78 [.700]	7	16	5-146258-8
	7	17.37 [.684]	15.24 [.600]	6	14	5-146258-7
	7	14.83 [.584]	12.70 [.500]	5	12	5-146258-6
	7	12.29 [.484]	10.16 [.400]	4	10	5-146258-5
	7	9.75 [.384]	7.62 [.300]	3	8	5-146258-4
	7	7.21 [.284]	5.08 [.200]	2	6	5-146258-3
	7	4.67 [.184]	2.54 [.100]	1	4	5-146258-2
	7	- [-]	- [-]	0	2	5-146258-1
	PLATING	C	B	A	NO. OF POSITIONS	PART NUMBER

	$\triangle$	101.1 [3.984]	99.06 [3.900]	39	80	4-146258-0
$\triangle$	$\triangle$	98.65 [3.884]	96.52 [3.800]	38	78	3-146258-9
$\triangle$	$\triangle$	96.11 [3.784]	93.98 [3.700]	37	76	3-146258-8
$\triangle$	$\triangle$	93.57 [3.684]	91.44 [3.600]	36	74	3-146258-7
$\triangle$	$\triangle$	91.03 [3.584]	88.90 [3.500]	35	72	3-146258-6
$\triangle$	$\triangle$	88.49 [3.484]	86.36 [3.400]	34	70	3-146258-5
$\triangle$	$\triangle$	85.95 [3.384]	83.82 [3.300]	33	68	3-146258-4
$\triangle$	$\triangle$	83.41 [3.284]	81.28 [3.200]	32	66	3-146258-3
$\triangle$	$\triangle$	80.87 [3.184]	78.74 [3.100]	31	64	3-146258-2
$\triangle$	$\triangle$	78.33 [3.084]	76.20 [3.000]	30	62	3-146258-1
$\triangle$	$\triangle$	75.79 [2.984]	73.66 [2.900]	29	60	3-146258-0
$\triangle$	$\triangle$	73.25 [2.884]	71.12 [2.800]	28	58	2-146258-9
$\triangle$	$\triangle$	70.71 [2.784]	68.58 [2.700]	27	56	2-146258-8
$\triangle$	$\triangle$	68.17 [2.684]	66.04 [2.600]	26	54	2-146258-7
$\triangle$	$\triangle$	65.63 [2.584]	63.5 [2.500]	25	52	2-146258-6
$\triangle$	$\triangle$	63.09 [2.484]	60.96 [2.400]	24	50	2-146258-5
$\triangle$	$\triangle$	60.55 [2.384]	58.42 [2.300]	23	48	2-146258-4
$\triangle$	$\triangle$	58.01 [2.284]	55.88 [2.200]	22	46	2-146258-3
$\triangle$	$\triangle$	55.47 [2.184]	53.34 [2.100]	21	44	2-146258-2
$\triangle$	$\triangle$	52.93 [2.084]	50.80 [2.000]	20	42	2-146258-1
$\triangle$	$\triangle$	50.39 [1.984]	48.26 [1.900]	19	40	2-146258-0
$\triangle$	$\triangle$	47.85 [1.884]	45.72 [1.800]	18	38	1-146258-9
$\triangle$	$\triangle$	45.31 [1.784]	43.18 [1.700]	17	36	1-146258-8
$\triangle$	$\triangle$	42.77 [1.684]	40.64 [1.600]	16	34	1-146258-7
$\triangle$	$\triangle$	40.23 [1.584]	38.10 [1.500]	15	32	1-146258-6
$\triangle$	$\triangle$	37.69 [1.484]	35.56 [1.400]	14	30	1-146258-5
$\triangle$	$\triangle$	35.15 [1.384]	33.02 [1.300]	13	28	1-146258-4
$\triangle$	$\triangle$	32.61 [1.284]	30.48 [1.200]	12	26	1-146258-3
$\triangle$	$\triangle$	30.07 [1.184]	27.94 [1.100]	11	24	1-146258-2
$\triangle$	$\triangle$	27.53 [1.084]	25.40 [1.000]	10	22	1-146258-1
$\triangle$	$\triangle$	24.99 [.984]	22.86 [.900]	9	20	1-146258-0
$\triangle$	$\triangle$	22.45 [.884]	20.32 [.800]	8	18	—146258-9
$\triangle$	$\triangle$	19.91 [.784]	17.78 [.700]	7	16	—146258-8
$\triangle$	$\triangle$	17.37 [.684]	15.24 [.600]	6	14	—146258-7
$\triangle$	$\triangle$	14.83 [.584]	12.70 [.500]	5	12	—146258-6
$\triangle$	$\triangle$	12.29 [.484]	10.16 [.400]	4	10	—146258-5
$\triangle$	$\triangle$	9.75 [.384]	7.62 [.300]	3	8	—146258-4
$\triangle$	$\triangle$	7.21 [.284]	5.08 [.200]	2	6	—146258-3
$\triangle$	$\triangle$	4.67 [.184]	2.54 [.100]	1	4	—146258-2
$\triangle$	$\triangle$	- [-]	- [-]	0	2	—146258-1
	PLATING	C	B	A	NO. OF POSITIONS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG REV DATE BY CHK		19JAN05 19JAN05		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPROV DATE BY CHK		NAME	
		0 PLG ± 1 PLG ± 2 PLG ± 0.51 [02] 3 PLG ± 0.127 [005] 4 PLG ± 0.025 [001] ANGLES ± 0.02° [0.005]		PRODUCT SPEC		HEADER ASSEMBLY, MOD II, BREAKAWAY, DOUBLE ROW, HIGH TEMPERATURE	
MATERIAL		FINISH		APPLICATION SPEC		SIZE CAGE CODE DRAWING NO A1 00779 C 146258	
		SEE TABLE		WEIGHT		RESTRICTED TO	
				—		—	
CUSTOMER DRAWING				SCALE 4:1 SHEET 1 OF 1 REV J			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5-146258-1](#)