





REVISIONS					
P.	LTR.	DESCRIPTION	DATE	OWN	APVD
-	-	SEE SHEET 1	-	-	-




1438129-1
KEYING OPTION "A"




1438129-2
KEYING OPTION "B"




1438129-3
KEYING OPTION "C"



1438129-4
KEYING OPTION "D"



1438129-5
KEYING OPTION "E"



1438129-6
KEYING OPTION "F"

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN R. VESTAL 15APR2005	TE Connectivity	
DIMENSIONS: mm		CHK T. VALASEK 15APR2005		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD T. VALASEK 15APR2005	NAME 50-WAY HARNESS ASSEMBLY, PCM	
0 PLC ±.3		PRODUCT SPEC	SIZE CAGE CODE DRAWING NO	
1 PLC ±0.10		APPLICATION SPEC	A 00779 C=1438129	
2 PLC ±.		WEIGHT	RESTRICTED TO	
3 PLC ±.		CUSTOMER DRAWING	SCALE 2:1 SHEET 2 OF 10	
4 PLC ±.			REV F41	
ANGLES ±1°				
FINISH				

REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN
-		SEE SHEET 1	-	-

KEYING OPTION B

CAVITIES WITH A NUMERIC SYMBOL INDICATES CLOSED TERMINAL LOCATIONS

BLANK CAVITIES INDICATES OPEN TERMINAL HOLE LOCATIONS

TERMINAL HOLE POSITION

5S4T-14A464-M* PIN-OUT CHART

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
-

-

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC
1 PLC
2 PLC
3 PLC
4 PLC
ANGLES

±0.3
±0.10
±
±1°

-
-

DWN
R. VESTAL
T. VALASEK
APVD
T. VALASEK

15APR2005
15APR2005

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT
-

CUSTOMER DRAWING

NAME
50-WAY HARNESS ASSEMBLY, PCM

SIZE
A

CAGE CODE
100779

DRAWING NO
C=1438129

RESTRICTED TO
REV. 4

SCALE
1:1


SHEET
4

OF
10


REV.
F 41

8	7	6	5	4	3	2	1												
© 2020 TE Connectivity. All Rights Reserved.							REVISIONS												
P		LYR		DESCRIPTION										DATE		DWN		APVD	
		-		SEE SHEET 1										-		-		-	

50	49	48	47	46	45	44	43	42	41		39	38	37	36	35		33	32	31	30	28		25	24	23	22	21	20	19			15	14	13	12	11	9	8	7	6	5	4	3	1	5-1438950-8	5S4T-14A464-NA-065				
	49	48	47	46				42			39	38		36				32	31		28	27	26	25	24		22	21			17			13	12		9		7	6	5		3	2	1	5-1438950-7	5S4T-14A464-NA-064			
49	48	47	46					42			39	38	37	36	35	34				27				23	22					16	15		12	11		8	7	6	5		3	2	1	5-1438950-6	5S4T-14A464-NA-063					
50	49				45	44			40	39	38	37	36	35	34	33	32	31	30		26			23	22	21	20	19	18			14	12	11	10	9	8	7	6	5	4		2	1	4-1438950-6	5S4T-14A464-NA-062				
49	48	47	46					42			39	38	37	36			32	31		28	27	26		24	23	22	21			17			13	12		9		6	5		3	2	1	4-1438950-5	5S4T-14A464-NA-061					
50	49	48	47	46	45	44	43	42	41	40	39	38	37	36			32	31		28			24	22	21			17			13	12		9		6	5		3	2	1	4-1438950-4	5S4T-14A464-NA-060							
50	49	48		45					40	39	38	37	36	35	34	33	32	31	30		26	25		23	22	21	20	18			14	13	12	10	9	8	7	6	5	4	3	2	1	4-1438950-1	5S4T-14A464-NA-059					
50	49	48	47	46	45	44	43	42	41	39	38	37	36	35	34	33	32	31	30	28			24	23	22	21	20	19			15	14	13	12	11	9	8		6	5	4	3	2	1	3-1438950-8	5S4T-14A464-NA-058				
	49	48	47	46				42			39	38		36			32	31		28	27	26		24	22	21			17			12		9		7	6	5		3	2	1	3-1438950-7	5S4T-14A464-NA-057						
50	49			46	45	44	43	42		40	39	38	37	36	35	34	33	32	31	30	29	28	27	26		23	22		20	19	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4		2	1	3-1438950-5	5S4T-14A464-NA-056
			46	45		43	42			39	37	36	35	34		32	31	30	29	27				22	20	19		16	15							6	5		3	2	1	3-1438950-3	5S4T-14A464-NA-055							
50	49				45	44			40	39	38	37	36	35	34	33	32	31	30	28		26			22	21	20	19	18	17	16		14	13	12	10	9	8	7	6	5		3	2	1	3-1438950-1	5S4T-14A464-NA-054			
50	49			46	45	44	43	42		40	39	38	37	36	35	34	33	32	31	30	29	28	27	26		23	22		20	19	17	16	15	14	13	12	11	10	9	8	7	6	5	4		2	1	2-1438950-4	5S4T-14A464-NA-053	
50	49				45	44			40	39	38	37	36	35	34	33		31	30		26			23	22	21	20	19	18			14	13	12	10	9	8	7	6	5	4		2	1	2-1438950-1	5S4T-14A464-NA-052				
50	49								40	39	38	37	36	35	34	33	32	31	30		26			23	22	21	20	19	18			14	13	12	10	9	8	7	6	5			2	1	1-1438950-6	5S4T-14A464-NA-050				
50	49			46	45	44	43	42		40	39	38	37	36	35	34	33	32	31	30	29	28	27	26		23	22	21	20	19	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4		2	1	1-1438950-5	5S4T-14A464-NA-049
50	49	48							40	39	38	37	36	35	34	33	32	31	30		26	25		23	22	21	20	19	18			14	13	12	10	9	8	7	6	5			2	1	1-1438950-2	5S4T-14A464-NA-048				
50	49	48		46	45	44	43	42		40	39	38	37	36	35	34	33	32	31	30	29	28	27	26	25	23	22	21	20	19	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4		2	1	1-1438950-1	5S4T-14A464-NA-047
				45	44				40	38	37	36	35	34	33	32	31	30		26			22	21	20	18		14				9	8	7	6	5							1438950-3	5S4T-14A464-NA-051						
50	49	48			45				40	39	38	37	36	35		33	32	31	30		26	25		23	22	21	20	18			14	13	12	10		8			5	4	3	2	1	1438950-7	5S4T-14A464-NA-046					
50	49	48	46	44	42							37	36	34	33		31	30		26	25	24	23	22	21			16		13	12	11	10	9	8	7	6	5	4	3	2	1	1438950-5	5S4T-14A464-NA-045						
50	49	48		46		44	42					37	36		34	33		31	30		26	25	24	23	22	21			16		13	12	11	10	9	8	7	6	5	4		2	1	1438950-4	5S4T-14A464-NA-044					
50	49		46	45	44	43	42		40	38	37	36	35	34		31	30	28	27	26		23	22	21	20	19	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	1438950-3	5S4T-14A464-NA-043				
			46	45	44	43	42		40	38	37	36	35	34		31	30	28	27	26			22	21	20	18	17	16		14			9	8	7	6	5							1438950-2	5S4T-14A464-NA-042					
50	49		46	45	44	43	42		40	39	38	37	36	35	34	33		31	30	29	28	27	26		23	22	21	20	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	9-1438129-6	5S4T-14A464-NA-041		
50	49	47																																																



SECTION B-B




DETAIL E
SCALE 8:1

1. GENERAL TOLERANCE:
±0.3 ALL ONE PLACE DIMENSIONS
±0.10 ALL TWO PLACE DIMENSIONS
±1°00' ALL ANGULAR DIMENSIONS
2. DRAFT ANGLE PERMISSIBLE ONLY WITHIN DRAWING TOLERANCE.
3. SEALING SURFACE, NO WITNESS LINES OR DAMAGE PERMITTED.
4. ALL UNMARKED RADII TO BE 0.5 MAX., UNLESS OTHERWISE SPECIFIED.
5. VENT HOLE SIZE AND LOCATION IS OPTIONAL.
6. THIS AREA TO REMAIN CLEAR FOR THE HARNESS ASSEMBLY.
7. TERMINAL POSITION IDENTIFICATION.
8. MATES WITH TYCO ELECTRONICS PART NUMBERS 1438129-• &





SECTION A - A

[illegible]

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG. 15APR2005 R. VESTAL CHK. 15APR2005 T. VALASEK		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±.1 1 PLC ±0.3 2 PLC ±0.10 3 PLC ±.1 4 PLC ±.1 ANGLES ±1°		NAME 50-WAY HARNESS ASSEMBLY, PCM -	
		PRODUCT SPEC - APPLICATION SPEC -		SIZE CAGE CODE DRAWING NO A1 00779 C=1438129	
MATERIAL - -		FINISH - -		RESTRICTED TO - -	
		WEIGHT -		CUSTOMER DRAWING	
				SCALE 1:1 SHEET 9 OF 10 REF 4	

P.		REVISIONS			
P.	LTR	DESCRIPTION	DATE	DWN	APPV
-	-	SEE SHEET 1	-	-	-



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG. NO. VESTAL 15APR2005 CHK. VALASEK 15APR2005 APD. VALASEK 15APR2005		 TE Connectivity	
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ±0.3 2 PLC ±0.10 3 PLC ± 4 PLC ± ANGLES ±1°		NAME 50-WAY HARNESS ASSEMBLY, PCM PRODUCT SPEC APPLICATION SPEC	
MATERIAL - - -		FINISH - - -		SIZE A	
		WEIGHT -		CAGE CODE 00779	
		CUSTOMER DRAWING		DRAWING NO. 1438129	
				SCALE 1:1 SHEET 10 OF 10 REF 4	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1438129-7](#)