


8	7	6	5	4	3	2	1		
THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION		REVISIONS					
(C) COPYRIGHT -- By --		ALL RIGHTS RESERVED.		RP	LTR	DESCRIPTION	DATE	DWN	APVD
					--	SEE SHEET 1	--	--	--
D	OBSOLETE	6	5	101.19	99.06	39	40	9-146283-0	
			5	[3.984]	[3.900]	38	39	-8-146283-9-	
			5	[3.884]	[3.800]	37	38	-8-146283-8-	
			5	96.11	93.98	36	37	-8-146283-7-	
			5	93.57	91.44	35	36	8-146283-6	
			5	[3.684]	[3.600]	34	35	-8-146283-5-	
			5	[3.584]	[3.500]	33	34	-8-146283-4-	
			5	88.49	86.36	32	33	-8-146283-3-	
			5	85.95	83.82	31	32	-8-146283-2-	
			5	[3.384]	[3.300]	30	31	-8-146283-1-	
			5	83.41	81.28	29	30	-8-146283-0-	
			5	[3.284]	[3.200]	28	29	-7-146283-9-	
			5	80.87	78.74	27	28	-7-146283-8-	
			5	[3.184]	[3.100]	26	27	-7-146283-7-	
			5	78.33	76.20	25	26	-7-146283-6-	
			5	[3.084]	[3.000]	24	25	-7-146283-5-	
			5	75.79	73.66	23	24	-7-146283-4-	
			5	[2.984]	[2.900]	22	23	-7-146283-3-	
			5	73.25	71.12	21	22	-7-146283-2-	
			5	[2.884]	[2.800]	20	21	-7-146283-1-	
			5	70.71	68.58	19	20	-7-146283-0-	
			5	[2.784]	[2.700]	18	19	-6-146283-9-	
			5	68.17	66.04	17	18	-6-146283-8-	
			5	[2.684]	[2.600]	16	17	-6-146283-7-	
			5	65.63	63.5	15	16	-6-146283-6-	
			5	[2.584]	[2.500]	14	15	-6-146283-5-	
			5	63.09	60.96	13	14	-6-146283-4-	
			5	[2.484]	[2.400]	12	13	-6-146283-3-	
			5	60.55	58.42	11	12	-6-146283-2-	
			5	[2.384]	[2.300]	10	11	-6-146283-1-	
			5	58.01	55.88	9	10	-6-146283-0-	
			5	[2.284]	[2.200]	8	9	-5-146283-9-	
			5	55.47	53.34	7	8	-5-146283-8-	
			5	[2.184]	[2.100]	6	7	-5-146283-7-	
			5	52.93	50.80	5	6	5-146283-6	
			5	[2.084]	[2.000]	4	5	-5-146283-5-	
			5	50.39	48.26	3	4	-5-146283-4-	
			5	[1.984]	[1.900]	2	3	-5-146283-3-	
			5	47.85	45.72	1	2	-5-146283-2-	
			5	[1.884]	[1.800]	0	1	-5-146283-1-	
			5	45.31	43.18				
			5	[1.784]	[1.700]				
			5	42.77	40.64				
			5	[1.684]	[1.600]				
			5	40.23	38.10				
			5	[1.584]	[1.500]				
			5	37.69	35.56				
			5	[1.484]	[1.400]				
			5	35.15	33.02				
			5	[1.384]	[1.300]				
			5	32.61	30.48				
			5	[1.284]	[1.200]				
			5	30.07	27.94				
			5	[1.184]	[1.100]				
			5	27.53	25.40				
			5	[1.084]	[1.000]				
			5	24.99	22.86				
			5	[.984]	[.900]				
			5	22.45	20.32				
			5	[.884]	[.800]				
			5	19.91	17.78				
			5	[.784]	[.700]				
			5	17.37	15.24				
			5	[.684]	[.600]				
			5	14.83	12.70				
			5	[.584]	[.500]				
			5	12.29	10.16				
			5	[.484]	[.400]				
			5	9.75	7.62				
			5	[.384]	[.300]				
			5	7.21	5.08				
			5	[.284]	[.200]				
			5	4.67	2.54				
			5	[.184]	[.100]				
			5	2.13	-				
			5	[.084]	[]				
			PLATING	C	B	A	NO. OF POSITIONS	PART NUMBER	
A	THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN T. HOFFMAN 12JUN95		TE Connectivity		
	DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK G. DUBNICKZKI 29JUN95		NAME		
			0 PLC ± -		APVD G. DUBNICKZKI 29JUN95		PRODUCT SPEC		
			1 PLC ± -		APPLICATION SPEC		SIZE CAGE CODE DRAWING NO		
			2 PLC ± 0.51[.02]		WEIGHT -		RESTRICTED TO		
	3 PLC ± 0.127[.005]		MATERIAL 4		APVD G. DUBNICKZKI 29JUN95		100779 146283		
	4 PLC ± 0.0127[.0005]		FINISH SEE TABLE		CUSTOMER DRAWING		SCALE 1:1 SHEET 2 OF 2 REV G1		
	ANGLES ±								

4805 (1/15)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-146283-6](#)