


LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			C	REVISED PER ECO-14-000255	14JUL2014	NK	MM

- | | |
|---|---|
| 1 | THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING. |
| 2 | BREAKAWAY NOTCH ANGLE CAN BE ORIENTED TO THE RIGHT (AS SHOWN) OR TO THE LEFT |
| 3 | 0.000762 [.000030] GOLD ON CONTACT AREA,
0.00254-0.00508 [.000100-.000200] MATTE,
TIN-LEAD ON SOLDER TAIL, ALL OVER 0.00127 [.000050] NICKEL. |
| 4 | HOUSING: GLASS FILLED THERMOPLASTIC, COLOR, BLACK.
(WILL WITHSTAND VAPOR PHASE REFLOW.)
CONTACT: COPPER ALLOY. |
| 5 | 0.000762 [.000030] GOLD ON CONTACT AREA,
0.00254-0.00508 [.000100-.000200] MATTE TIN,
ON SOLDER TAIL, ALL OVER 0.00127 [.000050] NICKEL. |
| 6 | OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI |



R D.RENAUD/D.SINISI		6 OBSOLETE	3	101.19 [3.984]	99.06 [3.900]	39	40	4-146304-0
6 SUPERSEDED BY 8-146304-6	3		98.65 [3.884]	96.52 [3.800]	38	39	3-146304-9	
	3		96.11 [3.784]	93.98 [3.700]	37	38	3-146304-8	
	3		93.57 [3.684]	91.44 [3.600]	36	37	3-146304-7	
	3	91.03 [3.584]	88.90 [3.500]	35	36	3-146304-6		
5±0.38 [±0.015]	6 OBSOLETE	3	88.49 [3.484]	86.36 [3.400]	34	35	3-146304-5	
		3	85.95 [3.384]	83.82 [3.300]	33	34	3-146304-4	
		3	83.41 [3.284]	81.28 [3.200]	32	33	3-146304-3	
		3	80.87 [3.184]	78.74 [3.100]	31	32	3-146304-2	
		3	78.33 [3.084]	76.20 [3.000]	30	31	3-146304-1	
		3	75.79 [2.984]	73.66 [2.900]	29	30	3-146304-0	
		3	73.25 [2.884]	71.12 [2.800]	28	29	2-146304-9	
		3	70.71 [2.784]	68.58 [2.700]	27	28	2-146304-8	
		3	68.17 [2.684]	66.04 [2.600]	26	27	2-146304-7	
		3	65.63 [2.584]	63.5 [2.500]	25	26	2-146304-6	
		6 SUPERSEDED BY 7-146304-5	3	63.09 [2.484]	60.96 [2.400]	24	25	2-146304-5
			3	60.55 [2.384]	58.42 [2.300]	23	24	2-146304-4
3	58.01 [2.284]		55.88 [2.200]	22	23	2-146304-3		
3	55.47 [2.184]		53.34 [2.100]	21	22	2-146304-2		
3	52.93 [2.084]		50.80 [2.000]	20	21	2-146304-1		
3	50.39 [1.984]		48.26 [1.900]	19	20	2-146304-0		
3	47.85 [1.884]		45.72 [1.800]	18	19	1-146304-9		
3	45.31 [1.784]		43.18 [1.700]	17	18	1-146304-8		
3	42.77 [1.684]		40.64 [1.600]	16	17	1-146304-7		
3	40.23 [1.584]		38.10 [1.500]	15	16	1-146304-6		
6 SUPERSEDED BY 6-146304-2	3		37.69 [1.484]	35.56 [1.400]	14	15	1-146304-5	
	3		35.15 [1.384]	33.02 [1.300]	13	14	1-146304-4	
	3	32.61 [1.284]	30.48 [1.200]	12	13	1-146304-3		
	3	30.07 [1.184]	27.94 [1.100]	11	12	1-146304-2		
	6 OBSOLETE	3	27.53 [1.084]	25.40 [1.000]	10	11	1-146304-1	
	6 SUPERSEDED BY 5-146304-9	3	24.99 [.984]	22.86 [.900]	9	10	1-146304-0	
		3	22.45 [.884]	20.32 [.800]	8	9	146304-9	
	6 OBSOLETE	3	19.91 [.784]	17.78 [.700]	7	8	146304-8	
		3	17.37 [.684]	15.24 [.600]	6	7	146304-7	
	6 OBSOLETE	3	14.83 [.584]	12.70 [.500]	5	6	146304-6	
		3	12.29 [.484]	10.16 [.400]	4	5	146304-5	
	6 SUPERSEDED BY 5-146304-3	3	9.75 [.384]	7.62 [.300]	3	4	146304-4	
3		7.21 [.284]	5.08 [.200]	2	3	146304-3		
6 OBSOLETE	3	4.67 [.184]	2.54 [.100]	1	2	146304-2		
	3	2.13 [.084]	-	0	1	146304-1		
			PLATING	C	B	A	NO. OF POSITIONS	PART NUMBER

[illegible]

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[6-146304-0](#)