

LOC		DIST		REVISIONS					
HJ		-		P	LTR	DESCRIPTION	DATE	DWN	APVD
				B14		ECR-12-021486 (Marking C to Q)	20DEC2012	UKo	JB
				C		ECR-13-014508	13OCT2015	UKo	AK
				C1		ECR-14-007162	21SET2017	AP	AK
				C2		ECR-18-017686 (Add prod. site; PN List update)	07MAY2019	HC	LS

Order Number - ABCCCC

Portugal made:

A - Packing day

B - Shift (1=day, 2=night)

C - Lot number (sequential)

Austria Made:

A - Line (1...Line1)

B - Day (1...7, Monday=1, Tuesday=2)

C - Time(hhmm)

Other country made:

A - Year (first digit)

B - Year (second digit)

C - Lot number (sequential)

Mark 2

Mark 1

H Swiss made (until 2013)

PT Portugal made

Q China made (until 2016)

C China made (until 2012)

AT Austria made

Date code (YYWW)

Relay-Typ	Mark 1)	Mark 2)	PN (GR)	PN (JR)	PN (TS)	PN (KS/NS)
IM00..	00	1.5	3-1462037-7		3-1462037-5	
IM00NS	00N	1.5				1-1462038-0*
IM01..	01	3	1462037-1	4-1462037-0	1462037-4	
IM01B..	01B	3	4-1462039-5			
IM01C ..	01C	3	1462038-4			
IM01NS	01N	3				1-1462038-1
IM01N..L	01N	3				4-1462039-3
IM01P	01P	3	9-1462037-3			
IM02..	02	4.5	1462037-9	1-1462037-1	1-1462037-3	6-1462039-4
IM02..	02	4.5	8-1462039-1			
IM02..L	02	4.5	2-1462039-3			
IM02C ..	02C	4.5	1462038-1			
IM02D ..	02D	4.5	9-1462038-8			
IM02H..	02H	4.5	1-1462039-1			
IM02I..	02I	4.5	1462047-9	1462047-8		
IM02NS	02N	4.5				1-1462038-2

*obsolete

DRAWING ALIAS: IM0C-DOK17

DIMENSIONS:		DWN		MATERIAL		FINISH	
mm		HD 9121	21FEB2003	-		-	
TOLERANCES UNLESS OTHERWISE SPECIFIED: DIN 7168-m		CHK	21FEB2003	TE Connectivity			
		HD 9121	21FEB2003				
		APVD	21FEB2003				
		HD 9121	21FEB2003				
0 PLC ±-		PRODUCT SPEC		NAME IM-Relay Marking			
1 PLC ±-		-					
2 PLC ±-		APPLICATION SPEC					
3 PLC ±-		-		SIZE		CAGE CODE	
4 PLC ±-		WEIGHT		DRAWING NO		RESTRICTED TO	
ANGLES ±-		-		A 4		00779	
		CUSTOMER DRAWING		SCALE		SHEET	
		10:1		1 OF 6			
				REV		C 2	

2000

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

THIS DRAWING IS UNPUBLISHED.

COPYRIGHT 2000

LOC		DIST		REVISIONS						
HJ		-		P	LTR	DESCRIPTION	DATE	DWN	APVD	
					-	SEE SHEET 1	-	-	-	
Relay-Typ	Mark 1)	Mark 2)	PN (GR)	PN (JR)	PN (TS)	PN (KS/NS)				
IM02NS..L	02N	4.5				2-1462039-4				
IM02PNS	02P	4.5				5-1462039-8				
IM03..	03	5	1-1462037-4	1-1462037-6	1-1462037-8					
IM03..L	03	5	2-1462039-5							
IM03..X	03	5	8-1462039-6							
IM03C..	03C	5	1462038-2		4-1462039-7					
IM03D..	03D	5	9-1462038-9	3-1462039-3	8-1462039-3					
IM03I..	03I	5		1472047-6						
IM03NS	03N	5				1-1462038-3				
IM03P..	03P	5	5-1462039-5							
IM03PNS	03P	5				5-1462039-9				
IM04..	04	6	4-1462037-2	4-1462037-4	4-1462037-1					
IM04B..	04B	6	6-1462039-5							
IM04NS	04N	6				1-1462038-4				
IM05..	05	9	3-1462037-4	4-1462037-5	2-1462037-2					
IM05B..	05B	9	5-1462039-3							
IM05C..	05C	9	1462038-3							
IM05D..	05D	9	1-1462039-7							
IM05NS	05N	9				1-1462038-5				
IM06..	06	12	2-1462037-3	4-1462037-6	2-1462037-7					
IM06C..	06C	12	9-1462037-9	3-1462039-4	4-1462037-9					
IM06D..	06D	12	1-1462039-8	7-1462039-0	3-1462039-8					
IM06NS	06N	12				1-1462038-6				
IM06P..	06P	12	5-1462039-6							
IM06PNS	06P	12				6-1462039-0				
IM07..	07	24	4-1462037-7	4-1462037-8	3-1462037-0					
2000 ALL RIGHTS RESERVED. THIS DRAWING IS UNPUBLISHED. *obsolete										
DIMENSIONS: mm			DWN HD 9121 21FEB2003		MATERIAL -		DRAWING ALIAS: IM0C-DOK17			
TOLERANCES UNLESS OTHERWISE SPECIFIED: DIN 7168-m			CHK HD 9121 21FEB2003		TE Connectivity					
0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±-			APVD HD 9121 21FEB2003							
PRODUCT SPEC -			NAME IM-Relay Marking							
APPLICATION SPEC -			SIZE A 4							
WEIGHT -			CAGE CODE 00779		DRAWING NO C-1462037-1		RESTRICTED TO -			
			CUSTOMER DRAWING				SCALE 10:1		SHEET 2 OF 6	
							REV C 2			

LOC		DIST		REVISIONS					
HJ		-		P	LTR	DESCRIPTION	DATE	DWN	APVD
					-	SEE SHEET 1	-	-	-
Relay-Typ	Mark 1)	Mark 2)	PN (GR)	PN (JR)	PN (TS)	PN (KS/NS)			
IM07C..	07C	24	1462039-2		1462039-1				
IM07D..	07D	24		7-1462039-4	7-1462039-2				
IM07NS	07N	24				1-1462038-7			
IM08I..	08I	2.4			1462047-3				
IM11..	11	3	9-1462038-5						
IM12..	12	4.5	1462039-3						
IM13..	13	5	1462039-4						
IM15..	15	9	8-1462039-5						
IM16..	16	12	1462039-5						
IM17..	17	24	1462039-6		4-1462039-6				
IM21..	21	3	2-1462039-6		1-1462039-5				
IM22..	22	4.5	2-1462039-7		2-1462039-8	8-1462039-9			
IM23..	23	5	2-1462039-9		3-1462039-0	6-1462039-7			
IM25..	25	9	3-1462039-5						
IM26..	26	12	3-1462039-1		3-1462039-2				
IM40..	40	1.5	5-1462037-1						
IM40D..	40D	1.5	8-1462039-4						
IM40NS	40N	1.5				1-1462038-8			
IM41..	41	3	5-1462037-4	5-1462037-5	5-1462037-3				
IM41C..	41C	3	4-1462039-2						
IM41D..	41D	3	6-1462039-8						
IM41NS	41N	3				1-1462038-9			
IM42..	42	4.5	3-1462037-1	5-1462037-7	5-1462037-6				
IM42C..	42C	4.5	4-1462039-1						
IM42D..	42D	4.5	1-1462039-9						
*obsolete									
DIMENSIONS: mm				DWN HD 9121 21FEB2003		MATERIAL -		DRAWING ALIAS: IM0C-DOK17	
TOLERANCES UNLESS OTHERWISE SPECIFIED: DIN 7168-m 0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±-				CHK HD 9121 21FEB2003		FINISH -			
APVD HD 9121 21FEB2003				TE Connectivity					
PRODUCT SPEC -				NAME IM-Relay Marking					
APPLICATION SPEC -				SIZE A 4		CAGE CODE 00779		DRAWING NO C-1462037-1	
WEIGHT -				RESTRICTED TO -		SCALE 10:1			
CUSTOMER DRAWING				SHEET 3 OF 6		REV C 2			


2000

RELEASED FOR PUBLICATION

THIS DRAWING IS UNPUBLISHED.

ALL RIGHTS RESERVED.

COPYRIGHT 2000




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
HJ	-		-	SEE SHEET 1	-	-	-

Relay-Typ	Mark 1)	Mark 2)	PN (GR)	PN (JR)	PN (TS)	PN (KS/NS)
IM42DNS	42D	4.5				1-1462039-6
IM42NS	42N	4.5				2-1462038-0
IM42P..	42P	4.5	5-1462039-7			
IM42PNS	42P	4.5				7-1462039-8
IM43..	43	5	5-1462037-9	6-1462037-0	5-1462037-8	
IM43C..	43C	5	9-1462038-7			
IM43NS	43N	5				2-1462038-1
IM44..	44	6	6-1462037-2	6-1462037-3	6-1462037-1	
IM44NS	44N	6				2-1462038-2
IM45..	45	9	6-1462037-4	6-1462037-5	3-1462037-2	
IM45I..	45I	9	1462047-5			
IM45NS	45	9				2-1462038-3
IM46..	46	12	6-1462037-7	6-1462037-8	6-1462037-6	
IM46C..	46C	12	8-1462039-0			
IM46NS	46N	12				2-1462038-4
IM46PNS	46P	12				6-1462039-1
IM47..	47	24	7-1462037-0		6-1462037-9	
IM47D..	47D	24		7-1462039-5		
IM47NS	47N	24				2-1462038-5
IM48..	48	2.4	1462039-8			
IM48D..	48D	2.4	1462039-9			
IM48C..	48C	2.4	9-1462039-0			
IM48I..	48I	2.4	1462047-1			
IM49I..	49I	2	1462047-4			

*obsolete

DRAWING ALIAS: IMOC-DOK17

DIMENSIONS:		DWN HD 9121	21FEB2003	MATERIAL -		FINISH -							
mm		CHK HD 9121	21FEB2003	TE Connectivity									
TOLERANCES UNLESS OTHERWISE SPECIFIED: DIN 7168-m		APVD HD 9121	21FEB2003										
		PRODUCT SPEC		NAME IM-Relay Marking									
		APPLICATION SPEC											
		-				SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO				
		0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±-		WEIGHT -		A 4	00779	Ⓒ- 1462037-1	-				
		CUSTOMER DRAWING				SCALE	10:1	SHEET	4	OF	6	REV	C 2

LOC		DIST		REVISIONS					
HJ		-		P	LTR	DESCRIPTION	DATE	DWN	APVD
					-	SEE SHEET 1	-	-	-
Relay-Typ	Mark 1)	Mark 2)	PN (GR)	PN (JR)	PN (TS)	PN (KS/NS)			
IM61..	61	3	7-1462039-7						
IM68..	68	2.4	8-1462039-2						
IMB01C ..	B01C	3	1462041-1		1462041-4				
IMB02C ..	B02C	4.5	1462041-2						
IMB03C ..	B03C	5	1462041-7						
IMB03C ..E	B03C	5	1-1462041-8						
IMB04C ..	B04C	6	1462041-9		1-1462041-1				
IMB05C ..	B05C	9	1-1462041-0		1-1462041-2				
IMB06C ..	B06C	12	1462041-3		1462041-6				
IMB07C ..	B07C	24	1-1462041-3		1-1462041-4				
IMB32B..	B32B	4.5	2-1462041-0						
IMB33B..	B33B	5	1-1462041-9						
IMB41C ..	B41C	3	1-1462041-7						
IMB42C ..	B42C	4.5	1-1462041-6		1-1462041-5				
THIS DRAWING IS UNPUBLISHED. 2000 RELEASED FOR PUBLICATION ALL RIGHTS RESERVED. © COPYRIGHT 2000 *obsolete DRAWING ALIAS: IM0C-DOK17									
DIMENSIONS:		DWN		21FEB2003		MATERIAL		FINISH	
mm		HD 9121				-		-	
TOLERANCES UNLESS OTHERWISE SPECIFIED: DIN 7168-m		CHK		21FEB2003		 TE Connectivity			
		HD 9121							
		APVD		21FEB2003					
		HD 9121							
0 PLC ±-		PRODUCT SPEC				NAME			
1 PLC ±-		-							
2 PLC ±-		APPLICATION SPEC				IM-Relay Marking			
3 PLC ±-		-							
4 PLC ±-						SIZE			
ANGLES ±-									
		WEIGHT		-		CAGE CODE		DRAWING NO	
						A 4		00779	
						C=		1462037-1	
								RESTRICTED TO	
								-	
						SCALE		10:1	
						SHEET		5 OF 6	
						REV		C 2	

LOC		DIST		REVISIONS					
HJ		-		P	LTR	DESCRIPTION	DATE	DWN	APVD
					-	SEE SHEET 1	-	-	-
Relay-Typ	Mark 1)	Mark 2)	PN (GR)	PN (JR)	PN (TS)	PN (KS/NS)			
IMC01..	C01	3	1462042-1		1462042-4				
IMC02..	C02	4.5	1462042-2		1462042-5				
IMC03..	C03	5	1462042-8		1462042-7				
IMC06..	C06	12	1462042-3		1462042-6				
IMC07..	C07	24	1-1462042-1		1-1462042-2				
IMC02C..	C02C	4.5	1-1462042-0						
IMC03C..	C03C	5	1-1462042-5						
IMC06C..	C06C	12	1462042-9		1-1462042-4				
IMC41C..	C41C	3			1-1462042-3				
IME01..	E01	3	1462043-1		1462043-5				
IME02..	E02	4.5	1462043-2		1462043-6				
IME03..	E03	5	1462043-3		1462043-7				
IME06..	E06	12	1462043-4		1462043-8				
IMF61..	F61	3	1462048-3						
IMF68..	F68	2.4	1-1462048-0						
THIS DRAWING IS UNPUBLISHED. 2000 RELEASED FOR PUBLICATION ALL RIGHTS RESERVED. © COPYRIGHT 2000 *obsolete DRAWING ALIAS: IM0C-DOK17									
DIMENSIONS:		DWN HD 9121 21FEB2003		MATERIAL		FINISH			
mm		CHK HD 9121 21FEB2003		-		-			
TOLERANCES UNLESS OTHERWISE SPECIFIED: DIN 7168-m		APVD HD 9121 21FEB2003		 TE Connectivity					
0 PLC ±-		PRODUCT SPEC							
1 PLC ±-		-							
2 PLC ±-		APPLICATION SPEC		NAME					
3 PLC ±-		-		IM-Relay Marking					
4 PLC ±-				SIZE	CAGE CODE	DRAWING NO		RESTRICTED TO	
ANGLES ±-		WEIGHT -		A 4	00779	C- 1462037-1		-	
CUSTOMER DRAWING				SCALE	10:1	SHEET	6	OF	6
						REV		C 2	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5-1462039-7](#)