

LOC		DIST		REVISIONS					
HJ		-		P	LTR	DESCRIPTION	DATE	DWN	APVD
				B14		ECR-12-021486 (Marking C to Q)	20DEC2012	UKo	JB
				C		ECR-13-014508	13OCT2015	UKo	AK
				C1		ECR-14-007162	21SET2017	AP	AK
				C2		ECR-18-017686 (Add prod. site; PN List update)	07MAY2019	HC	LS

Order Number - ABCCCC

Portugal made:

A - Packing day

B - Shift (1=day, 2=night)

C - Lot number (sequential)

Austria Made:

A - Line (1...Line1)

B - Day (1...7, Monday=1, Tuesday=2)

C - Time(hhmm)

Other country made:

A - Year (first digit)

B - Year (second digit)

C - Lot number (sequential)

H Swiss made (until 2013)

PT Portugal made

Q China made (until 2016)

C China made (until 2012)

AT Austria made

Date code (YYWW)

Relay-Typ	Mark 1)	Mark 2)	PN (GR)	PN (JR)	PN (TS)	PN (KS/NS)
IM00..	00	1.5	3-1462037-7		3-1462037-5	
IM00NS	00N	1.5				1-1462038-0*
IM01..	01	3	1462037-1	4-1462037-0	1462037-4	
IM01B..	01B	3	4-1462039-5			
IM01C ..	01C	3	1462038-4			
IM01NS	01N	3				1-1462038-1
IM01N..L	01N	3				4-1462039-3
IM01P	01P	3	9-1462037-3			
IM02..	02	4.5	1462037-9	1-1462037-1	1-1462037-3	6-1462039-4
IM02..	02	4.5	8-1462039-1			
IM02..L	02	4.5	2-1462039-3			
IM02C ..	02C	4.5	1462038-1			
IM02D ..	02D	4.5	9-1462038-8			
IM02H..	02H	4.5	1-1462039-1			
IM02I..	02I	4.5	1462047-9	1462047-8		
IM02NS	02N	4.5				1-1462038-2

*obsolete

DRAWING ALIAS: IM0C-DOK17

DIMENSIONS:		DWN		MATERIAL		FINISH	
mm		HD 9121	21FEB2003	-		-	
TOLERANCES UNLESS OTHERWISE SPECIFIED: DIN 7168-m		CHK	21FEB2003	TE Connectivity			
		HD 9121					
		APVD	21FEB2003				
		HD 9121					
PRODUCT SPEC		-		NAME IM-Relay Marking			
APPLICATION SPEC		-					
WEIGHT		-					
0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±-		-		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
		-		A 4	00779	C- 1462037-1	-
CUSTOMER DRAWING				SCALE	10:1	SHEET	1 OF 6
				REV C 2			


2000

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

THIS DRAWING IS UNPUBLISHED.

COPYRIGHT 2000

LOC		DIST		REVISIONS					
HJ		-		P	LTR	DESCRIPTION	DATE	DWN	APVD
					-	SEE SHEET 1	-	-	-
Relay-Typ	Mark 1)	Mark 2)	PN (GR)	PN (JR)	PN (TS)	PN (KS/NS)			
IM02NS..L	02N	4.5				2-1462039-4			
IM02PNS	02P	4.5				5-1462039-8			
IM03..	03	5	1-1462037-4	1-1462037-6	1-1462037-8				
IM03..L	03	5	2-1462039-5						
IM03..X	03	5	8-1462039-6						
IM03C..	03C	5	1462038-2		4-1462039-7				
IM03D..	03D	5	9-1462038-9	3-1462039-3	8-1462039-3				
IM03I..	03I	5		1472047-6					
IM03NS	03N	5				1-1462038-3			
IM03P..	03P	5	5-1462039-5						
IM03PNS	03P	5				5-1462039-9			
IM04..	04	6	4-1462037-2	4-1462037-4	4-1462037-1				
IM04B..	04B	6	6-1462039-5						
IM04NS	04N	6				1-1462038-4			
IM05..	05	9	3-1462037-4	4-1462037-5	2-1462037-2				
IM05B..	05B	9	5-1462039-3						
IM05C..	05C	9	1462038-3						
IM05D..	05D	9	1-1462039-7						
IM05NS	05N	9				1-1462038-5			
IM06..	06	12	2-1462037-3	4-1462037-6	2-1462037-7				
IM06C..	06C	12	9-1462037-9	3-1462039-4	4-1462037-9				
IM06D..	06D	12	1-1462039-8	7-1462039-0	3-1462039-8				
IM06NS	06N	12				1-1462038-6			
IM06P..	06P	12	5-1462039-6						
IM06PNS	06P	12				6-1462039-0			
IM07..	07	24	4-1462037-7	4-1462037-8	3-1462037-0				
*obsolete DRAWING ALIAS: IM0C-DOK17									
DIMENSIONS:		DWN	21FEB2003	MATERIAL		FINISH			
mm		HD 9121		-		-			
TOLERANCES UNLESS OTHERWISE SPECIFIED: DIN 7168-m		CHK	21FEB2003	 TE Connectivity					
		HD 9121							
		APVD	21FEB2003						
		HD 9121							
0 PLC ±-		PRODUCT SPEC		NAME IM-Relay Marking					
1 PLC ±-		-							
2 PLC ±-		APPLICATION SPEC							
3 PLC ±-		-		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
4 PLC ±-		-		A 4	00779	©- 1462037-1	-		
ANGLES ±-		WEIGHT		-					
		CUSTOMER DRAWING							
				SCALE	10:1	SHEET	2	OF	6
						REV	C 2		

2000

RELEASED FOR PUBLICATION

THIS DRAWING IS UNPUBLISHED.

ALL RIGHTS RESERVED.

COPYRIGHT 2000

LOC		DIST		REVISIONS						
HJ		-		P	LTR	DESCRIPTION	DATE	DWN	APVD	
					-	SEE SHEET 1	-	-	-	
Relay-Typ	Mark 1)	Mark 2)	PN (GR)	PN (JR)	PN (TS)	PN (KS/NS)				
IM07C..	07C	24	1462039-2		1462039-1					
IM07D..	07D	24		7-1462039-4	7-1462039-2					
IM07NS	07N	24				1-1462038-7				
IM08I..	08I	2.4			1462047-3					
IM11..	11	3	9-1462038-5							
IM12..	12	4.5	1462039-3							
IM13..	13	5	1462039-4							
IM15..	15	9	8-1462039-5							
IM16..	16	12	1462039-5							
IM17..	17	24	1462039-6		4-1462039-6					
IM21..	21	3	2-1462039-6		1-1462039-5					
IM22..	22	4.5	2-1462039-7		2-1462039-8	8-1462039-9				
IM23..	23	5	2-1462039-9		3-1462039-0	6-1462039-7				
IM25..	25	9	3-1462039-5							
IM26..	26	12	3-1462039-1		3-1462039-2					
IM40..	40	1.5	5-1462037-1							
IM40D..	40D	1.5	8-1462039-4							
IM40NS	40N	1.5				1-1462038-8				
IM41..	41	3	5-1462037-4	5-1462037-5	5-1462037-3					
IM41C..	41C	3	4-1462039-2							
IM41D..	41D	3	6-1462039-8							
IM41NS	41N	3				1-1462038-9				
IM42..	42	4.5	3-1462037-1	5-1462037-7	5-1462037-6					
IM42C..	42C	4.5	4-1462039-1							
IM42D..	42D	4.5	1-1462039-9							
*obsolete										
DIMENSIONS: mm TOLERANCES UNLESS OTHERWISE SPECIFIED: DIN 7168-m 0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±-				DWN HD 9121 21FEB2003 CHK HD 9121 21FEB2003 APVD HD 9121 21FEB2003 PRODUCT SPEC - APPLICATION SPEC - WEIGHT -		MATERIAL - FINISH - NAME IM-Relay Marking SIZE A 4 CAGE CODE 00779 DRAWING NO C-1462037-1		DRAWING ALIAS: IM0C-DOK17		RESTRICTED TO -
CUSTOMER DRAWING				SCALE 10:1		SHEET 3 OF 6		REV C 2		


2000

RELEASED FOR PUBLICATION

THIS DRAWING IS UNPUBLISHED.

ALL RIGHTS RESERVED.

COPYRIGHT 2000





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
HJ	-		-	SEE SHEET 1	-	-	-


Relay-Typ	Mark 1)	Mark 2)	PN (GR)	PN (JR)	PN (TS)	PN (KS/NS)
IM42DNS	42D	4.5				1-1462039-6
IM42NS	42N	4.5				2-1462038-0
IM42P..	42P	4.5	5-1462039-7			
IM42PNS	42P	4.5				7-1462039-8
IM43..	43	5	5-1462037-9	6-1462037-0	5-1462037-8	
IM43C..	43C	5	9-1462038-7			
IM43NS	43N	5				2-1462038-1
IM44..	44	6	6-1462037-2	6-1462037-3	6-1462037-1	
IM44NS	44N	6				2-1462038-2
IM45..	45	9	6-1462037-4	6-1462037-5	3-1462037-2	
IM45I..	45I	9	1462047-5			
IM45NS	45	9				2-1462038-3
IM46..	46	12	6-1462037-7	6-1462037-8	6-1462037-6	
IM46C..	46C	12	8-1462039-0			
IM46NS	46N	12				2-1462038-4
IM46PNS	46P	12				6-1462039-1
IM47..	47	24	7-1462037-0		6-1462037-9	
IM47D..	47D	24		7-1462039-5		
IM47NS	47N	24				2-1462038-5
IM48..	48	2.4	1462039-8			
IM48D..	48D	2.4	1462039-9			
IM48C..	48C	2.4	9-1462039-0			
IM48I..	48I	2.4	1462047-1			
IM49I..	49I	2	1462047-4			

*obsolete

DRAWING ALIAS: IMOC-DOK17

DIMENSIONS:		DWN	HD 9121	21FEB2003	MATERIAL		-	FINISH		-			
mm		CHK	HD 9121	21FEB2003	TE Connectivity								
TOLERANCES UNLESS OTHERWISE SPECIFIED: DIN 7168-m		APVD	HD 9121	21FEB2003									
		PRODUCT SPEC		NAME IM-Relay Marking									
		APPLICATION SPEC											
		WEIGHT					SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO			
0 PLC ±-		-		A 4	00779	G- 1462037-1		-					
1 PLC ±-													
2 PLC ±-													
3 PLC ±-													
4 PLC ±-													
ANGLES ±-													
		CUSTOMER DRAWING			SCALE		10:1	SHEET	4	OF	6	REV	C 2

2000	RELEASED FOR PUBLICATION	ALL RIGHTS RESERVED.	COPYRIGHT 2000	THIS DRAWING IS UNPUBLISHED.	LOC	DIST	REVISIONS					
					HJ	-	P	LTR	DESCRIPTION	DATE	DWN	APVD
							-		SEE SHEET 1	-	-	-
Relay-Typ	Mark 1)	Mark 2)	PN (GR)	PN (JR)	PN (TS)	PN (KS/NS)						
IM61..	61	3	7-1462039-7									
IM68..	68	2.4	8-1462039-2									
IMB01C ..	B01C	3	1462041-1		1462041-4							
IMB02C ..	B02C	4.5	1462041-2									
IMB03C ..	B03C	5	1462041-7									
IMB03C ..E	B03C	5	1-1462041-8									
IMB04C ..	B04C	6	1462041-9		1-1462041-1							
IMB05C ..	B05C	9	1-1462041-0		1-1462041-2							
IMB06C ..	B06C	12	1462041-3		1462041-6							
IMB07C ..	B07C	24	1-1462041-3		1-1462041-4							
IMB32B..	B32B	4.5	2-1462041-0									
IMB33B..	B33B	5	1-1462041-9									
IMB41C ..	B41C	3	1-1462041-7									
IMB42C ..	B42C	4.5	1-1462041-6		1-1462041-5							
*obsolete												
DIMENSIONS:		DWN	21FEB2003	MATERIAL		DRAWING ALIAS:						
mm		HD 9121		-		IM0C-DOK17						
TOLERANCES UNLESS OTHERWISE SPECIFIED: DIN 7168-m		CHK	21FEB2003	 TE Connectivity								
		HD 9121										
		APVD	21FEB2003									
		HD 9121										
0 PLC ±-		PRODUCT SPEC		NAME		IM-Relay Marking						
1 PLC ±-		-										
2 PLC ±-		APPLICATION SPEC										
3 PLC ±-		-		SIZE		CAGE CODE		DRAWING NO				
4 PLC ±-		WEIGHT		A 4		00779		C- 1462037-1				
ANGLES ±-		-		CUSTOMER DRAWING		SCALE		RESTRICTED TO				
						10:1		SHEET 5 OF 6				
								REV C 2				

2000 RELEASED FOR PUBLICATION ALL RIGHTS RESERVED. THIS DRAWING IS UNPUBLISHED. COPYRIGHT 2000	LOC HJ	DIST -	REVISIONS					
			P	LTR	DESCRIPTION	DATE	DWN	APVD
			-		SEE SHEET 1	-	-	-
	Relay-Typ	Mark 1)	Mark 2)	PN (GR)	PN (JR)	PN (TS)	PN (KS/NS)	
	IMC01..	C01	3	1462042-1		1462042-4		
	IMC02..	C02	4.5	1462042-2		1462042-5		
	IMC03..	C03	5	1462042-8		1462042-7		
	IMC06..	C06	12	1462042-3		1462042-6		
	IMC07..	C07	24	1-1462042-1		1-1462042-2		
	IMC02C..	C02C	4.5	1-1462042-0				
	IMC03C..	C03C	5	1-1462042-5				
	IMC06C..	C06C	12	1462042-9		1-1462042-4		
	IMC41C..	C41C	3			1-1462042-3		
	IME01..	E01	3	1462043-1		1462043-5		
	IME02..	E02	4.5	1462043-2		1462043-6		
	IME03..	E03	5	1462043-3		1462043-7		
	IME06..	E06	12	1462043-4		1462043-8		
	IMF61..	F61	3	1462048-3				
	IMF68..	F68	2.4	1-1462048-0				
	*obsolete							
DIMENSIONS:		DWN HD 9121	21FEB2003	MATERIAL		DRAWING ALIAS: IM0C-DOK17		
mm		CHK HD 9121	21FEB2003	FINISH		-		
TOLERANCES UNLESS OTHERWISE SPECIFIED: DIN 7168-m		APVD HD 9121	21FEB2003	 TE Connectivity				
0 PLC ±-		PRODUCT SPEC						
1 PLC ±-								
2 PLC ±-		APPLICATION SPEC		NAME IM-Relay Marking				
3 PLC ±-								
4 PLC ±-				SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
ANGLES ±-		WEIGHT	-	A 4	00779	C- 1462037-1	-	
		CUSTOMER DRAWING		SCALE	10:1	SHEET	6 OF 6	
						REV	C 2	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[4-1462039-6](#)