

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	G	REVISED PER ECO-20-001327	05JUN2020	SB	JO

D

D

C






C

B

B

A

A



- 1 .00038[.000015] GOLD IN THE CONTACT AREA, .00254[.000100] MATTE TIN-LEAD ON REMAINDER OF CONTACT, ALL OVER .00127[.000050] NICKEL.
- 2 POINT OF MEASUREMENT FOR PLATING THICKNESS.
- 3 THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND THE HOUSING.
- 4 ON ASSEMBLIES WITH FOUR OR MORE POSITIONS, TWO POLARIZATION SLOTS. ON ASSEMBLIES WITH TWO OR THREE POSITIONS, ONE POLARIZATION SLOT.
- 5 HOUSING: FLAME RETARDANT LCP, COLOR-BLACK. CONTACTS: BRASS.
- 6 SELECT POST TAILS FORMED TO PROVIDE CONNECTOR HOLD-DOWN UNTIL SOLDERED. CONFIGURATION ACCEPTS 0.69-2.03 [.027-.080] THICK PRINTED CIRCUIT BOARD.
- 7 PRELIMINARY PART-NOT RELEASED FOR PRODUCTION.
- 8 .00038[.000015] GOLD IN THE CONTACT AREA, .00254[.000100] MATTE TIN ON REMAINDER OF CONTACT, ALL OVER .00127[.000050] NICKEL.
- 9 HIGH TEMPERATURE CONFIGURATION.
- 10 STANDOFFS NOT PRESENT ON UNDERSIDE OF ASSEMBLY.
- 11 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 12 0.25 [.010] RECESS PERMISSIBLE IN THIS AREA FOR MOLD SHUT OFF

11	7	OBSOLETE	9	10	8	5,7,9,11,14,17	48.77 [1.920]	50.67 [1.995]	18	19	5-147321-4
11		OBSOLETE	9	10	8	3,6,9,12,15	43.69 [1.720]	45.59 [1.795]	16	17	5-147321-3
11	7	OBSOLETE	9	10	8	2,3,4,5,6	18.29 [.720]	20.19 [.795]	6	7	5-147321-2
11		OBSOLETE	9	10	8	4,5	25.91 [1.020]	27.81 [1.095]	9	10	5-147321-1
	7		9		1	19	51.31 [2.020]	53.21 [2.095]	19	20	147321-6
	7		9		1	2	41.15 [1.620]	43.05 [1.695]	15	16	147321-5
	7		9		1	5,7,9,11,14,17	48.77 [1.920]	27.81 [1.095]	18	19	147321-4
			9		1	3,6,9,12,15	43.69 [1.720]	45.59 [1.795]	16	17	147321-3
	7		9		1	2,3,4,5,6	18.29 [.720]	20.19 [.795]	6	7	147321-2
11		OBSOLETE	9		1	4,5	25.91 [1.020]	27.81 [1.095]	9	10	147321-1
		REMARKS	PLATING		POST NUMBER OMITTED		C	B	A	NO. OF POSN	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. HAYMAKER 12OCT99	TE Connectivity	
DIMENSIONS: mm [INCHES]		CHK J. MOSIER 12OCT99		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J. MOSIER 12OCT99	NAME	
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.13[.005] 4 PLC ± - ANGLES ± -		PRODUCT SPEC	HDR ASSY,VERT,SINGLE ROW 2.54[.100]C/L.064[.025]SQPOST,WITH PLZN RETENTIVE POSTS, SELECT LOAD,AMPMODU MTE	
MATERIAL		APPLICATION SPEC	SIZE	CAGE CODE
SEE TABLE		WEIGHT	A1	00779
CUSTOMER DRAWING		SCALE	4:1	SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[147321-3](#)