




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	D	REDRAWN/REVISED PER ECO-17-001757	05DEC2017	KS	JO

D

C


B

A




BASIC DIMENSIONS FOR
EVEN NUMBER OF SPACES
(SEE TABLE)


BASIC DIMENSIONS FOR
ODD NUMBER OF SPACES
(SEE TABLE)



SECTION B-B




DETAIL G
SCALE 8:1



VACUUM COVER

- 0.76µm GOLD IN LOCALIZED PLATE ARE, 3.81µm TIN-LEAD ON SOLDER TAILS ALL OVER 1.27µm NICKEL.
- NOTE DELETED.
- REFER TO NO.OF POSN. IN CHART FOR NUMBER OF SURFACES WHICH ARE COPLANER.
- VACUUM COVER DESIGNED FOR 4mm DIA NOZZLE.VACUUM COVER TO BE REMOVED AFTER SOLDERING.
- PACKGED IN TAPE & REEL PER EIA-481 SPECIATIONS. SEE CHART FOR TAPE WIDTHS.
- 6.75mm MIN TARGET AREA FOR VACUUM PICK-UP.
- HOUSING:BLACK THERMOPLASTIC, CONTACT:PHOSPHOR BRONZE. VACUUM COVER:ALUMINUM.
- VACUUM COVER SHOWN IN PHANTOM LINE.
- TE LOGO PRESENCE AND LOCATION OPTIONAL.
- 0.76µm GOLD IN LOCALIZED PLATE ARE, 3.81µm TIN ON SOLDER TAILS ALL OVER 1.27µm NICKEL.
- NOTE DELETED.



SCALE 4:1

10	44 MM	13.97	11	16.36	24	5-147378-9
	88 MM	62.23	49	64.62	100	5-147378-8
	88 MM	49.53	39	51.92	80	5-147378-7
	72 MM	36.83	29	39.22	60	5-147378-6
	56 MM	30.48	24	32.87	50	5-147378-5
	56 MM	24.13	19	26.52	40	5-147378-4
	44 MM	17.78	14	20.17	30	5-147378-3
	32 MM	11.43	9	13.82	20	5-147378-2
	32 MM	5.08	4	7.47	10	5-147378-1
1	44 MM	13.97	11	16.36	24	147378-9
	88 MM	62.23	49	64.62	100	147378-8
	88 MM	49.53	39	51.92	80	147378-7
	72 MM	36.83	29	39.22	60	147378-6
	56 MM	30.48	24	32.87	50	147378-5
	56 MM	24.13	19	26.52	40	147378-4
	44 MM	17.78	14	20.17	30	147378-3
	32 MM	11.43	9	13.82	20	147378-2
	32 MM	5.08	4	7.47	10	147378-1
FINISH	TAPE WIDTH	DIM_F	E SPACES	DIM_A	NO OF POSN	PART NUMBER

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[147378-4](#)