




THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

MATERIAL
1

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± 0.13 [.005]
3 PLC ± -
4 PLC ± -
ANGLES ± -
FINISH 2 11

DWN
M.BINNER
06NOV2002

CHK
J.OLSON
06NOV02

APVD
J.OLSON
06NOV02

PRODUCT SPEC
108-25022

APPLICATION SPEC
114-25018

WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

NAME
RECEPTACLE ASSEMBLY, MOD IV,
DOUBLE ROW, TOP ENTRY, .100X.100CL,
VERTICAL MOUNT, AMPMODU

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=147424

RESTRICTED TO
-

SCALE
4:1

SHEET
1 OF 2

REV
F7

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By -

ALL RIGHTS RESERVED.

LOCAD

DIST00

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

	2	99.06[3.900]	101.60[4.000]	80	4-147424-0	
	2	96.52[3.800]	99.06[3.900]	78	3-147424-9	
	2	93.98[3.700]	96.52[3.800]	76	3-147424-8	
	2	91.44[3.600]	93.98[3.700]	74	3-147424-7	
	2	88.90[3.500]	91.44[3.600]	72	3-147424-6	
	2	86.36[3.400]	88.90[3.500]	70	3-147424-5	
	2	83.82[3.300]	86.36[3.400]	68	3-147424-4	
	2	81.28[3.200]	83.82[3.300]	66	3-147424-3	
	2	78.74[3.100]	81.28[3.200]	64	3-147424-2	
	2	76.20[3.000]	78.74[3.100]	62	3-147424-1	
	2	73.66[2.900]	76.20[3.000]	60	3-147424-0	
	2	71.12[2.800]	73.66[2.900]	58	2-147424-9	
	2	68.58[2.700]	71.12[2.800]	56	2-147424-8	
	2	66.04[2.600]	68.58[2.700]	54	2-147424-7	
	2	63.50[2.500]	66.04[2.600]	52	2-147424-6	
	2	60.96[2.400]	63.50[2.500]	50	2-147424-5	
SUPERSEDED BY 7-147424-4	2	58.42[2.300]	60.96[2.400]	48	2-147424-4	
	2	55.88[2.200]	58.42[2.300]	46	2-147424-3	
	2	53.34[2.100]	55.88[2.200]	44	2-147424-2	
	2	50.80[2.000]	53.34[2.100]	42	2-147424-1	
SUPERSEDED BY 7-147424-0	2	48.26[1.900]	50.80[2.000]	40	2-147424-0	
	2	45.72[1.800]	48.26[1.900]	38	1-147424-9	
	2	43.18[1.700]	45.72[1.800]	36	1-147424-8	
	2	40.64[1.600]	43.18[1.700]	34	1-147424-7	
SUPERSEDED BY 6-147424-6	2	38.10[1.500]	40.64[1.600]	32	1-147424-6	
SUPERSEDED BY 6-147424-5	2	35.56[1.400]	38.10[1.500]	30	1-147424-5	
	2	33.02[1.300]	35.56[1.400]	28	1-147424-4	
	2	30.48[1.200]	33.02[1.300]	26	1-147424-3	
	2	27.94[1.100]	30.48[1.200]	24	1-147424-2	
	2	25.40[1.000]	27.94[1.100]	22	1-147424-1	
SUPERSEDED BY 6-147424-0	2	22.86[.900]	25.40[1.000]	20	1-147424-0	
	2	20.32[.800]	22.86[.900]	18	147424-9	
	2	17.78[.700]	20.32[.800]	16	147424-8	
	2	15.24[.600]	17.78[.700]	14	147424-7	
	2	12.70[.500]	15.24[.600]	12	147424-6	
	2	10.16[.400]	12.70[.500]	10	147424-5	
	2	7.62[.300]	10.16[.400]	8	147424-4	
	2	5.08[.200]	7.62[.300]	6	147424-3	
	2	2.54[.100]	5.08[.200]	4	147424-2	
9 OBSELETE	2		2.54[.100]	2	6 147424-1	
		FINISH	B	A	NO OF POSN	PART NUMBER

	11	99.06[3.900]	101.60[4.000]	80	12 9-147424-0	
	11	96.52[3.800]	99.06[3.900]	78	12 8-147424-9	
	11	93.98[3.700]	96.52[3.800]	76	12 8-147424-8	
	11	91.44[3.600]	93.98[3.700]	74	12 8-147424-7	
	11	88.90[3.500]	91.44[3.600]	72	12 8-147424-6	
	11	86.36[3.400]	88.90[3.500]	70	12 8-147424-5	
	11	83.82[3.300]	86.36[3.400]	68	12 8-147424-4	
	11	81.28[3.200]	83.82[3.300]	66	12 8-147424-3	
	11	78.74[3.100]	81.28[3.200]	64	12 8-147424-2	
	11	76.20[3.000]	78.74[3.100]	62	12 8-147424-1	
	11	73.66[2.900]	76.20[3.000]	60	12 8-147424-0	
	11	71.12[2.800]	73.66[2.900]	58	12 7-147424-9	
	11	68.58[2.700]	71.12[2.800]	56	12 7-147424-8	
	11	66.04[2.600]	68.58[2.700]	54	12 7-147424-7	
	11	63.50[2.500]	66.04[2.600]	52	12 7-147424-6	
	11	60.96[2.400]	63.50[2.500]	50	12 7-147424-5	
	11	58.42[2.300]	60.96[2.400]	48	12 7-147424-4	
	11	55.88[2.200]	58.42[2.300]	46	12 7-147424-3	
	11	53.34[2.100]	55.88[2.200]	44	12 7-147424-2	
	11	50.80[2.000]	53.34[2.100]	42	12 7-147424-1	
	11	48.26[1.900]	50.80[2.000]	40	12 7-147424-0	
	11	45.72[1.800]	48.26[1.900]	38	12 6-147424-9	
	11	43.18[1.700]	45.72[1.800]	36	12 6-147424-8	
	11	40.64[1.600]	43.18[1.700]	34	12 6-147424-7	
	11	38.10[1.500]	40.64[1.600]	32	12 6-147424-6	
	11	35.56[1.400]	38.10[1.500]	30	12 6-147424-5	
	11	33.02[1.300]	35.56[1.400]	28	12 6-147424-4	
	11	30.48[1.200]	33.02[1.300]	26	12 6-147424-3	
	11	27.94[1.100]	30.48[1.200]	24	12 6-147424-2	
	11	25.40[1.000]	27.94[1.100]	22	12 6-147424-1	
	11	22.86[.900]	25.40[1.000]	20	12 6-147424-0	
	11	20.32[.800]	22.86[.900]	18	12 5-147424-9	
	11	17.78[.700]	20.32[.800]	16	12 5-147424-8	
	11	15.24[.600]	17.78[.700]	14	12 5-147424-7	
	11	12.70[.500]	15.24[.600]	12	12 5-147424-6	
	11	10.16[.400]	12.70[.500]	10	12 5-147424-5	
	11	7.62[.300]	10.16[.400]	8	12 5-147424-4	
	11	5.08[.200]	7.62[.300]	6	12 5-147424-3	
	11	2.54[.100]	5.08[.200]	4	12 5-147424-2	
9 OBSELETE	11		2.54[.100]	2	6 12 5-147424-1	
		FINISH	B	A	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

MATERIAL

1

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± 0.13[.005]

3 PLC ± -

4 PLC ± -

ANGLES ± -

FINISH

2

11

PRODUCT SPEC

108-25022

APPLICATION SPEC

114-25018

WEIGHT

-

CUSTOMER DRAWING

DWN M.BINNER 06NOV2002

CHK J.OLSON 06NOV02

APVD J.OLSON 06NOV02

NAME

SIZE A2

CAGE CODE 00779

DRAWING NO

C=147424

RESTRICTED TO

-

SCALE 1:1

SHEET 2 OF 2

REV F7

TE Connectivity

RECEPTACLE ASSEMBLY, MOD IV,
DOUBLE ROW, TOP ENTRY, .100X.100CL,
VERTICAL MOUNT, AMPMODU

1471-9 (3/11)

147424

1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5-147424-7](#)