

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
0 PLC	\pm -	1 PLC	\pm -
2 PLC	\pm 0.13 [.005]	3 PLC	\pm -
4 PLC	\pm -	ANGLES	\pm -
MATERIAL		FINISH	
△		△△△	

NAME: **TE Connectivity**
 RECEPTACLE ASSEMBLY, MOD IV,
 DOUBLE ROW, TOP ENTRY, .100X.100CL,
 VERTICAL MOUNT, AMPMODU

SIZE: A2 CAGE CODE: 00779 DRAWING NO: C-147424 RESTRICTED TO: -

WEIGHT: -

CUSTOMER DRAWING

SCALE: 4:1 SHEET: 1 OF 2 REV: F7


THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION
ALL RIGHTS RESERVED.

LOC AD	DIST 00	REVISIONS					
		P	LTR	DESCRIPTION		DATE	DWN
		—	—	SEE SHEET 1	—	—	—

2	99.06[3.900]	101.60[4.000]	80	4-147424-0
2	96.52[3.800]	99.06[3.900]	78	3-147424-9
2	93.98[3.700]	96.52[3.800]	76	3-147424-8
2	91.44[3.600]	93.98[3.700]	74	3-147424-7
2	88.90[3.500]	91.44[3.600]	72	3-147424-6
2	86.36[3.400]	88.90[3.500]	70	3-147424-5
2	83.82[3.300]	86.36[3.400]	68	3-147424-4
2	81.28[3.200]	83.82[3.300]	66	3-147424-3
2	78.74[3.100]	81.28[3.200]	64	3-147424-2
2	76.20[3.000]	78.74[3.100]	62	3-147424-1
2	73.66[2.900]	76.20[3.000]	60	3-147424-0
2	71.12[2.800]	73.66[2.900]	58	2-147424-9
2	68.58[2.700]	71.12[2.800]	56	2-147424-8
2	66.04[2.600]	68.58[2.700]	54	2-147424-7
2	63.50[2.500]	66.04[2.600]	52	2-147424-6
2	60.96[2.400]	63.50[2.500]	50	2-147424-5
2	58.42[2.300]	60.96[2.400]	48	2-147424-4
2	55.88[2.200]	58.42[2.300]	46	2-147424-3
2	53.34[2.100]	55.88[2.200]	44	2-147424-2
2	50.80[2.000]	53.34[2.100]	42	2-147424-1
2	48.26[1.900]	50.80[2.000]	40	2-147424-0
2	45.72[1.800]	48.26[1.900]	38	1-147424-9
2	43.18[1.700]	45.72[1.800]	36	1-147424-8
2	40.64[1.600]	43.18[1.700]	34	1-147424-7
2	38.10[1.500]	40.64[1.600]	32	1-147424-6
2	35.56[1.400]	38.10[1.500]	30	1-147424-5
2	33.02[1.300]	35.56[1.400]	28	1-147424-4
2	30.48[1.200]	33.02[1.300]	26	1-147424-3
2	27.94[1.100]	30.48[1.200]	24	1-147424-2
2	25.40[1.000]	27.94[1.100]	22	1-147424-1
2	22.86[.900]	25.40[1.000]	20	1-147424-0
2	20.32[.800]	22.86[.900]	18	147424-9
2	17.78[.700]	20.32[.800]	16	147424-8
2	15.24[.600]	17.78[.700]	14	147424-7
2	12.70[.500]	15.24[.600]	12	147424-6
2	10.16[.400]	12.70[.500]	10	147424-5
2	7.62[.300]	10.16[.400]	8	147424-4
2	5.08[.200]	7.62[.300]	6	147424-3
2	2.54[.100]	5.08[.200]	4	147424-2
2		2.54[.100]	2	147424-1
6				
FINISH	B	A	NO OF POSN	PART NUMBER

	99.06[3.900]	101.60[4.000]	80		9-147424-0
	96.52[3.800]	99.06[3.900]	78		8-147424-9
	93.98[3.700]	96.52[3.800]	76		8-147424-8
	91.44[3.600]	93.98[3.700]	74		8-147424-7
	88.90[3.500]	91.44[3.600]	72		8-147424-6
	86.36[3.400]	88.90[3.500]	70		8-147424-5
	83.82[3.300]	86.36[3.400]	68		8-147424-4
	81.28[3.200]	83.82[3.300]	66		8-147424-3
	78.74[3.100]	81.28[3.200]	64		8-147424-2
	76.20[3.000]	78.74[3.100]	62		8-147424-1
	73.66[2.900]	76.20[3.000]	60		8-147424-0
	71.12[2.800]	73.66[2.900]	58		7-147424-9
	68.58[2.700]	71.12[2.800]	56		7-147424-8
	66.04[2.600]	68.58[2.700]	54		7-147424-7
	63.50[2.500]	66.04[2.600]	52		7-147424-6
	60.96[2.400]	63.50[2.500]	50		7-147424-5
	58.42[2.300]	60.96[2.400]	48		7-147424-4
	55.88[2.200]	58.42[2.300]	46		7-147424-3
	53.34[2.100]	55.88[2.200]	44		7-147424-2
	50.80[2.000]	53.34[2.100]	42		7-147424-1
	48.26[1.900]	50.80[2.000]	40		7-147424-0
	45.72[1.800]	48.26[1.900]	38		6-147424-9
	43.18[1.700]	45.72[1.800]	36		6-147424-8
	40.64[1.600]	43.18[1.700]	34		6-147424-7
	38.10[1.500]	40.64[1.600]	32		6-147424-6
	35.56[1.400]	38.10[1.500]	30		6-147424-5
	33.02[1.300]	35.56[1.400]	28		6-147424-4
	30.48[1.200]	33.02[1.300]	26		6-147424-3
	27.94[1.100]	30.48[1.200]	24		6-147424-2
	25.40[1.000]	27.94[1.100]	22		6-147424-1
	22.86[.900]	25.40[1.000]	20		6-147424-0
	20.32[.800]	22.86[.900]	18		5-147424-9
	17.78[.700]	20.32[.800]	16		5-147424-8
	15.24[.600]	17.78[.700]	14		5-147424-7
	12.70[.500]	15.24[.600]	12		5-147424-6
	 10.16[.400]	12.70[.500]	10		5-147424-5
	 7.62[.300]	10.16[.400]	8		5-147424-4
	 5.08[.200]	7.62[.300]	6		5-147424-3
	 2.54[.100]	5.08[.200]	4		5-147424-2
	—	2.54[.100]	2		 5-147424-1
					
	FINISH	B	A	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.BINNER CHK J.OLSON	06NOV2002 06NOV02	 TE Connectivity	
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD J.OLSON	06NOV02		
	0 PLC	± -	PRODUCT SPEC	NAME RECEPTACLE ASSEMBLY, MOD IV, DOUBLE ROW, TOP ENTRY, .100X.100CL, VERTICAL MOUNT, AMPMODU	
	1 PLC	± -			
	2 PLC	± 0.13[.005]	108-25022		
	3 PLC	± -	APPLICATION SPEC		
	4 PLC	± -			
	ANGLES	± -			114-25018
MATERIAL	FINISH	WEIGHT	A2	SIZE CAGE CODE DRAWING NO	RESTRICTED TO
 1	 2 11	—	00779	C-147424	—

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[6-147424-5](#)