





LOC		DIST		REVISIONS					
GP	00	P	LTR	DESCRIPTION			DATE	DWN	APVD
			C	REV	PER	EC	09-028503	30DEC09	RG




SCALE 5:1

- 1 MATERIAL: BRASS
2 MATERIAL: HIGH CONDUCTIVITY COPPER ALLOY
3 FINISH: CONTACT MATING AREA .38μm MIN Au;
CRIMP AREA 2.03μm MIN. Sn;
UNDERPLATE OVERALL 1.27μm MIN. Ni
4 FINISH: CONTACT MATING AREA 1.27μm MIN Au;
CRIMP AREA 2.03μm MIN. Sn;
UNDERPLATE OVERALL 1.27μm MIN Ni
5 CONTACT SHOWN W/O CARRIER, OR HIDDEN LINES, FOR CLARITY
6 CUT OFF TO BE .13 MAX
7 INSULATION DIAMETER : 2.0-3.1 mm
8 WIRE DIAMETER: 16-20 AWG
10 THIS PRODUCT HAS NOT COMPLETED VALIDATION TESTING.
11 FINISH: ENTIRE CONTACT 1.27μm MIN Au;
UNDERPLATE OVERALL 1.27μm MIN Ni

SCALE 12:1



SECTION A-A
SCALE 20:1



SECTION B-B
SCALE 20:1

2	6	11	11.4	1-1489128-6
2	6	11	9.8	1-1489128-5
1	6	11	11.4	1-1489128-4
1	6	11	9.8	1-1489128-3
2	-	4	11.4	1-1489128-0
2	-	4	9.8	1489128-9
1	-	3	11.4	1489128-8
1	-	3	9.8	1489128-7
1	-	4	11.4	1489128-3
1	-	4	9.8	1489128-2
MATERIAL	LOOSE PIECE	FINISH	DIM "A"	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN AL FRANTUM CHK -	15 MAY 02		Tyco Electronics Corporation Middletown, Pa 17057	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC 108-1998 APPLICATION SPEC 114-13067		SIZE A1		
MATERIAL 1 2		FINISH 3 4		WEIGHT -		
CUSTOMER DRAWING				SCALE 4:1	SHEET 1 OF 1	
				REV C		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1489128-7](#)