


DATE	C	B	A	NO. OF POSITIONS	PART NUMBER	
INSTRUMENT.	OWN J. HOFFMAN	06DEC95	 TE Connectivity			
UNLESS NOTED:	CHK G. DUBNICZKI	01FEB96				
	APVD G. DUBNICZKI	01FEB96				NAME
	PRODUCT SPEC					HEADER ASSEMBLY, MOD II, BREAKAWAY, SINGLE ROW, HIGH TEMPERATURE, VERTICAL WITH RETENTION FEATURE, W/.025 SQ. POSTS, .100 C/L
[.02] 27 [.005] 127 [.0005]	APPLICATION SPEC		SIZE	CAGE CODE	DRAWING NO	
E	WEIGHT	—	A1	00779	 146294	
CUSTOMER DRAWING			SCALE	4:1	SHEET 1 OF 1 REV K	



1. TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADER IS HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD

2. THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING

3. RETENTION FEATURES ON SOLDER TAILS, LOCATED AT MANUFACTURERS OPTION

4. 0.00254 - 0.00504 [.000100 - .000200] MATTE TIN-LEAD,
ALL OVER 0.00127 [.000050] NICKEL

5. HOUSING: LCP, COLOR: BLACK
POSTS: COPPER ALLOY.

6. 0.00254 - 0.00504 [.000100 - .000200] MATTE TIN,
ALL OVER 0.00127 [.000050] NICKEL



7. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI


OBSOLETE

7
OBSOLETE

SUPERSEDED BY 146270—
OBSOLETE

SUPERSEDED BY 146270—
OBSOLETE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG 1. HOFFMAN	06DEC95	 TE Connectivity	
		CHK G. DUBNICZKI	01FEB96		
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS SPECIFIED:		NAME G. DUBNICZKI	
		PRODUCT SPEC		HEADER ASSEMBLY, MOD II, BREAKAWAY, SINGLE ROW, HIGH TEMPERATURE, VERTICAL WITH RETENTION FEATURE, W/.025 SQ. POSTS, .100 C/L	
		APPLICATION SPEC		SIZE CAGE CODE DRAWING NO	
		WEIGHT		RESTRICTED TO	
		FINISH		A1 00779 C-146294	
MATERIAL 		SEE TABLE		SCALE 4:1 SHEET 1 OF 1 REV K	
CUSTOMER DRAWING					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5-146294-3](#)