






SOLETTI

		101.19 [3.984]	99.06 [3.900]	39	40	3-146405-8
		98.65 [3.884]	96.52 [3.800]	38	39	3-146405-7
		96.11 [3.784]	93.98 [3.700]	37	38	3-146405-6
		93.57 [3.684]	91.44 [3.600]	36	37	3-146405-5
		91.03 [3.584]	88.90 [3.500]	35	36	3-146405-4
		88.49 [3.484]	86.36 [3.400]	34	35	3-146405-3
		85.95 [3.384]	83.82 [3.300]	33	34	3-146405-2
		83.41 [3.284]	81.28 [3.200]	32	33	3-146405-1
		80.87 [3.184]	78.74 [3.100]	31	32	3-146405-0
		78.33 [3.084]	76.20 [3.000]	30	31	2-146405-9
		75.79 [2.984]	73.66 [2.900]	29	30	2-146405-8
		73.25 [2.884]	71.12 [2.800]	28	29	2-146405-7
		70.71 [2.784]	68.58 [2.700]	27	28	2-146405-6
		68.17 [2.684]	66.04 [2.600]	26	27	2-146405-5
		65.63 [2.584]	63.5 [2.500]	25	26	2-146405-4
		63.09 [2.484]	60.96 [2.400]	24	25	2-146405-3
		60.55 [2.384]	58.42 [2.300]	23	24	2-146405-2
		58.01 [2.284]	55.88 [2.200]	22	23	2-146405-1
		55.47 [2.184]	53.34 [2.100]	21	22	2-146405-0
		52.93 [2.084]	50.80 [2.000]	20	21	1-146405-9
		50.39 [1.984]	48.26 [1.900]	19	20	1-146405-8
		47.85 [1.884]	45.72 [1.800]	18	19	1-146405-7
		45.31 [1.784]	43.18 [1.700]	17	18	1-146405-6
		42.77 [1.684]	40.64 [1.600]	16	17	1-146405-5
		40.23 [1.584]	38.10 [1.500]	15	16	1-146405-4
		37.69 [1.484]	35.56 [1.400]	14	15	1-146405-3
		35.15 [1.384]	33.02 [1.300]	13	14	1-146405-2
		32.61 [1.284]	30.48 [1.200]	12	13	1-146405-1
		30.07 [1.184]	27.94 [1.100]	11	12	1-146405-0
		27.53 [1.084]	25.40 [1.000]	10	11	146405-9
		24.99 [.984]	22.86 [.900]	9	10	146405-8
		22.45 [.884]	20.32 [.800]	8	9	146405-7
		19.91 [.784]	17.78 [.700]	7	8	146405-6
		17.37 [.684]	15.24 [.600]	6	7	146405-5
		14.83 [.584]	12.70 [.500]	5	6	146405-4
		12.29 [.484]	10.16 [.400]	4	5	146405-3
		9.75 [.384]	7.62 [.300]	3	4	146405-2
		7.21 [.284]	5.08 [.200]	2	3	146405-1
REMARKS	PLATING	C	B	A	NO. OF POSITIONS	PART NUMBER

1. TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADERS ARE HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD.
2. THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND THE HOUSING.
3. RETENTION FEATURES ON SOLDER TAILS, LOCATED AT MANUFACTURERS OPTION.
4.  FOR KINKED TAILS.
5. 0.000025 [.000001] GOLD IN CONTACT AREA, 0.00127-0.00504 [.000050-.000200] MATTE TIN-LEAD ON SOLDER TAILS, ALL OVER 0.00076-0.00203 [.000030-.000080] NICKEL.
6. 0.000025 [.000001] GOLD IN CONTACT AREA, 0.00127-0.00504 [.000050-.000200] MATTE TIN ON SOLDER TAILS, ALL OVER 0.00076-0.00203 [.000030-.000080] NICKEL.
7. HIGH TEMPERATURE CONFIGURATION
8. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

THIS DRAWING IS A CONTROLLED DOCUMENT.						DIN T. HOFFMAN		26/6-95				TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK G. DUBNICZKI		12/9-95							
		0 P.LC ± - 1 P.LC ± - 2 P.LC ± 0.51[.02] 3 P.LC ± 0.127[.005] ANGLES ± 0.12[.005]		APP'D G. DUBNICZKI		12/9-95		NAME		HEADER ASSEMBLY, MOD II, BREAKAWAY, SINGLE ROW, .100 C/L VERTICAL, .025 SQ.POSTS WITH RETENTIVE FEATURES			
MATERIAL		FINISH		PRODUCT SPEC		WEIGHT		SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO	
POSTS: COPPER ALLOY		SEE TABLE		APPLICATION		—		A1		00779	 146405		
CUSTOMER DRAWING						SCALE		4:1		SHEET	1 OF 2	REV F	

8		7		6		5		4		3		2		1	
THIS DRAWING IS UNPUBLISHED.				RELEASED FOR PUBLICATION											
© COPYRIGHT - - By - -				ALL RIGHTS RESERVED.											

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[8-146405-8](#)