




LOC		DIST		REVISIONS					
GP	00	P	LTR	DESCRIPTION			DATE	DWN	APVD
			C	REV PER EC 09-028503			30DEC09	RG	DO

D

C

B


A




SCALE 5:1

SCALE 12:1

- 1 MATERIAL: BRASS
2 MATERIAL: HIGH CONDUCTIVITY COPPER ALLOY
3 FINISH: CONTACT MATING AREA .38µm MIN Au;
CRIMP AREA 2.03µm MIN. Sn;
UNDERPLATE OVERALL 1.27µm MIN. Ni
4 FINISH: CONTACT MATING AREA 1.27µm MIN Au;
CRIMP AREA 2.03µm MIN. Sn;
UNDERPLATE OVERALL 1.27µm MIN Ni
5 CONTACT SHOWN W/O CARRIER, OR HIDDEN LINES, FOR CLARITY
6 CUT OFF TO BE .13 MAX
7 INSULATION DIAMETER : 2.0-3.1 mm
8 WIRE DIAMETER: 16-20 AWG
10 THIS PRODUCT HAS NOT COMPLETED VALIDATION TESTING.
11 FINISH: ENTIRE CONTACT 1.27µm MIN Au;
UNDERPLATE OVERALL 1.27µm MIN Ni



SECTION A-A
SCALE 20:1



SECTION B-B
SCALE 20:1

			11.4	1-1489128-6
			9.8	1-1489128-5
			11.4	1-1489128-4
			9.8	1-1489128-3
	-		11.4	1-1489128-0
	-		9.8	1489128-9
	-		11.4	1489128-8
	-		9.8	1489128-7
	-		11.4	1489128-3
	-		9.8	1489128-2
MATERIAL	LOOSE PIECE	FINISH	DIM "A"	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN AL FRANTUM CHK - APVD -	15 MAY 02	Tyco Electronics Corporation Middletown, Pa 17057	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		NAME MINI POWER DRAWER CRIMP PLUG CONTACT 16 - 20 GAUGE	
MATERIAL 1 2		FINISH 3 4		SIZE A1	
WEIGHT -		CUSTOMER DRAWING		SCALE 4:1 SHEET 1 OF 1 REV C	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1489128-3](#)