


1 . ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS

2. TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADER IS HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD

3 THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING



4 HOUSING: FLAME RETARDANT THERMOPLASTIC; COLOR: BLACK.

5 FINISH: 0.000381 [.000015] GOLD ON CONTACT AREA,
ALL OVER 0.00127 [.000050] NICKEL ENTIRE POST.



RECOMMENDED HOLE LAYOUT

99.06	39	40	4-146482-0
[3.984]	[3.900]		
98.65	38	39	3-146482-9
[3.884]	[3.800]		
96.11	37	38	3-146482-8
[3.784]	[3.700]		
93.57	36	37	3-146482-7
[3.684]	[3.600]		
91.03	35	36	3-146482-6
[3.584]	[3.500]		
88.49	34	35	3-146482-5
[3.484]	[3.400]		
85.95	33	34	3-146482-4
[3.384]	[3.300]		
83.41	32	33	3-146482-3
[3.284]	[3.200]		
80.87	31	32	3-146482-2
[3.184]	[3.100]		
78.33	30	31	3-146482-1
[3.084]	[3.000]		
75.79	29	30	3-146482-0
[2.984]	[2.900]		
73.25	28	29	2-146482-9
[2.884]	[2.800]		
70.71	27	28	2-146482-8
[2.784]	[2.700]		
68.17	26	27	2-146482-7
[2.684]	[2.600]		
65.63	25	26	2-146482-6
[2.584]	[2.500]		
63.09	24	25	2-146482-5
[2.484]	[2.400]		
60.55	23	24	2-146482-4
[2.384]	[2.300]		
58.01	22	23	2-146482-3
[2.284]	[2.200]		
55.47	21	22	2-146482-2
[2.184]	[2.100]		
52.93	20	21	2-146482-1
[2.084]	[2.000]		
50.39	19	20	2-146482-0
[1.984]	[1.900]		
47.85	18	19	1-146482-9
[1.884]	[1.800]		
45.31	17	18	1-146482-8
[1.784]	[1.700]		
42.77	16	17	1-146482-7
[1.684]	[1.600]		
40.23	15	16	1-146482-6
[1.584]	[1.500]		
37.69	14	15	1-146482-5
[1.484]	[1.400]		
35.15	13	14	1-146482-4
[1.384]	[1.300]		
32.61	12	13	1-146482-3
[1.284]	[1.200]		
30.07	11	12	1-146482-2
[1.184]	[1.100]		
27.53	10	11	1-146482-1
[1.084]	[1.000]		
24.99	9	10	1-146482-0
[.984]	[.900]		
22.45	8	9	146482-9
[.884]	[.800]		
19.91	7	8	146482-8
[.784]	[.700]		
17.37	6	7	146482-7
[.684]	[.600]		
14.83	5	6	146482-6
[.584]	[.500]		
12.29	4	5	146482-5
[.484]	[.400]		
9.75	3	4	146482-4
[.384]	[.300]		
7.21	2	3	146482-3
[.284]	[.200]		
4.67	1	2	146482-2
[.184]	[.100]		
2.13	-	1	146482-1
[.084]	-		
G	F	E	NO. OF POSITIONS
			PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.						DWG 14-MAR-97			TE Connectivity	
						CHK G. DUBNICZKI	14-MAR-97			
						APPV G. DUBNICZKI	14-MAR-97			
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		HEADER ASSEMBLY, MOD II, STACKING, SINGLE ROW, .025 SQ.POST, UNSHROUDED				
		0 PLC ± .		PRODUCT SPEC						
		2 PLC ± .								
		2 PCL ± 0.01[.003]		APPLICATION SPEC		SIZE CAGE CODE DRAWING NO RESTRICTED TO				
		0.01[0.003] ANGLES ± .								
MATERIAL		FINISH		WEIGHT	A1 00779 C 146482					
				CUSTOMER DRAWING	SCALE 4:1 SHEET 1 OF 1 REV P					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[146482-6](#)