


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	D8	PN 5-2 AND 5-6 RELEASED FOR PRODUCTION	07DEC2018	RK	PS
	D9	PART OBSOLETE	28AUG2020	DV	PS



Technical drawing of a mechanical part, likely a bracket or support, showing dimensions and labels.

Dimensions:


- Vertical dimension: 15.5
- Horizontal dimension: 18.4

Labels:

- RETENTION LATCH
- MATING FACE

	OBSOLETE	BLACK	DETAIL N	TIN	30.48±0.20	6	6-1546108-9	
		GREEN	DETAIL M	TIN	15.24±0.15	3	6-1546108-8	
		ORANGE	DETAIL M	TIN	15.24±0.15	3	6-1546108-7	
		BLACK	DETAIL M	TIN	15.24±0.15	3	6-1546108-6	
		BLACK	DETAIL N	TIN	25.40±0.20	5	6-1546108-5	
		GREEN	DETAIL N	TIN	15.24±0.15	3	6-1546108-4	
		ORANGE	DETAIL N	TIN	15.24±0.15	3	6-1546108-3	
		BLACK	DETAIL N	TIN	15.24±0.15	3	6-1546108-2	
OBSOLETE	GRAY	DETAIL H	TIN	55.88	11	6-1546108-1		
	GRAY	DETAIL H	TIN	45.72	9	5-1546108-9		
	GRAY	DETAIL H	TIN	30.48±0.20	6	5-1546108-6		
	GRAY	DETAIL H	TIN	20.32±0.15	4	5-1546108-4		
	GRAY	DETAIL H	TIN	15.24±0.15	3	5-1546108-3		
	GRAY	DETAIL H	TIN	10.16±0.15	2	5-1546108-2		
	OBSOLETE	GRAY	DETAIL H	TIN	60.96	12	4-1546108-7	
		GRAY	-	TIN	15.24±0.15	3	4-1546108-6	
		GRAY	DETAIL K	TIN	40.64	8	4-1546108-5	
		GRAY	DETAIL H	TIN	40.64	8	4-1546108-4	
TCH	OBSOLETE	GRAY	DETAIL H	TIN	96.52±0.35	19	4-1546108-3	
		GRAY		.000030 GOLD	60.96±0.20	12	4-1546108-2	
		GRAY		.000030 GOLD	30.48±0.20	6	3-1546108-6	
		GRAY		.000030 GOLD	20.32±0.15	4	3-1546108-4	
	FACE	OBSOLETE	GRAY		.000030 GOLD	15.24±0.15	3	3-1546108-3
			GRAY		TIN	127.00±0.35	25	2-1546108-5
			GRAY		TIN	121.92±0.35	24	2-1546108-4
			GRAY		TIN	116.84±0.35	23	2-1546108-3
			GRAY		TIN	111.76±0.35	22	2-1546108-2
			GRAY		TIN	106.68±0.35	21	2-1546108-1
GRAY				TIN	101.60±0.35	20	2-1546108-0	
GRAY				TIN	96.52±0.35	19	1-1546108-9	
OBSOLETE	OBSOLETE	GRAY		TIN	91.44±0.30	18	1-1546108-8	
		GRAY		TIN	86.36±0.30	17	1-1546108-7	
		GRAY		TIN	81.28±0.30	16	1-1546108-6	
		GRAY		TIN	76.20±0.30	15	1-1546108-5	
		GRAY		TIN	71.12	14	1-1546108-4	
	OBSOLETE	GRAY		TIN	66.04	13	1-1546108-3	
		GRAY		TIN	60.96	12	1-1546108-2	
		GRAY		TIN	55.88	11	1-1546108-1	
		GRAY		TIN	50.80	10	1-1546108-0	
		GRAY		TIN	45.72	9	1546108-9	
OBSOLETE	OBSOLETE	GRAY		TIN	40.64	8	1546108-8	
		GRAY		TIN	35.56±0.20	7	1546108-7	
		GRAY		TIN	30.48±0.20	6	1546108-6	
OBSOLETE	OBSOLETE	GRAY		TIN	25.40±0.20	5	1546108-5	
		GRAY		TIN	20.32±0.15	4	1546108-4	
		GRAY		TIN	15.24±0.15	3	1546108-3	
OBSOLETE	OBSOLETE	GRAY		TIN	10.16±0.15	2	1546108-2	
		COLOR	MARKING STYLE	CONTACT FINISH	L	NO OF POSN	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S.WELDON 11SEP2002		 TE Connectivity			
		CHK C.RICHARD 11SEP2002					
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME TERMINAL BLOCK, PLUG, STACKING. 5.08mm PITCH			
mm							
		0 PLC ±		SIZE A2 CAGE CODE 00779 DRAWING NO C=1546108 RESTRICTED TO -			
		1 PLC ±0.3					
		2 PLC ±0.25					
		3 PLC ±					
		4 PLC ±					
ANGLES ±2°		PRODUCT SPEC					
FINISH		APPLICATION SPEC					
MATERIAL		-					
SEE NOTES		SEE NOTES		SCALE 4:1 SHEET 1 OF 2 REV D9			
CUSTOMER DRAWING							



THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN S.WELDON 11SEP2002

CHK C.RICHARD 11SEP2002

APVD C.RICHARD 11SEP2002

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

DIMENSIONS:
mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±

1 PLC ±0.3

2 PLC ±0.25

3 PLC ±

4 PLC ±

ANGLES ±2°

FINISH

SEE NOTES

SEE NOTES

NAME

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

SCALE 4:1

SHEET 2 OF 2

REV 09

TE Connectivity

TERMINAL BLOCK, PLUG, STACKING,
5.08mm PITCH

A2100779

©-1546108

1471-9 (3/13)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-1546108-6](#)