


1. ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS
2. TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADER IS HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD
3. THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING
4. HOUSING: FLAME RETARDANT THERMOPLASTIC; COLOR: BLACK.
5. FINISH: 0.000381 [.000015] GOLD ON CONTACT AREA,
ALL OVER 0.00127 [.000050] NICKEL ENTIRE POST.



RECOMMENDED HOLE LAYOUT

[3.984]	[3.900]	39	40	4-146482-0
[3.884]	[3.800]	38	39	3-146482-9
[3.784]	[3.700]	37	38	3-146482-8
[3.684]	[3.600]	36	37	3-146482-7
[3.584]	[3.500]	35	36	3-146482-6
[3.484]	[3.400]	34	35	3-146482-5
[3.384]	[3.300]	33	34	3-146482-4
[3.284]	[3.200]	32	33	3-146482-3
[3.184]	[3.100]	31	32	3-146482-2
[3.084]	[3.000]	30	31	3-146482-1
[2.984]	[2.900]	29	30	3-146482-0
[2.884]	[2.800]	28	29	2-146482-9
[2.784]	[2.700]	27	28	2-146482-8
[2.684]	[2.600]	26	27	2-146482-7
[2.584]	[2.500]	25	26	2-146482-6
[2.484]	[2.400]	24	25	2-146482-5
[2.384]	[2.300]	23	24	2-146482-4
[2.284]	[2.200]	22	23	2-146482-3
[2.184]	[2.100]	21	22	2-146482-2
[2.084]	[2.000]	20	21	2-146482-1
[1.984]	[1.900]	19	20	2-146482-0
[1.884]	[1.800]	18	19	1-146482-9
[1.784]	[1.700]	17	18	1-146482-8
[1.684]	[1.600]	16	17	1-146482-7
[1.584]	[1.500]	15	16	1-146482-6
[1.484]	[1.400]	14	15	1-146482-5
[1.384]	[1.300]	13	14	1-146482-4
[1.284]	[1.200]	12	13	1-146482-3
[1.184]	[1.100]	11	12	1-146482-2
[1.084]	[1.000]	10	11	1-146482-1
[.984]	[.900]	9	10	1-146482-0
[.884]	[.800]	8	9	146482-9
[.784]	[.700]	7	8	146482-8
[.684]	[.600]	6	7	146482-7
[.584]	[.500]	5	6	146482-6
[.484]	[.400]	4	5	146482-5
[.384]	[.300]	3	4	146482-4
[.284]	[.200]	2	3	146482-3
[.184]	[.100]	1	2	146482-2
[.084]	-	-	1	146482-1
G	F	E	NO. OF POSITIONS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG. 14-MAR-97 E. BRANDBERG CHK. 14-MAR-97 G. DUBNICZKI APP'D 14-MAR-97 G. DUBNICZKI		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME	
 0 PLC ± - 1 PLC ± - 2 PLC ± 0.51[.02] 3 PLC ± 0.127[.005] 4 PLC ± 0.127[.005] ANGLES ±		PRODUCT SPEC APPLICATION SPEC		HEADER ASSEMBLY, MOD II, STACKING, SINGLE ROW, .025 SQ.POST, UNSHROUDED	
MATERIAL		FINISH		SIZE	CAGE CODE
				WEIGHT	DRAWING NO
				A1	00779
CUSTOMER DRAWING				SCALE	REV
				4:1	1 of 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-146482-9](#)