

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT

By

ALL RIGHTS RESERVED.

LOC

DIST

AD

00

REVISED

PER

ECO

14-005404

DATE

05AUG2014

DWN

NK

APVD

MM

13

NONE

30.48
[1.200]

12

32.61
[1.284]

26

7-146806-4

5

6

NONE

3

7.62
[.300]

3

9.75
[.384]

8

7-146806-3

5

6

NONE

2

7.62
[.300]

3

9.75
[.384]

8

7-146806-2

5

3

NONE

8

22.86
[.900]

9

24.99
[.984]

20

7-146806-0

6

8

NONE

NONE

17.78
[.700]

7

19.91
[.784]

16

6-146806-9

6

7

4

15.24
[.600]

6

17.37
[.684]

14

6-146806-8

5

7

OBSOLETE

6

1

15.24
[.600]

6

17.37
[.684]

14

6-146806-7

6

NONE

4

12.70
[.500]

5

14.83
[.584]

12

6-146806-6

7

OBSOLETE

6

NONE

1

17.78
[.700]

7

19.91
[.784]

16

6-146806-5

6

NONE

1

10.16
[.400]

4

12.29
[.484]

10

6-146806-4

6

NONE

3

10.16
[.400]

4

12.29
[.484]

10

6-146806-3

5

6

1

NONE

10.16
[.400]

4

12.29
[.484]

10

6-146806-2

6

13

1

30.48
[1.200]

12

32.61
[1.284]

26

6-146806-1

7

OBSOLETE

6

1

15

35.56
[1.400]

14

37.69
[1.484]

30

5-146806-6

6

NONE

4

10.16
[.400]

4

12.29
[.484]

10

5-146806-5

7

OBSOLETE

6

NONE

10

40.64
[1.600]

16

42.77
[1.684]

34

5-146806-4

6

11

NONE

35.56
[1.400]

14

37.69
[1.484]

30

5-146806-3

6

10

NONE

35.56
[1.400]

14

37.69
[1.484]

30

5-146806-2

6

NONE

3

30.48
[1.200]

12

32.61
[1.284]

26

5-146806-1

3

NONE

5

12.70
[.500]

5

14.83
[.584]

12

2-146806-1

5

3

7

4

15.24
[.600]

6

17.37
[.684]

14

1-146806-7

7

OBSOLETE

3

NONE

4

12.70
[.500]

5

14.83
[.584]

12

1-146806-6

3

NONE

1

17.78
[.700]

7

19.91
[.784]

16

1-146806-5

3

NONE

1

10.16
[.400]

4

12.29
[.484]

10

1-146806-4

3

NONE

3

10.16
[.400]

4

12.29
[.484]

10

1-146806-3

5

3

1

NONE

10.16
[.400]

4

12.29
[.484]

10

1-146806-2

7

SUPERSEDED

3

13

1

30.48
[1.200]

12

32.61
[1.284]

26

1-146806-1

5

3

7,8,9

6,8,9,10

22.86
[.900]

9

24.99
[.984]

20

1-146806-0

5

3

3

NONE

15.24
[.600]

6

17.37
[.684]

14

146806-9

5

3

3

4

10.16
[.400]

4

12.29
[.484]

10

146806-8

OBSOLETE

3

NONE

3

10.16
[.400]

4

12.29
[.484]

10

146806-7

7

OBSOLETE

3

1

15

35.56
[1.400]

14

37.69
[1.484]

30

146806-6

3

NONE

4

10.16
[.400]

4

12.29
[.484]

10

146806-5

OBSOLETE

3

NONE

10

40.64
[1.600]

16

42.77
[1.684]

34

146806-4

3

11

NONE

35.56
[1.400]

14

37.69
[1.484]

30

146806-3

3

10

NONE

35.56
[1.400]

14

37.69
[1.484]

30

146806-2

3

NONE

3

30.48
[1.200]

12

32.61
[1.284]

26

146806-1

PLATING

ROW M

ROW N

POSTS OMITTED

C

B

A

NO OF POSN

PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
E. BRANDBERG
CHK
G. DUBNICZKI
APVD
G. DUBNICZKI

29-JAN-97

29-JAN-97

NAME

DIMENSIONS:
mm [INCHES]

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± 0.13[.005]
4 PLC ± -
ANGLES ± -

SEE TABLE

MATERIAL

4

WEIGHT

-

SIZE

CAGE CODE

DRAWING NO

A100779

RESTRICTED TO

-

CUSTOMER DRAWING

SCALE

1:1

SHEET

1

OF

1

REV

AA

TE Connectivity

SURFACE MOUNT HEADER ASSEMBLY,
MOD II, BREAKAWAY, VERTICAL,
DOUBLE ROW, .100 X.100 CL, .025 SQ.POST

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT

By

ALL RIGHTS RESERVED.

LOC

DIST

AD

00

REVISED

PER

ECO

14-005404

DATE

05AUG2014

DWN

NK

APVD

MM

13

NONE

30.48
[1.200]

12

32.61
[1.284]

26

7-146806-4

5

6

NONE

3

7.62
[.300]

3

9.75
[.384]

8

7-146806-3

5

6

NONE

2

7.62
[.300]

3

9.75
[.384]

8

7-146806-2

5

3

NONE

8

22.86
[.900]

9

24.99
[.984]

20

7-146806-0

6

8

NONE

NONE

17.78
[.700]

7

19.91
[.784]

16

6-146806-9

6

7

4

15.24
[.600]

6

17.37
[.684]

14

6-146806-8

5

7

OBSOLETE

6

1

15.24
[.600]

6

17.37
[.684]

14

6-146806-7

6

NONE

4

12.70
[.500]

5

14.83
[.584]

12

6-146806-6

7

OBSOLETE

6

NONE

1

17.78
[.700]

7

19.91
[.784]

16

6-146806-5

6

NONE

1

10.16
[.400]

4

12.29
[.484]

10

6-146806-4

6

NONE

3

10.16
[.400]

4

12.29
[.484]

10

6-146806-3

5

6

1

NONE

10.16
[.400]

4

12.29
[.484]

10

6-146806-2

6

13

1

30.48
[1.200]

12

32.61
[1.284]

26

6-146806-1

7

OBSOLETE

6

1

15

35.56
[1.400]

14

37.69
[1.484]

30

5-146806-6

6

NONE

4

10.16
[.400]

4

12.29
[.484]

10

5-146806-5

7

OBSOLETE

6

NONE

10

40.64
[1.600]

16

42.77
[1.684]

34

5-146806-4

6

11

NONE

35.56
[1.400]

14

37.69
[1.484]

30

5-146806-3

6

10

NONE

35.56
[1.400]

14

37.69
[1.484]

30

5-146806-2

6

NONE

3

30.48
[1.200]

12

32.61
[1.284]

26

5-146806-1

3

NONE

5

12.70
[.500]

5

14.83
[.584]

12

2-146806-1

5

3

7

4

15.24
[.600]

6

17.37
[.684]

14

1-146806-7

7

OBSOLETE

3

NONE

4

12.70
[.500]

5

14.83
[.584]

12

1-146806-6

3

NONE

1

17.78
[.700]

7

19.91
[.784]

16

1-146806-5

3

NONE

1

10.16
[.400]

4

12.29
[.484]

10

1-146806-4

3

NONE

3

10.16
[.400]

4

12.29
[.484]

10

1-146806-3

5

3

1

NONE

10.16
[.400]

4

12.29
[.484]

10

1-146806-2

7

SUPERSEDED

3

13

1

30.48
[1.200]

12

32.61
[1.284]

26

1-146806-1

5

3

7,8,9

6,8,9,10

22.86
[.900]

9

24.99
[.984]

20

1-146806-0

5

3

3

NONE

15.24
[.600]

6

17.37
[.684]

14

146806-9

5

3

3

4

10.16
[.400]

4

12.29
[.484]

10

146806-8

OBSOLETE

3

NONE

3

10.16
[.400]

4

12.29
[.484]

10

146806-7

7

OBSOLETE

3

1

15

35.56
[1.400]

14

37.69
[1.484]

30

146806-6

3

NONE

4

10.16
[.400]

4

12.29
[.484]

10

146806-5

OBSOLETE

3

NONE

10

40.64
[1.600]

16

42.77
[1.684]

34

146806-4

3

11

NONE

35.56
[1.400]

14

37.69
[1.484]

30

146806-3

3

10

NONE

35.56
[1.400]

14

37.69
[1.484]

30

146806-2

3

NONE

3

30.48
[1.200]

12

32.61
[1.284]

26

146806-1

PLATING

ROW M

ROW N

POSTS OMITTED

C

B

A

NO OF POSN

PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
E. BRANDBERG
CHK
G. DUBNICZKI
APVD
G. DUBNICZKI

29-JAN-97

29-JAN-97

NAME

DIMENSIONS:
mm [INCHES]

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± 0.13[.005]
4 PLC ± -
ANGLES ± -

SEE TABLE

MATERIAL

4

WEIGHT

-

SIZE

CAGE CODE

DRAWING NO

A100779

RESTRICTED TO

-

CUSTOMER DRAWING

SCALE

1:1

SHEET

1

OF

1

REV

AA

TE Connectivity

SURFACE MOUNT HEADER ASSEMBLY,
MOD II, BREAKAWAY, VERTICAL,
DOUBLE ROW, .100 X.100 CL, .025 SQ.POST

RECOMMENDED PCB LAYOUT
FOR USE WITH .008 THICK STENCIL

4805 (3/11)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[6-146806-4](#)