

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

-,-

© COPYRIGHT - By -

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

FT

0

P

LTR

DESCRIPTION

DATE

DWN

APVD

B2

REVISED PER ECO-13-001940

01OCT2013

KH

MB

NOTES:

MATERIAL:

TERMINAL BLOCK: POLYAMIDE 66, UL94V-0, BLACK.

TERMINAL: BRASS, TIN PLATED.

SCREW: M3 STEEL, NICKEL PLATED W/ WIRE CLAMP.

ELECTRICAL:

CURRENT RATING: 10A, 300V

INSULATION WITHSTANDS: 2000V, MIN

INSULATION RESISTANCE: >2000MEGA OHM, 500V

MECHANICAL:





WIRE RANGE: 16-30AWG

RECOMMENDED TORQUE: 10 IN-LB

OPERATION TEMP: -40°C TO 105°C


UL RECOGNIZED PER US & CANADIAN STANDARDS.

1 PRELIMINARY NUMBER



RECOMMENDED PCB LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHESTOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± .02
3 PLC ± .005
4 PLC ± -
ANGLES ± -

MATERIAL

FINISH

DWN S SCHLEGEL

30MAY03

CHK S YODER

5/30/03

APVD S YODER

5/30/03

PRODUCT SPEC

APPLICATION SPEC

WEIGHT -

CUSTOMER DRAWING

STE

TE Connectivity

NAME
TERMINAL BLOCK, .250 PITCH, DUAL BARRIER
PCV STYLE

SIZE CAGE CODE DRAWING NO RESTRICTED TO

A3 00779 C-1546657

SCALE 2:1

SHEET 1 OF 1

REV B2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1546657-2](#)