


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION		DATE	APVD
AD	00		E	REVISED PER	ECO-14-000264	14JUL2014	NK



- 1
- POINT OF MEASUREMENT FOR PLATING THICKNESS

2

3

4

5

6

7

8

9

9	OBSOLETE	8	7	14	14	63.09 [2.484]	60.96 [2.400]	24	50	5-147067-1
	6		4	2	—	30.07 [1.184]	27.94 [1.100]	11	24	147067-4
	6		4	—	2	12.29 [.484]	10.16 [.400]	4	10	147067-3
	6		4	1	—	12.29 [.484]	10.16 [.400]	4	10	147067-2
			4	14	14	63.09 [2.484]	60.96 [2.400]	24	50	147067-1
	REMARKS	PLATING	ROW Y	ROW X	C	B	A	NO OF POS	ASSEMBLY PART NUMBER	
POSTS OMITTED										

RECOMMENDED HOLE LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± 0.13 [.005]
4 PLC ± -
ANGLES ± -
FINISH SEE TABLE

DWN
B. HAYMAKER
29JUN98

CHK
J. GESFORD
29JUN98

APVD
J. GESFORD
29JUN98

PRODUCT SPEC

APPLICATION SPEC

WEIGHT -

CUSTOMER DRAWING

TE Connectivity

NAME
ASSEMBLY, MOD II, HEADER, BREAKAWAY, DOUBLE ROW, RIGHT ANGLE, .100X.100 CL, WITH .025 SQUARE POSTS, SELECT LOAD

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=147067

RESTRICTED TO
-

SCALE
4:1

SHEET
1 OF 1

REV
E

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[147067-1](#)