







P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—








2.00–3.00 [.079–.118]	21.2+0.1 [.835+.004]	37.0+0.2 [1.457+.008]
1.25–2.00 [.049–.079]	21.2+0.1 [.835+.004]	36.8+0.2 [1.449+.008]
.075–1.25 [.030–.049]	21.2+0.1 [.835+.004]	36.6+0.2 [1.441+.008]
PANEL THICKNESS	Y	X



OBSOLETE ~~1571100-5~~
SHOWN



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.BINNER CHK D.ROHDE APVD D.ROHDE PRODUCT SPEC APPLICATION SPEC — WEIGHT —		25FEB2002 16NOV05 16NOV05 NAME POWER ROCKER SWITCH, 21.2mm X 36.6mm MIN PANEL CUT-OUT SIZE SINGLE POLE, DOUBLE THROW, NON-ILLUMINATED SIZE A2		TE Connectivity 	
DIMENSIONS: mm [INCHES] 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± — FINISH		MATERIAL 		RESTRICTED TO —	
		CUSTOMER DRAWING		SCALE 2:1		SHEET 2 OF 4	
				REV D			




THIS DRAWING IS UNPUBLISHED.
RELEASED FOR PUBLICATION
ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
—	—	SEE SHEET 1	—	—	—

2.00–3.00	[.079–.118]	21.2+0.1	[.835+.004]	37.0+0.2	[1.457+.008]
1.25–2.00	[.049–.079]	21.2+0.1	[.835+.004]	36.8+0.2	[1.449+.008]
.075–1.25	[.030–.049]	21.2+0.1	[.835+.004]	36.6+0.2	[1.441+.008]
PANEL THICKNESS		Y		X	

SWITCH FUNCTION D1
CIRCUIT DIAGRAM



OBSOLETE 1-1571100-0
SHOWN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.BINNER 25FEB2002	TE Connectivity		
DIMENSIONS: mm [INCHES]		CHK D.ROHDE 16NOV05			
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD D.ROHDE 16NOV05	NAME POWER ROCKER SWITCH, 21.2mm X 36.6mm MIN PANEL CUT-OUT SIZE		
		PRODUCT SPEC	SINGLE POLE, DOUBLE THROW, NON-ILLUMINATED		
		APPLICATION SPEC	RESTRICTED TO		
MATERIAL 1	2	WEIGHT —	SIZE A2	CAGE CODE 00779	DRAWING NO C=1571100
CUSTOMER DRAWING			SCALE 2:1	SHEET 3 of 4	REV D

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1571100-2](#)