

4

3

2

1

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
F	00		B	6.76 MIN WAS 6.76 MAX	07FEB2007	GR	GR
			C	ECR 07-025006	26OCT2007	JT	GR

6.9MAX

COUPE C - C

3.9MAX

FOR INSULATION
Ø 1.4 - 2.67

Ø 5.15 MAX

STAMP : AMP 18 16

SLEEVE

INSULATION

SERRATIONS

BODY 0.80±0.03 TONGUE
THICKNESS

Ø 4.34±0.08
FOR #8 OR M4 STUD

1.3MAX


7.92±0.15

0.79 MIN

6.76 MIN

18.39 MAX

22.43 MAX



SCALE 3:1

WIRE
TERMINAL

1577632-1

BODY : COPPER ANNEALED
FINISH : NICKEL PLATED


SLEEVE : COPPER ANNEALED
FINISH : NICKEL PLATED

INSULATION : PEEK
COLOR : ORANGE

DESCRIPTION

PART NUMBER

MATERIAL & FINISH

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN JJ. DESPRETZ 22FEB2006		tyco Electronics		Tyco Electronics France SAS 95300 Pontoise, France							
DIMENSIONS: mm		CHK G. ROBERT 22FEB2006				NAME TERMINAL, PEEK PIDG STRATO, 18-16 AWG -							
		APVD Y. PETRONIN 22FEB2006		SIZE A3				CAGE CODE 00779		DRAWING NO C-1577632		RESTRICTED TO -	
		PRODUCT SPEC 108-15356											
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±0.3 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±5		APPLICATION SPEC 114-15102		WEIGHT 0,95 gr		CUSTOMER DRAWING		SCALE 8:1		SHEET 1 OF 1		REV C	
		MATERIAL SEE TABLE											

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1577632-1](#)