





REVISIONS					
P	LYR	DESCRIPTION	DATE	DWN	APVD
B		REV PER ECO 18-005353	5-3-18	CT	AS



SEE SHEET 2 FOR NOTES

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C SCHOLL	2 JUL 12	TE Connectivity	
DIMENSIONS:		CHK M STORRY	2 JUL 12		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD M STORRY	2 JUL 12	NAME RECEPTACLE ASSY, MCKS, ST1 STRAIGHT	
0 PLC ± -		PRODUCT SPEC		TERMINATION, PCB MOUNT, 2 ROW,	
1 PLC ± -		APPLICATION SPEC		PER MIL-DTL-83513/25	
2 PLC ± .010		SIZE	A2	CAGE CODE	
3 PLC ± .005		WEIGHT	-	DRAWING NO	
4 PLC ± -		CUSTOMER DRAWING	98278	RESTRICTED TO	
ANGLES ± 1°		SCALE	4:1	SHEET	
FINISH		REV	B	1 of 2	

REVISIONS				
P	LYR	DESCRIPTION	DATE	DWN APVO
-	-	SEE SHEET 1	-	-

TE PART NUMBER	MIL-DTL-83513 PIN	MCKS DESCRIPTION	SHELL FINISH $\triangle 1$	HARDWARE $\triangle 3$	L DIM $\pm$.015
1532279-1	M83513/25-F01CN	MCKS-C2-B-37SST1	CADMIUM	NONE	.109
1532279-2	M83513/25-F01CP	MCKS-C2-P-37SST1	CADMIUM	JACKPOSTS	.109
1532279-3	M83513/25-F01NN	MCKS-N1-B-37SST1	NICKEL	NONE	.109
1532279-4	M83513/25-F01NP	MCKS-N1-P-37SST1	NICKEL	JACKPOSTS	.109
1532279-5	M83513/25-F02CN	MCKS-C2-B-37SST1A	CADMIUM	NONE	.140
1532279-6	M83513/25-F02CP	MCKS-C2-P-37SST1A	CADMIUM	JACKPOSTS	.140
1532279-7	M83513/25-F02NN	MCKS-N1-B-37SST1A	NICKEL	NONE	.140
1532279-8	M83513/25-F02NP	MCKS-N1-P-37SST1A	NICKEL	JACKPOSTS	.140
1532279-9	M83513/25-F03CN	MCKS-C2-B-37SST1B	CADMIUM	NONE	.172
1-1532279-0	M83513/25-F03CP	MCKS-C2-P-37SST1B	CADMIUM	JACKPOSTS	.172
1-1532279-1	M83513/25-F03NN	MCKS-N1-B-37SST1B	NICKEL	NONE	.172
1-1532279-2	M83513/25-F03NP	MCKS-N1-P-37SST1B	NICKEL	JACKPOSTS	.172

- $\triangle 1$ SHELL MATERIAL: 6061-T6 ALUMINUM
FINISH OPTIONS:
ELECTROLESS NICKEL PLATED PER SAE-AMS-C-26074 OR SAE AMS 2404 OR CADMIUM PLATED PER SAE-AMS-QQ-P-416 WITH YELLOW CHROMATE
INSULATOR: LIQUID CRYSTAL POLYMER (LCP)
HARDWARE: 300 SERIES STAINLESS STEEL
TB BOX: POLYPHENYLENE SULFIDE (PPS) AND EPOXY POTTING
- $\triangle 2$ TERMINATION: 24AWG GOLD PLATED COPPER WIRE, Sn63Pb37 SOLDER DIPPED UP TO MOUNTING SURFACE AT A MINIMUM
- $\triangle 3$ JACKPOST HARDWARE SHALL BE PERMANENTLY INSTALLED AS SHOWN WHEN REQUIRED BY THE MIL PIN. JACKPOST DIMENSIONS AND REQUIREMENTS ARE DEFINED IN MIL-DTL-83513/5.
- $\triangle 4$ CONNECTOR SHALL BE MARKED IN ACCORDANCE WITH METHOD I OF MIL-STD-1285. MARKING SHALL CONTAIN THE MILITARY PIN, CAGE CODE (OR TE), AND DATE CODE. EXAMPLE: M83513/25-F0XXX TE YYWW (WHERE XXX IS PART OF THE PIN SHOWN IN THE "MIL-DTL-83513 PIN" COLUMN OF THE PART NUMBER TABLE, AND YYWW IS THE DATE CODE). THE MARKING MUST BE PRINTED ON THE FLANGE. TEXT HEIGHT SHALL BE .035 INCH MINIMUM.
- $\triangle 5$ POSITION 1 SHALL BE INDICATED BY AN IDENTIFIABLE MARK, LOCATED APPROXIMATELY AS SHOWN ON THE POSITION 1 SIDE OF THE CONNECTOR FLANGE. THIS MARK SHALL BE INCLUDED AS PART OF THE PART MARKING INFORMATION.
- $\triangle 6$ TERMINAL IDENTIFICATION NUMBERS AS SHOWN DO NOT ACTUALLY APPEAR ON THE PART (FOR IDENTIFICATION ONLY)
- 7 ALL REQUIREMENTS CONFORM TO MIL-DTL-83513/25. SEE MIL-SPEC FOR DETAILED INTERFACE DIMENSIONS AND SUGGESTED PCB LAYOUTS

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C SCHOLL 2 JUL 12	TE Connectivity	
DIMENSIONS: INCHES		APVO M STORRY 2 JUL 12	NAME RECEPTACLE ASSY,MCKS,ST1 STRAIGHT TERMINATION,PCB MOUNT,2 ROW, PER MIL-DTL-83513/25	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC $\pm$ - 1 PLC $\pm$ - 2 PLC $\pm$.010 3 PLC $\pm$.005 4 PLC $\pm$ - $\pm$.1"		PRODUCT SPEC: APPLICATION SPEC: WEIGHT -	SIZE A2	CAGE CODE 98278
MATERIAL SEE NOTES		DRAWING NO 1532279		RESTRICTED TO -
FINISH SEE NOTES		CUSTOMER DRAWING		SCALE 4:1
		SHEET 2 of 2		REV B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1532279-7](#)