

PHYSICAL PROPERTIES:  
HOUSING MATERIAL: THERMOPLASTIC, PC  
FLAMABILITY: UL94V-0  
COLOR: BLACK

TERMINAL:  
TERMINALS: BRASS, TIN PLATED  
SCREWS: 6-32 STEEL, NICKEL PLATED

MECHANICAL:  
PITCH: .437  
WIRE RANGE: 14-22 AWG  
RECOMMENDED TIGHTENING TORQUE: 12IN-LB

ELECTRICAL PROPERTIES:  
MAX CURRENT: 25A  
OPERATING VOLTAGE: 300V

ENVIRONMENTAL PROPERTIES:  
OPERATING TEMP: -40°C TO 120°C

- 1


SEE FIGURE.
- 2

PRELIMINARY PART NUMBER.
- 3

STAINLESS STEEL SCREWS.
- 4

WHITE INK STAMP.
- 5


TE CONNECTIVITY LOGO LOCATED APPROXIMATE AREA.




	5.646	5.992	12	4-1546670-2
	9.142	9.488	20	2-1546670-0
	8.705	9.051	19	1-1546670-9
2	8.268	8.614	18	3-1546670-0
	8.268	8.614	18	1-1546670-8
	7.831	8.177	17	1-1546670-7
	7.394	7.740	16	1-1546670-6
	6.957	7.303	15	1-1546670-5
	6.520	6.866	14	1-1546670-4
	6.083	6.429	13	1-1546670-3
	5.646	5.992	12	1-1546670-2
	5.209	5.555	11	1-1546670-1
4	4.772	5.118	10	4-1546670-3
2	4.772	5.118	10	3-1546670-8
	4.772	5.118	10	1-1546670-0
2	4.335	4.681	9	3-1546670-5
2	4.335	4.681	9	3-1546670-2
	4.335	4.681	9	1546670-9
1	3.898	4.244	8	4-1546670-1
3	3.898	4.244	8	3-1546670-6
2	3.898	4.244	8	3-1546670-4
2	3.898	4.244	8	3-1546670-3
	3.898	4.244	8	1546670-8
	3.461	3.807	7	1546670-7
1	3.024	3.370	6	3-1546670-1
	3.024	3.370	6	1546670-6
1	2.587	2.933	5	2-1546670-8
1	2.587	2.933	5	2-1546670-7
	2.587	2.933	5	1546670-5
2	2.496	2.933	4	3-1546670-9
1	2.150	2.496	4	2-1546670-9
	2.150	2.496	4	1546670-4
	1.713	2.059	3	1546670-3
	1.276	1.622	2	1546670-2
	DIM B	DIM A	NO OF POS	PART NUMBER

LOC	DIST	REVISIONS				
FT	0	P	LTR	DESCRIPTION	DATE	DWN
		-	-	SEE SHEET 1	-	-
				APVD		


DOUBLE SIDED, DOUBLE HOLE  
QC TAB, QTY 5



DOUBLE SIDED, DOUBLE HOLE  
QC TAB, QTY 5




JUMPER, QTY 1





DOUBLE SIDED, DOUBLE HOLE  
45° QC TAB, QTY 9



DOUBLE SIDED, DOUBLE HOLE  
90° QC TAB, QTY 9



JUMPER QTY 2



.250  
TYP




2-1546670-7


2-1546670-8

3-1546670-2



DOUBLE SIDED, DOUBLE HOLE  
QC TAB, QTY 5



SINGLE SIDED, DOUBLE HOLE  
QC TAB, QTY 6





SINGLE SIDED, SINGLE HOLE  
QC TAB, QTY 2



2-1546670-9


.250  
TYP



3-1546670-1


DOUBLE SIDED, DOUBLE HOLE  
FLAT QC TAB, QTY 8.

JUMPER, QTY 2




DOUBLE SIDED, DOUBLE HOLE  
45° QC TAB, QTY 6

DOUBLE SIDED, DOUBLE HOLE  
90° QC TAB, QTY 4




3-1546670-3


SINGLE SIDED, DOUBLE HOLE  
QC TAB, QTY 18




.250  
TYP




3-1546670-0





DOUBLE SIDED, DOUBLE HOLE  
FLAT QC TAB, QTY 8.



3-1546670-4



11.764	12.110	26	2-1546670-6
11.327	11.673	25	2-1546670-5
10.90	11.236	24	2-1546670-4
10.453	10.799	23	2-1546670-3
10.016	10.362	22	2-1546670-2
9.579	9.925	21	2-1546670-1
9.142	9.488	20	3-1546670-7
DIM B	DIM A	NO OF POS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN S SCHEGEL 4/4/03	 TE Connectivity				
			CHK C RICHARD 4/4/03					
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:  0 PLC ± - 1 PLC ± - 2 PLC ± .01 3 PLC ± .005 4 PLC ± - ANGLES ± 3°	APVD C RICHARD 4/4/03	NAME  DOUBLE ROW BARRIER STRIP W/ BINDING HD SCREW, .437 SPACING				
			PRODUCT SPEC —					
			APPLICATION SPEC —					
			SIZE A2	CAGE CODE 00779	DRAWING NO C=1546670	RESTRICTED TO —		
			CUSTOMER DRAWING			SCALE NTS	SHEET 2 of 3	REV K18
			MATERIAL —	FINISH —	WEIGHT —			

THIS DRAWING IS UNPUBLISHED.



RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.




© COPYRIGHT - By -

LOC	DIST	REVISIONS					
FT	0	P	LTR	DESCRIPTION	DATE	DWN	APVD
			—	SEE SHEET 1	—	—	—


D



3-1546670-5




4-1546670-3




SINGLE SIDED, DOUBLE HOLE 45° QC TAB, QTY 10

SINGLE SIDED, DOUBLE HOLE 90° QC TAB, QTY 10




SINGLE SIDED, DOUBLE HOLE FLAT QC TAB, QTY 10



C




3-1546670-7




3-1546670-8




3-1546670-9



B



4-1546670-1



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	S	SCHEGEL	4/4/03			TE Connectivity	
DIMENSIONS: INCHES		CHK	C	RICHARD	4/4/03			NAME	
		APVD	C	RICHARD	4/4/03	PRODUCT SPEC		DOUBLE ROW BARRIER STRIP W/ BINDING HD SCREW, .437 SPACING	
		APPLICATION SPEC		WEIGHT		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
MATERIAL		FINISH		CUSTOMER DRAWING		A2	00779	C-1546670	-
						SCALE	NTS	SHEET	3 OF 3
								REV	K18

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-1546670-6](#)