





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AF	50		E2	REVISED PER ECR-10-013696	19AUG10	HMR	GJ

1. SPECIFICATIONS:  
MAGNET WIRE #18 - #34 AWG, 1.02MM(.040)  
-0.16MM(.006) DIA. COPPER.
2. POCKET RECOMMENDATION: #1601427
3. TERMINAL TO BE APPLIED PER TYCO ELECTRONICS  
SPECIFICATION #114-13166 FIGURE 15.
4. SELECTIVE PLATE THIS AREA:  
0.00076 [.00030] MIN GOLD PLATE OVER  
0.00127 [.00050] MIN NICKEL UNDERPLATE  
OVER ENTIRE TERMINAL.
5. PRELIMINARY - NOT FOR PRODUCTION.
6. TWO(2) TERMINALS SHOWN FOR ILLUSTRATION  
PURPOSES ONLY.



—		—		—	
<div>4</div>		—		<div>5</div> 2-1601018-3	
PRE-TIN PLATE OVER COPPER UNDERPLATE		131-042-014		2-1601018-2	
<div>4</div>		—		<div>5</div> 1601018-3	
PRE-TIN PLATE OVER COPPER UNDERPLATE		131-044-014		1601018-2	
UNPLATED		—		<div>5</div> 1601018-1	
FINISH		REFERENCE PART NUMBER		TE PART NUMBER	
THIS DRAWING IS A CONTROLLED DOCUMENT.		<div>DWN</div> J.WELLER 11JAN2002			
		<div>CHK</div> M.FEHER 11JAN2002			
		<div>APVD</div> K.RANDOLPH 11JAN2002			
<div>DIMENSIONS:</div> <div>mm [INCHES]</div>		<div>NAME</div>			
<div><div><div><div></div><div></div><div></div></div><div></div></div></div>		STANDARD RANGE WIRE TO 4.75[.187] BARB TAB SIAMEZE TERMINAL			
<div>1 PLC ± —</div> <div>2 PLC ± —</div> <div>3 PLC ± 0.13[.005]</div> <div>4 PLC ± —</div> <div>4 PLC ± —</div> <div>FINISH ± 2'</div>		<div>PRODUCT SPEC</div> <div>108-2085</div> <div>APPLICATION SPEC</div> <div>3</div>			
MATERIAL		WEIGHT		RESTRICTED TO	
BRASS, FULL HARD		—		—	
SEE TABLE		CUSTOMER DRAWING		SCALE 9:1 SHEET 1 OF 1 REV E2	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-1601018-2](#)