


DRAWING MADE IN AMERICAN PROJECTION


REVISIONS				
LTR	DESCRIPTION	DATE	DWN	APVD
E2	REVISED PER ECR-20-012400	24SEP20	SS	EW

NUMBER
C-160826



NOTES:

- 1 FOR USE ON MINIATURE APPLICATOR (LEFT-RIGHT FEED).
- 2 FOR USE ON MINIATURE APPLICATOR (LEFT-RIGHT FEED) AMPOMATOR APPLICATION
- 3 GENERAL TOLERANCE ± 0.3 (.012)
- 4 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 5 ONLY WELDED SPLICES ALLOWED



0.5(.020) MAX. CUT OFF

DIMENSIONS IN M.M. DO NOT SCALE PRINT

6-160826-8	PH. BRONZE	PRE-TIN PLATED
6-160826-7	BRASS	PRE-TIN PLATED
160826-4	PH. BRONZE	TIN PLATED
160826-3	BRASS	TIN PLATED
160826-2	PH. BRONZE	—
160826-1	BRASS	—

CUSTOMER COPY FOR REFERENCE ONLY

©1981 BY AMP-HOLLAND N.V. ALL RIGHTS RESERVED A-MP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING.

TE TE Connectivity

WIRE RANGE 22-18 AWG 0.30-0.81 mm ²	INSUL. RANGE 0.045-1.00 DIA. 1.1-2.5 mm DIA.	FIRST USED
--	--	------------

ORDER NO.	MATERIAL	PLATING
-----------	----------	---------

SCALE	SIZE	NO	REV
N.D.S.	A	C-160826	E1

DR	DATE	DE	DATE
R.V.H.	22.4.81		

CHK	DATE	APP	DATE
[Signature]	22.4.81	[Signature]	24.2.82

NAME **POSITIVE LOCK RECEPTACLE**

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[160826-3](#) [160826-3 \(Loose Piece\)](#)