

3. 5.

LENGTH AS SPECIFIED
IN PART NUMBER

.205


(B DIM)

2X (.075)



.117

1.

1.



1. SHELL OPTIONS (TO BE SPECIFIED IN NANONICS PART NUMBER):
 METAL: 6061-T6 ALUMINUM, ELECTROLESS NICKEL PLATED PER MIL-C-26074 (STANDARD) OR GOLD PLATED PER MIL-G-45204
 303 STAINLESS STEEL, PASSIVATED PER SAE-AMS-QQ-P-35
 INSULATOR MATERIAL FOR ALL METAL SHELLS IS LIQUID CRYSTAL POLYMER (LCP) PER MIL-M-24519 OR PER ASTM D5138
 PLASTIC: LIQUID CRYSTAL POLYMER (LCP) PER MIL-M-24519 OR PER ASTM D5138
 2. STANDARD 1.00UNM CAPTIVE JACKSCREWS ARE SHOWN FOR REFERENCE ONLY AND MUST BE SPECIFIED IN THE NANONICS PART NUMBER WHEN REQUIRED. JACKSCREW MATERIAL IS 303 STAINLESS STEEL, PASSIVATED PER SAE-AMS-QQ-P-35, AND DRY LUBED PER DOD-L-85645. RETAINING RING IS 17-4 STAINLESS STEEL, PASSIVATED PER SAE-AMS-QQ-P-35. JACKSCREWS HAVE A .9mm HEX SOCKET HEAD. 1.20UNM JACKSCREWS ALSO AVAILABLE.
 3. THIS CONFIGURATION MAY BE TERMINATED WITH 28 AWG SOLID, 30 AWG STRANDED, OR SMALLER WIRE. STANDARD WIRING IS 1 TO 1.
 4. THIS CONFIGURATION WOULD HAVE THE SAME CONNECTOR TYPE TERMINATED TO EACH END OF THE JUMPER ASSEMBLY.
 5. LENGTH TOLERANCE: UP TO 25.0 INCHES, $\pm_{.00}^{+.25}$; 25.0 INCHES AND LONGER, $\pm_{.00}^{+1\%}$
 6. DIMENSIONS TYPICAL FOR BOTH CONNECTORS.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C SCHOLL		03-19-02		 Tyco Electronics Corporation Harrisburg, PA 17105	
		CHK M STORRY		03-21-02			
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD D. MORALES		NAME	
		0 PLC ± -		JUMPER ASSEMBLY, PLUG TO PLUG, TWO ROW DUALOBE, PLASTIC OR METAL		SIZE A2	
		1 PLC ± -					
		2 PLC ± .010					
		3 PLC ± .005					
		4 PLC ± -		APPLICATION SPEC		DRAWING NO	
		ANGLES ± 1°		—		CAGE CODE	
MATERIAL		FINISH		WEIGHT		—	
SEE NOTES		SEE NOTES		CUSTOMER DRAWING		SCALE 6:1	
						SHEET 1 OF 1	
						REV C	

1589737

B

A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[7-1589673-2](#)