



LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
AD	00	C		REVISED PER ECO-13-002771	04MAR2013	KH
		D		REVISED PER ECO-19-009248	10JUL2019	AP



○ = SIGNAL
⊗ = GROUND
RECOMMENDED PC BOARD LAYOUT
DAUGHTER BOARD
COMPONENT SIDE SHOWN
SCALE 6:1



△ MATERIAL:
CONTACT AND SHIELD - PHOS BRONZE
HOUSING AND CHICKLET - LCP, UL 94V-0, COLOR - BLACK

△ FINISH:
CONTACT AREA FINISH CONFORMS TO THE REQUIREMENTS
OF TE PRODUCT SPECIFICATION 108-2303; BASED ON
TELCORDIA GR-1217-CORE FOR SYSTEM QUALITY
LEVEL III APPLICATIONS IN CONTROLLED
ENVIRONMENTS (CENTRAL OFFICE).
COMPLIANT PIN AREA- 0.5μm MIN MATTE TIN OVER 1.27μm MIN NICKEL.
SHIELD 1.27μm MIN NICKEL.

△ CONNECTOR MARKED ON EITHER SIDE OF HOUSING WITH PART NUMBER,
DATE CODE AND STANDARD IN APPROXIMATE AREA SHOWN.

△ DIMENSION APPLIES TO CENTERLINE OF THRU HOLE.



△ DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.

6. CONTACT AREA LUBRICATED WITH BELLCORE APPROVED LUBRICANT.
TECHNICAL REFERENCE: GR-1217-CORE, ISSUE 1, NOVEMBER 1995.

△ REFERENCE APPLICATION SPEC 114-13202 FOR RECOMMENDED PLATED
THRU HOLE DIAMETER AND PLATING THICKNESSES.

△ THE GROUNDS IN COLUMNS 1-15 ARE COMMONED.

△ SHOWN LOGO OR OTHER TE OWNED LOGOS IN APPROXIAMATE AREA.



2065634-1
PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. HUMBERT 23MAR2009	TE Connectivity	
DIMENSIONS:		CHK R. PATTERSON 23MAR2009		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD R. PATTERSON 23MAR2009	NAME	RECEPTACLE ASSEMBLY, 5 PAIR, 16 COLUMN
	0 PLC ±	PRODUCT SPEC	SIZE	A100779
	1 PLC ±	APPLICATION SPEC	CAGE CODE	C=2065634
	2 PLC ±	WEIGHT	DRAWING NO	RESTRICTED TO
	3 PLC ±	CUSTOMER DRAWING	SCALE	6:1
	4 PLC ±		SHEET	1 OF 1
ANGLES	±		REV	D
FINISH	△			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2065634-1](#)