


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	C	REVISED PER ECR-19-016494	23OCT2019	F.Z	R.B



△ COPPER ALLOY: FINISH; CONTACT AREA Au 0.38umMIN, OVER Ni 1.27umMIN	1903111-2
MATERIAL	PART NO

WIRE RANGE mm <sup>2</sup> 0.05~0.09	AWG#30~#28	INSULATION DIA Ø0.6~Ø1.2
THIS DRAWING IS A CONTROLLED DOCUMENT.		
DWN M. MAEBASHI 11APR2006		
CHK T. KUDO 11APR2006		
APVD D. MITSUGI 11APR2006		
PRODUCT SPEC 108-78268		
APPLICATION SPEC 114-5377		
WEIGHT 0.123 g		
CUSTOMER DRAWING		
SCALE 10:1		
SHEET 1 OF 1		
REV C		

1. THE SHAPE, SIZE AND POSITION OF THE CHARACTER SHOW THE OUTLINE. THEY DON'T SHOW DETAILS.
2. ALTERNATIVE TE LOGO FOR DIFFERENT DIE.
3. ALTERNATIVE ID MARK, WITH "■" OR NO MARK.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1903111-2](#)