

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASE	31OCT2016	JY	SH
	B	ADD NEW PN 4-2170808-7	21MAY2019	JY	SH

HEAT SINK CLIP

HEAT SINK

LIGHT PIPE

1x2 CAGE ASSEMBLY

2-2170808-1 AS SHOWN
SCALE 2:1

1. COMPONENTS
CAGE ASSEMBLY: NICKEL-SILVER ALLOY
HEAT SINK: ALUMINUM/BLACK ANODIZE
HEAT SINK CLIP: STAINLESS STEEL
EMI SPRING: COPPER ALLOY/NICKEL PLATE
LIGHT PIPE: CLEAR POLYCARBONATE

2. REFERENCE APPLICATION SPECIFICATION 114-32023
FOR RECOMMENDED DRILL HOLE DIAMETER AND
PLATING THICKNESS

3. DATUM AND BASIC DIMENSION ESTABLISHED BY CUSTOMER

4. DIMENSION APPLIES WITH MODULE INSERTED IN CAGE

5. HEAT SINKS, HEAT SINK CLIPS AND LIGHT PIPES
ARE SHIPPED ASSEMBLED ON CAGE

6. MINIMUM PC BOARD THICKNESS: SINGLE SIDED: 1.57 MIN
DOUBLE SIDED: 2.20 MIN

7. DATUM -A- IS TOP SURFACE OF THE HOST BOARD.
8. THESE HOLES ARE OPTIONAL WHEN THE REAR PINS ARE REMOVED.
9. MATES WITH QSFP28 MSA COMPATIBLE TRANSCEIVER.
10. DATE CODE (YYWWD) MARKED APPROXIMATELY AS SHOWN.
11. NOTED DIMENSIONS ONLY APPLY TO CAGE ASSEMBLY WITH LIGHT PIPE.
12. PRELIMINARY PART - NOT RELEASED FOR PRODUCTION.

38.50 REF

2X 18.75±0.10

2X 8.90±0.10

7.88

18.50

REAR PIN
OPTIONAL

SCALE 2:1

67.75 REF

B REF

12.79 REF

11.60 REF

9.65 REF

13.40

4.50

SEE DETAIL E

SECTION A-A
D-D

1.01 A MAX

15.11 REF

2.05 TYP

CL OF GUIDE POST

DETAIL E
SCALE 4:1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN BING LIU 16SEP2014
CHK JASON YANG 16SEP2014
APVD -

PRODUCT SPEC 108-19428
APPLICATION SPEC 114-32023
WEIGHT -

CUSTOMER DRAWING

TE Connectivity

NAME RECEPTACLE CAGE ASSEMBLY
1X2, QSFP28, THRU BEZEL, SPRING
WITH HEAT SINKS AND LIGHT PIPES


SIZE A2 CAGE CODE 00779 DRAWING NO C-2170808

RESTRICTED TO -


SCALE 1:1 SHEET 1 OF 9 REV B

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-


HEAT SINK OPTION



PCI HEAT SINK HEIGHT
SCALE 1:1




SAN HEAT SINK HEIGHT
SCALE 1:1




NETWORKING HEAT SINK HEIGHT
SCALE 1:1


LIGHT PIPE OPTION



SINGLE LIGHT PIPE
SCALE 1:1




DUAL LIGHT PIPE
SCALE 1:1




QUAD LIGHT PIPE
SCALE 1:1

OF REAR PIN OPTION



1 REAR PIN
SCALE 3:1



0 REAR PIN
SCALE 3:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN BING LIU CHK JASON YANG APVD -	16SEP2014 16SEP2014 -	TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±0.25 2 PLC ±0.2 3 PLC ±- 4 PLC ±- ANGLES ±- FINISH		NAME RECEPTACLE CAGE ASSEMBLY 1X2, QSFP28, THRU BEZEL, SPRING WITH HEAT SINKS AND LIGHT PIPES	
MATERIAL SEE NOTES		PRODUCT SPEC 108-19428 APPLICATION SPEC 114-32023 WEIGHT -		SIZE A200779	CAGE CODE C-2170808
		CUSTOMER DRAWING		SCALE 1:1	SHEET 2 OF 9
				REV B	

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

0	3.4	16.0	SAN	COATED QUAD LP	5-2170808-5
1	2.9	18.4	CUSTOMIZED	QUAD LP	4-2170808-7
0	2.9	23.0	NETWORKING	QUAD LP	4-2170808-6
0	2.9	16.0	SAN	QUAD LP	4-2170808-5
0	2.9	13.7	PCI	QUAD LP	4-2170808-4
1	2.9	23.0	NETWORKING	QUAD LP	4-2170808-3
1	2.9	16.0	SAN	QUAD LP	4-2170808-2
1	2.9	13.7	PCI	QUAD LP	4-2170808-1
1	4.5	13.7	PCI	SHORTER, QUAD LP	4-2170808-0
0	2.9	23.0	NETWORKING	DUAL LP	2-2170808-6
0	2.9	16.0	SAN	DUAL LP	2-2170808-5
0	2.9	13.7	PCI	DUAL LP	2-2170808-4
1	2.9	23.0	NETWORKING	DUAL LP	2-2170808-3
1	2.9	16.0	SAN	DUAL LP	2-2170808-2
1	2.9	13.7	PCI	DUAL LP	2-2170808-1
0	2.9	23.0	NETWORKING	SINGLE LP	2170808-6
0	2.9	16.0	SAN	SINGLE LP	2170808-5
0	2.9	13.7	PCI	SINGLE LP	2170808-4
1	2.9	23.0	NETWORKING	SINGLE LP	2170808-3
1	2.9	16.0	SAN	SINGLE LP	2170808-2
1	2.9	13.7	PCI	SINGLE LP	2170808-1
# OF REAR PIN	DIM B (LP EXTRUDE)	DIM A (PRODUCT HEIGHT)	APPLICATION	LIGHT PIPE OPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-
1 PLC ±0.25
2 PLC ±0.2
3 PLC ±-
4 PLC ±-
ANGLES ±-
FINISH

MATERIAL

SEE NOTES

-

DWN 16SEP2014
BING LIU

CHK 16SEP2014
JASON YANG

APVD -

PRODUCT SPEC
108-19428

APPLICATION SPEC
114-32023

WEIGHT -

CUSTOMER DRAWING

TE Connectivity

NAME

RECEPTACLE CAGE ASSEMBLY
1X2, QSFP28, THRU BEZEL, SPRING
WITH HEAT SINKS AND LIGHT PIPES

SIZE

A2

CAGE CODE

00779

DRAWING NO

2170808

RESTRICTED TO

-

SCALE

1:1

SHEET

3

OF


9

REV

B


1471-9 (3/13)

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



CAGE ASSEMBLY IS OMITED

SINGLE SIDE MOUNTING
SCALE 2:1



CAGE ASSEMBLY IS OMITED

SINGLE SIDE MOUNTING
SCALE 2:1

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

©


COPYRIGHT 20

BY -


ALL RIGHTS RESERVED.

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-




CAGE ASSEMBLY IS OMITED



CAGE ASSEMBLY IS OMITED



BELLY TO BELLY MOUNTING
SCALE 2:1




BELLY TO BELLY MOUNTING
SCALE 2:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN BING LIU 16SEP2014	TE Connectivity			
		CHK JASON YANG 16SEP2014				
DIMENSIONS:		APVD -	NAME RECEPTACLE CAGE ASSEMBLY 1X2, QSFP28, THRU BEZEL, SPRING WITH HEAT SINKS AND LIGHT PIPES			
mm		PRODUCT SPEC 108-19428	SIZE A200779			
		APPLICATION SPEC 114-32023	CAGE CODE C-2170808			
MATERIAL SEE NOTES		WEIGHT -	DRAWING NO -			
		CUSTOMER DRAWING	RESTRICTED TO -			
			SCALE 1:1 SHEET 5 OF 9 REV B			

1471-9 (3/13)


P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-




RECOMMENDED PCB LAYOUT
BELLY TO BELLY TYPE
PCB TOLERANCE: ± 0.05
SCALE 3:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 16SEP2014 BING LIU		 TE Connectivity	
		CHK 16SEP2014 JASON YANG			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME RECEPTACLE CAGE ASSEMBLY 1X2, QSFP28, THRU BEZEL, SPRING WITH HEAT SINKS AND LIGHT PIPES	
		APVD -			
		PRODUCT SPEC 108-19428			
		APPLICATION SPEC 114-32023			
MATERIAL SEE NOTES		FINISH SEE NOTES		SIZE A2	CAGE CODE 000779
		WEIGHT -		DRAWING NO C-2170808	RESTRICTED TO -
		CUSTOMER DRAWING		SCALE 1:1	SHEET 7 of 9
				REV B	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN BING LIU 16SEP2014	 TE Connectivity	
		CHK JASON YANG 16SEP2014		
DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD	NAME	
mm		PRODUCT SPEC	RECEPTACLE CAGE ASSEMBLY 1X2, QSFP28, THRU BEZEL, SPRING WITH HEAT SINKS AND LIGHT PIPES	
	0 PLC ±	108-19428		
	1 PLC ±0.25	APPLICATION SPEC		
	2 PLC ±0.2	114-32023	SIZE	CAGE CODE
	3 PLC ±	WEIGHT	DRAWING NO	
	4 PLC ±		RESTRICTED TO	
MATERIAL	FINISH		A2	
SEE NOTES	SEE NOTES		00779	
-	-	CUSTOMER DRAWING	C-2170808	
			SCALE	SHEET
			1:1	8 of 9
				REV B



THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
BING LIU
16SEP2014

CHK
JASON YANG
16SEP2014

APVD
-

PRODUCT SPEC
108-19428

APPLICATION SPEC
114-32023

WEIGHT
-

CUSTOMER DRAWING

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±
1 PLC	±0.25
2 PLC	±0.2
3 PLC	±
4 PLC	±
ANGLES	±
FINISH	-

MATERIAL
SEE NOTES
-

SEE NOTES
-

NAME
RECEPTACLE CAGE ASSEMBLY
1X2, QSFP28, THRU BEZEL, SPRING
WITH HEAT SINKS AND LIGHT PIPES

SIZE
A200779

CAGE CODE
C-2170808

DRAWING NO
-

RESTRICTED TO
-

SCALE
1:1

SHEET
9 OF 9

REV
B

TE Connectivity

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[4-2170808-3](#)