

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVO
	L	REVISED PER ECO-15-012365	17NOV2015	NK	MZ
	M	REVISED PER ECO-17-013723	21SEP2017	RS	MZ
	N	REVISED PER ECO-19-015808	22OCT2019	RS	MZ

The image contains two sets of technical drawings for louvers.

STYLE B (MALE)

- Top View:** A rectangular louver with a width of .20. It features a series of horizontal, slightly curved louvers.
- Side View:** A circular cross-section showing the louver's profile. The outer diameter is labeled (FREE DIA).

STYLE C (STRIP)

- Top View:** A rectangular louver with a length labeled LENGTH MIN. It features a series of vertical, slightly curved louvers. A triangle with the number 14 is shown in the upper left corner. The width is labeled .20.
- Side View:** A cross-section showing the louver's profile. The height is labeled LH (LOUVER HEIGHT).

- 1 FINISH—SILVER PLATE 200uIN THICK MIN.
- 2 FINISH—NICKEL PLATE 40uIN THICK MIN.
- 3 FINISH—GOLD PLATE 10uIN THICK MIN.
- 4 FINISH—GOLD PLATE 50uIN THICK MIN.
- 5 FINISH—GOLD PLATE 20uIN THICK MIN.
- 6 FINISH—GOLD PLATE 200uIN THICK MIN.
- 7 FINISH—COPPER PLATE 10uIN THICK MIN.
- 8
- 9
- 10
- 11 PLATING NOTES ARE TO BE INTERPRETED AS FOLLOWS, 6—8 AS 6 OVER 8.
- 12 MATERIAL—CDA172, BeCu.
- 13 MATERIAL—STAINLESS STEEL.
- 14 PRODUCT IS SOLD BY THE FOOT.
- 15 72 INCH STRIP WOUND TO ONE INCH INSIDE DIAMETER.
- 16 PRELIMINARY PART NO.
- 17 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN —		 TE Connectivity											
		CHK J.TURNER 08-04-93													
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME CONTACT BAND, LAV MALE											
		APVD —													
		PRODUCT SPEC —													
		APPLICATION SPEC —													
0 PLC ± — 1 PLC ± — 2 PLC ± .02 3 PLC ± .010 4 PLC ± — ANGLES ± —		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO							
MATERIAL SEE TABLE		FINISH SEE TABLE		WEIGHT —		A2		00779		C-192045		—			
CUSTOMER DRAWING						SCALE		1:1		SHEET		1 OF 2		REV N	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-192045-9](#)