



LOC		DIST		REVISIONS			
A	66	P	LTR	DESCRIPTION	DATE	DWN	APVD
		-	-	SEE SHEET 1	-	-	-


FEED TYPE
MECHANICAL






PNEUMATIC




SERVO
LATCH PLATE




CAM POSITIONS



TERMINAL SUPPORT LOCATION



HOLDDOWN SET-UP



FEED TRACK POSITION
GUIDE BY INSULATION BARREL

ATLANTIC VERSION
Shown on sheets 1 of 4 & 2 of 4
(Pacific version shown on sheets 3 of 4 & 4 of 4)

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DWN		10JUL2012		TE Connectivity	
mm		0 PLC ±0.1		CHK		10JUL2012		Harrisburg, PA 17105-3608	
Ø		1 PLC ±0.1		APPD		10JUL2012		NAME	
MATERIAL		2 PLC ±0.02		6		BAILEY		Ocean Side Feed	
		3 PLC ±0.005		PRODUCT SPEC				Applicator	
		4 PLC ±0.0005		APPLICATION SPEC					
		ANGLES ±0.0005		WEIGHT					
		FINISH		Customer Accessible Production Drawing		SCALE		1:1	
								SHEET	
								2	
								OF	
								4	
								REV	
								A	

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
A	66	-	-	SEE SHEET 1	-	-	-


DIMENSIONING AND TOLERANCING PER ASME Y14.5M-2003

C


B

A


FEED TYPE MECHANICAL




PNEUMATIC





SERVO LATCH PLATE




CAM POSITIONS




PACIFIC VERSION
Shown on sheets 3 of 4 & 4 of 4
(Atlantic version shown on sheets 1 of 4 & 2 of 4)



TERMINAL SUPPORT LOCATION



HOLDDOWN SET-UP



FEED TRACK POSITION
GUIDE BY INSULATION BARREL

THIS DRAWING IS CONTROLLED DOCUMENT NO. 1001000			
---	--	--	--

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2151691-2](#)