





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			A	INITIAL RELEASE	07JUN2012	LW	AC
			A1	REV PER ECR-12-013085	20JULY2012	LW	AC

- NOTES:
- 1 . MATERIALS:
HOUSING:HIGH TEMP , THERMOPLASTIC GLASS/MINERAL FILLED UL94V-0.
CONTACT::COPPER ALLOY
- △2 .FINISH OPTION
TIN OPTION:0.76um MINIMUM GOLD AT CONTACT AREA
2.54um MINIMUM NICKEL UNDERPLATE OVER ALL
TIN AT TAIL AREA.
TIN-LEAD OPTION:0.76um MINIMUM GOLD AT CONTACT AREA
2.54um MINIMUM NICKEL UNDERPLATE OVER ALL
TIN-LEAD AT TAIL AREA..
- △3 . PCB NOTE FOR DIAMETER 0.725mm PLATED HOLE.
-DRILLED HOLE SIZE IS 0.838mm
-PLATED WITH 0.007mm MIN.TIN OVER.
0.03 TO 0.08mm COPPER UNDERPLATE TO ACHIEVE
0.725±0.075mm HOLE.
4. MATES WITH 2169797-***.
- △5 . PART NUMBER AND DATE CODE AT ASSEMBLY AREA AS APPROXIMATE SHOWN.
- △6 .KEEP OUT ZONE FROM OTHER COMPONENTS.



OBSOLETE

TRAY	TIN-LEAD PLATING	5-2169806-1
	TIN PLATING	2169806-1
PACKAGING	△PLATING OPTION	PART NUMBER


THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN	12MAY2011	 TE Connectivity		
			CHK	12MAY2011			
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CMR	SZ	NAME	
mm				APVD	JHC		
	0 PLC	±"	PRODUCT SPEC	IMPACT PWD; 3 PAIR VERTICAL RECEPTACLE PRESS-FIT			
	1 PLC	±---					
	2 PLC	±.25					
	3 PLC	±---					
	4 PLC	±---	APPLICATION SPEC	SIZE			
	ANGLES	±°					
MATERIAL	FINISH	114-32028					CAGE CODE
		WEIGHT					
				DRAWING NO			
		CUSTOMER DRAWING		RESTRICTED TO			
				A100779C=2169806			
				SCALE 1:1 SHEET 1 OF 2 REV A			

D


C

B

A



PCB BOARD



CONNECTOR MATES WITH PCB

C

B

A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2169806-1](#)