





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION		DATE	APVD
-	-		BA	NEW DRAWING		24APR2012	ST.P



FOR FURTHER INFORMATION SEE DATA SHEET FOR
3650 SERIES-LOW INDUCTANCE,HIGH FREQUENCY CHIP INDUCTOR



SERIES	A Max.	B Max.	C Max.	E	F	G	H	I	J
3654 1E	1.15	0.70	0.60	0.45	0.20	0.60	0.65	0.35	0.50

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL -

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-

1 PLC ±0.5

2 PLC ±0.2

3 PLC ±0.1

4 PLC ±0.0001

ANGLES ±

FINISH -

DWN 24APR2012
RAGHAVENDRA K

CHK 24APR2012
ALLAN P

APVD 24APR2012
STEPHEN.P

PRODUCT SPEC -

APPLICATION SPEC -

WEIGHT 0.001 GRAM

CUSTOMER DRAWING

TE Connectivity

NAME -

CHIP INDUCTOR TYPE 3654 0201 SERIES

SIZE A3CAGE CODE 00779DRAWING NO C=2176086

RESTRICTED TO -

SCALE 32:1SHEET 1 OF 1REV BA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2176086-9](#)