






- 1 0-2302454-1 Kodierung A wie dargestellt
0-2302454-1 CODING A AS SHOWN
- 2 Passend zu Stiftwanne nach TE-Schnittstellenzeichnung 208-18006
MATING TO PINHEADER ACC. TE-INTERFACE DRAWING 208-18006
- 3 Kammer fuer MATenet 2Pos. NanoMQS female Insert module TE PN 0-2302450-X
CAVITY FOR MATenet 2Pos. NanoMQS FEMALE INSERT MODULE TE PN 0-2302450-X
- 4 Materialkennzeichnung
MATERIAL MARKING
- 5 TE-Logo
TE-LOGO
- 6 TE-Teil Nummer
TE-PART NUMBER
- 7 Revisionsstand
PART REVISION
- 8 Kontaktkammernummer
CONTACT CAVITY NUMBER
- 9 Produktionsdatum
PRODUCTION DATE
- 10 Anlieferzustand: 2. Kontaktsicherung geöffnet
DELIVERY CONDITION: RETAINER IN OPEN POSITION
- 11 Verpackung: Schuetzgut im Beutel im Karton
PACKAGING: LOOSE PIECES IN BAG IN BOX



B2	Z	0-2302454-9	A	Single-Port MATenet Frame, Code Z	PBT-GF10 0% regrind	0.9	water-blue 5021
	J	0-2302454-7	A	Single-Port MATenet Frame, Code J		0.9	beige 1001
	C	0-2302454-3	A	Single-Port MATenet Frame, Code C		0.9	blue 5012
	B	0-2302454-2	A	Single-Port MATenet Frame, Code B		0.9	white 9010
	A	0-2302454-1	A	Single-Port MATenet Frame, Code A		0.9	black 9011
	CODE	PART No.	Rev.	DESCRIPTION		MATERIAL	WEIGHT [in]

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 16AUG2016 CHK J.KIERWETTER 16AUG2016 R.WUERKER 29AUG2016 APVD A.KETTERER		NAME Single-Port MATenet Frame SINGLE-PORT MATenet FRAME -	
DIMENSIONS: MAXIMIERUNG mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: ALLEINGEHTOLERANZEN 0 P.LC ±0.2 1 P.LC ±0.1 2 P.LC ±0.1 3 P.LC ± 4 P.LC ± ANGLES/°WINKEL ±0°		PRODUCT SPEC PRODUCT SPEC 108-94568 APPLICATION SPEC VERABREITUNGSPZ. 114-94331	
		MATERIAL see table -		SIZE A1	
WEIGHT GEW./CMT see table		CAGE CODE 00779		DRAWING NO. C=2302454	
RESTRICTED TO NUR FÜR -		SCALE MASSSTAB 5:1		SHEET BLATT 1 von 2	
CUSTOMER DRAWING /KUNDENZEICHNUNG		REV. B		REV. B	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2302454-3](#)