




A	OBsolete	1, 4	1, 4	16.71 [.658]	3	8	7-534204-2	
	OBsolete	1,3	1,3	14.17 [.558]	2	6	7-534204-1	
	OBsolete	1, 2, 50, 51,99,100	1, 2, 50, 51,99,100	260.55 [10.258]	99	200	7-534204-0	
	OBsolete	1, 2, 40, 41, 79, 80	1, 2, 40, 41, 79, 80	209.75 [8.258]	79	160	6-534204-9	
	OBsolete	1, 2, 35, 36, 69, 70	1, 2, 35, 36, 69, 70	184.35 [7.258]	69	140	6-534204-8	
	OBsolete	1, 2, 32, 33, 64, 65	1, 2, 32, 33, 64, 65	171.65 [6.758]	64	130	6-534204-7	
		1, 2, 27, 28, 54, 55	1, 2, 27, 28, 54, 55	146.25 [5.758]	54	110	6-534204-6	
	OBsolete	1, 2, 47, 48	1, 2, 47, 48	128.47 [5.058]	47	96	6-534204-5	
	9		1, 2, 35, 36	1, 2, 35, 36	97.99 [3.858]	35	72	6-534204-4
			1, 2, 34, 35	1, 2, 34, 35	95.45 [3.758]	34	70	6-534204-3
		1, 2, 19, 20	1, 2, 19, 20	57.35 [2.258]	19	40	6-534204-2	
		1, 2, 11, 12	1, 2, 11, 12	37.03 [1.458]	11	24	6-534204-1	
OBsolete		1, 2, 7, 8	1, 2, 7, 8	26.87 [1.058]	7	16	6-534204-0	
A			1, 2, 9, 10	1, 2, 9, 10	31.95 [1.258]	9	20	5-534204-9
			1, 2, 39, 40	1, 2, 39, 40	108.15 [4.258]	39	80	5-534204-8
		OBsolete	1, 2, 30, 31, 59, 60	1, 2, 30, 31, 59, 60	158.95 [6.258]	59	120	5-534204-7
		OBsolete	1, 2, 25, 26, 49, 50	1, 2, 25, 26, 49, 50	133.55 [5.258]	49	100	5-534204-6
		A		1, 2, 29, 30	1, 2, 29, 30	82.75 [3.258]	29	60
			1, 2, 14, 15	1, 2, 14, 15	44.65 [1.758]	14	30	5-534204-4
			1, 2, 17, 18	1, 2, 17, 18	52.27 [2.058]	17	36	5-534204-3
			1, 2, 5, 6	1, 2, 5, 6	21.79 [.858]	5	12	5-534204-2
			1, 2, 24, 25	1, 2, 24, 25	70.05 [2.758]	24	50	5-534204-1
	8		1, 4	1, 4	16.71 [.658]	3	8	2-534204-2
8	1,3		1,3	14.17 [.558]	2	6	2-534204-1	
OBsolete	1, 2, 50, 51,99,100		1, 2, 50, 51,99,100	260.55 [10.258]	99	200	2-534204-0	
OBsolete	1, 2, 40, 41, 79, 80		1, 2, 40, 41, 79, 80	209.75 [8.258]	79	160	1-534204-9	
OBsolete	1, 2, 35, 36, 69, 70		1, 2, 35, 36, 69, 70	184.35 [7.258]	69	140	1-534204-8	
OBsolete	1, 2, 32, 33, 64, 65	1, 2, 32, 33, 64, 65	171.65 [6.758]	64	130	1-534204-7		
A		1, 2, 27, 28, 54, 55	1, 2, 27, 28, 54, 55	146.25 [5.758]	54	110	1-534204-6	
	OBsolete	1, 2, 47, 48	1, 2, 47, 48	128.47 [5.058]	47	96	1-534204-5	
	4		1, 2, 35, 36	1, 2, 35, 36	97.99 [3.858]	35	72	1-534204-4
			1, 2, 34, 35	1, 2, 34, 35	95.45 [3.758]	34	70	1-534204-3
			1, 2, 19, 20	1, 2, 19, 20	57.35 [2.258]	19	40	1-534204-2
			1, 2, 11, 12	1, 2, 11, 12	37.03 [1.458]	11	24	1-534204-1
			1, 2, 7, 8	1, 2, 7, 8	26.87 [1.058]	7	16	1-534204-0
			1, 2, 9, 10	1, 2, 9, 10	31.95 [1.258]	9	20	534204-9
			1, 2, 39, 40	1, 2, 39, 40	108.15 [4.258]	39	80	534204-8
		OBsolete	1, 2, 30, 31, 59, 60	1, 2, 30, 31, 59, 60	158.95 [6.258]	59	120	534204-7
OBsolete		1, 2, 25, 26, 49, 50	1, 2, 25, 26, 4					


△ PRELIMINARY PART – NOT RELEASED FOR PRODUCTION

9 CONTACT FINISH: DUPLEX PLATED 0.00076 [.000030] GOLD IN CONTACT AREA,
0.00127–0.00254 [.000050–.000100] MATTE TIN ON SOLDER TAILS,
ALL OVER 0.00127 [.000050] NICKEL.

△ 10 ROHS 2002/95/EC COMPLIANT.

△ 11 RECESSED AREA AROUND MOLD GATE IS OPTIONAL. THIS FEATURE IS ALLOWABLE ON
EITHER SIDE OF HOUSING OR MAY NOT BE PRESENT AT ALL.

△ 12 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 4/29/96 T. HOFFMAN CHK 5/7/96 A. GABANY		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.13 [.005] 3 PLC ± - 4 PLC ± - ANGLES ± -			
		NAME RECEPTACLE ASSY, MOD II, DBL ROW, 2.54 X 2.54 [.100 X .100] CL, GUIDE PIN EARS, CLOSED ENTRY,		SIZE A1	
MATERIAL 		PRODUCT SPEC — APPLICATION SPEC —			
FINISH SEE TABLE		WEIGHT —		DRAWING NO 00779	
CUSTOMER DRAWING		SCALE 6:1		SHEET 1 of 1	
				REV S4	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5-534204-2](#)