




















Notizen / NOTES

- 1 0-2305974-1 Kodierung A wie dargestellt
0-2305974-1 CODING A AS SHOWN
- 2 Passend zu Stiftwanne nach
TE-Schnittstellenzeichnung 208-18012
MATING TO PINHEADER ACC.
TE-INTERFACE DRAWING 208-18012
- 3 Kammer fuer MATEnet 2Pos. NanoMQS female Insert module
TE PN 0-2302450-X
CAVITY FOR MATEnet 2Pos. NanoMQS FEMALE INSERT MODULE
TE PN 0-2302450-X
- 4 Materialkennzeichnung
MATERIAL MARKING
- 5 TE-Logo
TE-LOGO
- 6 TE-Teile Nummer
TE-Part Number
- 7 Revisionsstand
PART REVISION
- 8 Kontaktkammernummer
CONTACT CAVITY NUMBER
- 9 Produktionsdatum
PRODUKTION DATE
- 10 Anlieferzustand: 2. Kontaktsicherung geoeffnet
DELIVERY CONDITION: RETAINER IN OPEN POSITION
- 11 Verpackung: Schueftgut im Beutel im Karton
PACKAGING: LOOSE PIECES IN BAG IN BOX



Z	0-2305974-9	A	Dual-Port MATenet Frame, Code Z	PBT-GF10 0% regrind	1.5	water-blue 5021
J	0-2305974-7	A	Dual-Port MATenet Frame, Code J		1.5	beige 1601
C	0-2305974-3	A	Dual-Port MATenet Frame, Code C		1.5	blue 5012
B	0-2305974-2	A	Dual-Port MATenet Frame, Code B		1.5	white 9010
A	0-2305974-1	A	Dual-Port MATenet Frame, Code A		1.5	black 9011
CODE	PART No.	REV.	DESCRIPTION		MATERIAL	WEIGHT [g]

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG. 130C T2016 CHK. R. WURKER APP'D. A. KETTLER 14.01.2016		 TE Connectivity	
DIMENSIONS: (mm)		TOL. FRANCES UNLESS OTHERWISE SPECIFIED: ALLGEMEINERLEGENEN		NAME Dual-Port MATenET Frame DUAL-PORT MATenET FRAME	
		0 P L C +0.2 1 P L C +0.1 2 P L C +0.1 3 P L C +0.1 4 P L C +0.1 ANGLE 5° ON INCL. FIN. IN SHOWER, ACHE, PARBE		PRODUKT SPEC PRODUKTSPEC 108-94568 APPLICATION SPEC VERABREITUNGSSPEC 111-94433	
MATERIAL		WEIGHT GEWICHT		SIZE A 1	
SEE TABLE		see table		CAGE CODE 00079	
-		CUSTOMER DRAWING		DRAWING NO. 02305974	
-		KUNDENZIEHNUNG		RESTRICTED TO NUR FÜR	
-		SCALE MASSSTAB		SCALE MASSSTAB	
-		5:1		5:1	
-		SHEET BLATT		SHEET BLATT	
-		1 OF VON		1 OF VON	
-		REV. A		REV. A	

[illegible]



B-MUSTER
PROTOTYPE B-SAMPLE

Z	9-2305974-9	A	Dual-Port MATenet Frame, Code Z		1.3	water-blue 5021
K	9-2305974-8	A	Dual-Port MATenet Frame, Code K		1.3	curry yellow 1027
J	9-2305974-7	A	Dual-Port MATenet Frame, Code J		1.3	beige 1001
H	9-2305974-6	A	Dual-Port MATenet Frame, Code H		1.3	heather violet 4003
E	9-2305974-5	A	Dual-Port MATenet Frame, Code E	PBT GF10 0% regrind	1.3	green 6018
D	9-2305974-4	A	Dual-Port MATenet Frame, Code D		1.3	claret violet 4004
C	9-2305974-3	A	Dual-Port MATenet Frame, Code C		1.3	blue 5012
B	9-2305974-2	A	Dual-Port MATenet Frame, Code B		1.3	white 9010
A	9-2305974-1	A	Dual-Port MATenet Frame, Code A		1.3	black 9011
CODE	PART No.	REV.	DESCRIPTION	MATERIAL	WEIGHT (g)	COLOUR similar RAL



THIS DRAWING IS A CONTROLLED DOCUMENT, DIMENSIONING AND TOLERANCING PER GPS (ISO STANDARDS)		DWN 23AUG2016 J. KIESSWETTER CON R. WUERKER		 TE Connectivity	
DIMENSIONS: MASSEITENEN mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: ALLE DIMENSIONEN TOLERANZEN		APVD 14OCT2016 A. KETTLER NAME Dual-Port MATenet Frame DUAL-PORT MATenet FRAME -	
		APPLICATION SPEC VERABREITUNGSSPEZ. 114-944.31		SIZE A1 CODE 00779 DRAWING NO. ZIEHNINGS-NR. C=2305974	
MATERIAL - SEE TABLE		ANGLES/OWINKEL ±° FÄHNSWINKEL ±°/ABW. see table		RESTRICTED TO NUR FÜR	
CUSTOMER DRAWING		/KUNDENZEICHNUNG		SCALE MASSTAB 1:1 SHEET BLATT 2 OF VON 2 REV A2	

OBSELETE



2. Kontaktsicherung geschlossen
RETAINER CLOSED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2305974-9](#)