

SPECIFICATION CONTROL DRAWING

55A6215

TITLE THREE CONDUCTOR CABLE, SHIELDED, JACKETED, NORMAL WEIGHT, 600 VOLT


Date 12-11-92

Revision C

This specification sheet forms a part of the latest issue of Raychem Specification 55A and MIL-C-27500 as applicable.

COMPONENT WIRES - 55A0813

SHIELD - TIN-COATED COPPER

JACKET - RADIATION-CROSSLINKED,
MODIFIED ETFE

CABLE CONSTRUCTION DETAILS

PART NUMBER	CONDUCTOR SIZE (AWG)	SHIELD SIZE (AWG)	JACKET THICKNESS (inches)		OUTSIDE DIAMETER (inches)		MAXIMUM WEIGHT (lbs/1000 ft)
			MINIMUM	MAXIMUM	NOMINAL	MAXIMUM	
55A6215-24-*	24	38	.005	.010	.130	.137	14.7
55A6215-22-*	22	38	.005	.010	.142	.149	18.8
55A6215-20-*	20	38	.005	.010	.159	.167	25.0
55A6215-18-*	18	38	.006	.011	.183	.191	33.6
55A6215-16-*	16	38	.006	.011	.200	.209	41.1
55A6215-14-*	14	38	.007	.012	.238	.250	57.8
55A6215-12-*	12	38	.007	.013	.275	.288	80.9

CABLE RATINGS AND ADDITIONAL REQUIREMENTS

TEMPERATURE RATING: 150°C

Maximum continuous conductor temperature

VOLTAGE RATING: 600 volts (rms)**AGING STABILITY: 230 ± 5°C for 96 hours****BLOCKING: 200 ± 3°C for 6 hours****CROSSLINKED VERIFICATION: 300 ± 5°C for 6 hours****DIELECTRIC WITHSTAND: 1500 volts (rms), 60 Hz****FLAMMABILITY: Procedure 1, 3 seconds (maximum);**

3 in. (maximum); no flaming of facial tissue

JACKET COLOR: White preferred**JACKET ELONGATION AND TENSILE STRENGTH:**

Elongation, 50% (minimum)

Tensile Strength, 5000 lbf/in² (minimum)**JACKET FLAWS:**

Spark Test, 1500 volts (rms), 60 Hz, 100% test

Impulse Dielectric Test, 6.0 kV (peak), 100% test

LOW TEMPERATURE-COLD BEND: -55 ± 5°C
for 4 hours**SHIELD COVERAGE: 85% (minimum)****THERMAL SHOCK: 230 ± 5°C for 4 hours****VOLTAGE WITHSTAND TEST (POST ENVIRONMENTAL):**
1000 volts (rms), 60 Hz, 1 minute**PART NUMBER:**

The *** in the part numbers above shall be replaced by color code designators with a slash separating the component wire colors and a dash separating the component wire colors from the jacket color.

Example: AWG 20, white, blue, and orange component wires; white jacket: 55A6215-20-9/6/3-9

NOTE: Nominal values are for information only.
Nominal values are not requirements.

This construction meets all the requirements of M27500-AWGSM3T23. less identification.

COLORS AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681.

DIMENSIONS ARE IN INCHES, AND UNLESS OTHERWISE DESIGNATED ARE NOMINAL.

RaychemRaychem Corporation
300 Constitution Drive, Menlo Park, California 94025
(415) 361 3333 TWX 910 373 1728

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[EL7259-000](#)