

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

LOC

DIST

AF

50

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	FIRST RELEASED	25MAR2019	WH	DZ

POSITION 1#

2.50
[.098]

POSITION 2#

2.50 TYP
[.098]


DIM L

DIM F

DIM M

POSITION 19#

POSITION 20#




9.80
[.386]

2

3.40
[.134]


POSITION 2#

0.60±0.05
[.024±.001]




Ø0.90
[.035]

DIM F



POSITION 1#

ULS




NOTES:

1 MATERIAL:
HOUSING: HIGH PERFORMANCE RESIN, UL94V-0, COLOR NATURAL
TERMINAL: COPPER ALLOY,80 U" TIN OVERALL

2 MATING PART:[]-2324579-[] AND []-2323743-[]

3 COMPLY WITH GLOW WIRE REQUIREMENTS FOR PARTS OF NON-METALLIC
MATERIAL SUPPORTING A CURRENT-CARRYING CONNECTION DETAILED IN
IEC 60335-1, SECTION 30(GWT)

10.47
[.412]



KINKED PIN OF SHEET 2

1.25 [.049]	2	47.50 [1.870]	52.89 [2.083]	40	4-2324245-0
0.00	2	45.00 [1.772]	50.39 [1.985]	38	3-2324245-8
1.25 [.049]	2	42.50 [1.673]	47.89 [1.886]	36	3-2324245-6
0.00	2	40.00 [1.575]	45.39 [1.788]	34	3-2324245-4
1.25 [.049]	2	37.50 [1.477]	42.89 [1.689]	32	3-2324245-2
0.00	2	35.00 [1.378]	40.39 [1.591]	30	3-2324245-0
1.25 [.049]	2	32.50 [1.280]	37.89 [1.492]	28	2-2324245-8
0.00	2	30.00 [1.181]	35.39 [1.394]	26	2-2324245-6
1.25 [.049]	2	27.50 [1.083]	32.89 [1.295]	24	2-2324245-4
0.00	2	25.00 [.984]	30.39 [1.197]	22	2-2324245-2
1.25 [.049]	2	22.50 [.886]	27.89 [1.098]	20	2-2324245-0
0.00	2	20.00 [.787]	25.39 [1.000]	18	1-2324245-8
1.25 [.049]	1	17.50 [.689]	22.89 [.901]	16	1-2324245-6
0.00	1	15.00 [.590]	20.39 [.803]	14	1-2324245-4
1.25 [.049]	1	12.50 [.492]	17.89 [.704]	12	1-2324245-2
0.00	1	10.00 [.394]	15.39 [.606]	10	1-2324245-0
1.25 [.049]	1	7.50 [.295]	12.89 [.507]	8	2324245-8
DIM "M"	NO. OF LATCH CUT-OUTS	DIM "F"	DIM "L"	NO. OF POSITIONS	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm[INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±
1 PLC ±
2 PLC ±0.25 [1.010]
3 PLC ±
4 PLC ±
ANGLES ±
FINISH

MATERIAL

DWN 26AUG2018
CHK WARREN HUO
DANIEL ZHANG
APVD 27AUG2018
DANIEL ZHANG

PRODUCT SPEC
108-106357
APPLICATION SPEC
114-13315
WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

NAME
ASSEMBLY, PIN HEADER,
EP 2.5, DUAL ROW, GLOW WIRE
VERTICAL,WITH BOSS

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-2324245

RESTRICTED TO
-

SCALE
N/A

SHEET
1

OF
2

REV
A

2-2324245-0 SHOWN

1471-9 (3/11)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-2324245-0](#)